



Essential SmartBright LED Projector – Value for money

Essential Smart Bright Projector

The Essential SmartBright LED Projector is a value-for-money product with high efficacy, good quality and reliability. It offers diverse configurations from 800 lm to 3,000 lm output, and has better beam performance with its lens design. It can be used in shopping centres and retail outlets. It's an ideal product family to distribute in trade market

Benefits

- Full range of lumen output from 800 lm to 3,000 lm
- Reliability and safety: meets national and international regulations
- Energy saving: High system efficacy with lower power consumption

Features

- System efficiency: up to 85 lm/W
- CRI 80, SDCM <5
- Beam Angle: 24-degree, 36-degree
- CCT: 3,000 K, 4,000 K, 5,000 K(G.C)
- High reliability, 20 Khrs (L70B50@25 °C)
- Mounting Type: 1C Track

Application

- Retail shop
- Fashion outlet
- Shopping centre

Essential Smart Bright Projector

Versions



Application Conditions

Ambient temperature range -20 to +40 °C

Approval and Application

Mech. impact protection code IK03

Ingress protection code IP20

Controls and Dimming

Dimmable No

Operating and Electrical

Input Voltage 220 to 240 V

General Information

Protection class IEC Safety class I (I)

Driver included Yes

Number of gear units 1 unit

Initial Performance (IEC Compliant)

Init. Colour rendering index >80

Luminous flux tolerance +/-10%

Application Conditions

Order Code	Full Product Name	Suitable for random switching
911401714052	ST030T LED8/830 8W 220-240V I NB BK CN	-
911401714372	ST030T LED8/830 8W 220-240V I NB BK	-
911401714382	ST030T LED8/840 8W 220-240V I NB BK	-
911401714392	ST030T LED8/830 8W 220-240V I MB BK	-
911401714402	ST030T LED8/840 8W 220-240V I MB BK	No
911401714412	ST030T LED12/830 14W 220-240V I NB BK	No
911401714422	ST030T LED12/840 14W 220-240V I NB BK	No
911401714432	ST030T LED12/830 14W 220-240V I MB BK	No
911401714452	ST030T LED20/830 23W 220-240V I NB BK	-
911401714462	ST030T LED20/840 23W 220-240V I NB BK	No
911401714472	ST030T LED20/830 23W 220-240V I MB BK	-
911401714482	ST030T LED20/840 23W 220-240V I MB BK	-
911401714492	ST030T LED30/830 35W 220-240V I NB BK	-
911401714502	ST030T LED30/840 35W 220-240V I NB BK	No
911401714512	ST030T LED30/830 35W 220-240V I MB BK	-
911401714522	ST030T LED30/840 35W 220-240V I MB BK	No
911401720652	ST030T LED8/850 8W 220-240V I NB BK	-
911401720662	ST030T LED8/850 8W 220-240V I MB BK	-
911401720672	ST030T LED12/850 14W 220-240V I NB BK	-
911401720682	ST030T LED12/850 14W 220-240V I MB BK	-
911401720692	ST030T LED20/850 23W 220-240V I NB BK	-
911401720702	ST030T LED20/850 23W 220-240V I MB BK	-
911401720712	ST030T LED30/850 35W 220-240V I NB BK	-
911401720722	ST030T LED30/850 35W 220-240V I MB BK	-
911401714212	ST030T LED8/830 8W 220-240V I NB WH	No
911401714222	ST030T LED8/840 8W 220-240V I NB WH	No
911401714232	ST030T LED8/830 8W 220-240V I MB WH	-
911401714242	ST030T LED8/840 8W 220-240V I MB WH	-
911401714252	ST030T LED12/830 14W 220-240V I NB WH	-
911401714262	ST030T LED12/840 14W 220-240V I NB WH	No
911401714272	ST030T LED12/830 14W 220-240V I MB WH	No
911401714282	ST030T LED12/840 14W 220-240V I MB WH	-
911401714292	ST030T LED20/830 23W 220-240V I NB WH	-
911401714302	ST030T LED20/840 23W 220-240V I NB WH	-
911401714312	ST030T LED20/830 23W 220-240V I MB WH	-
911401714322	ST030T LED20/840 23W 220-240V I MB WH	No

Essential Smart Bright Projector

Order Code	Full Product Name	Suitable for random switching
911401714332	ST030T LED30/830 35W 220-240V I NB WH	No
911401714342	ST030T LED30/840 35W 220-240V I NB WH	-
911401714352	ST030T LED30/830 35W 220-240V I MB WH	-
911401714362	ST030T LED30/840 35W 220-240V I MB WH	-
911401720572	ST030T LED8/850 8W 220-240V I NB WH	-
911401720582	ST030T LED8/850 8W 220-240V I MB WH	-
911401720592	ST030T LED12/850 14W 220-240V I NB WH	-
911401720602	ST030T LED12/850 14W 220-240V I MB WH	-
911401720612	ST030T LED20/850 23W 220-240V I NB WH	-
911401720622	ST030T LED20/850 23W 220-240V I MB WH	-
911401720632	ST030T LED30/850 35W 220-240V I NB WH	-
911401720642	ST030T LED30/850 35W 220-240V I MB WH	-

General Information (1/2)

Order Code	Full Product Name	CE mark	Optical cover/ lens type	ENEC mark	Flammability mark
911401714052	ST030T LED8/830 8W 220-240V I NB BK CN	-	Fashion proof optic beam angle 24°	-	-
911401714372	ST030T LED8/830 8W 220-240V I NB BK	CE mark	Fashion proof optic beam angle 24°	-	-
911401714382	ST030T LED8/840 8W 220-240V I NB BK	CE mark	Fashion proof optic beam angle 24°	-	-
911401714392	ST030T LED8/830 8W 220-240V I MB BK	CE mark	Fashion proof optic beam angle 36°	-	-
911401714402	ST030T LED8/840 8W 220-240V I MB BK	CE mark	Fashion proof optic beam angle 36°	-	NO
911401714412	ST030T LED12/830 14W 220-240V I NB BK	CE mark	Fashion proof optic beam angle 24°	-	NO
911401714422	ST030T LED12/840 14W 220-240V I NB BK	CE mark	Fashion proof optic beam angle 24°	-	NO
911401714432	ST030T LED12/830 14W 220-240V I MB BK	CE mark	Fashion proof optic beam angle 36°	-	NO
911401714452	ST030T LED20/830 23W 220-240V I NB BK	CE mark	Fashion proof optic beam angle 24°	-	-
911401714462	ST030T LED20/840 23W 220-240V I NB BK	CE mark	Fashion proof optic beam angle 24°	-	NO
911401714472	ST030T LED20/830 23W 220-240V I MB BK	CE mark	Fashion proof optic beam angle 36°	-	-
911401714482	ST030T LED20/840 23W 220-240V I MB BK	CE mark	Fashion proof optic beam angle 36°	-	-
911401714492	ST030T LED30/830 35W 220-240V I NB BK	CE mark	Fashion proof optic beam angle 24°	-	-
911401714502	ST030T LED30/840 35W 220-240V I NB BK	CE mark	Fashion proof optic beam angle 24°	-	NO
911401714512	ST030T LED30/830 35W 220-240V I MB BK	CE mark	Fashion proof optic beam angle 36°	-	-
911401714522	ST030T LED30/840 35W 220-240V I MB BK	CE mark	Fashion proof optic beam angle 36°	-	NO
911401720652	ST030T LED8/850 8W 220-240V I NB BK	-	Fashion proof optic beam angle 24°	-	-
911401720662	ST030T LED8/850 8W 220-240V I MB BK	-	Fashion proof optic beam angle 36°	-	-
911401720672	ST030T LED12/850 14W 220-240V I NB BK	-	Fashion proof optic beam angle 24°	-	-
911401720682	ST030T LED12/850 14W 220-240V I MB BK	-	Fashion proof optic beam angle 36°	-	-
911401720692	ST030T LED20/850 23W 220-240V I NB BK	-	Fashion proof optic beam angle 24°	-	-
911401720702	ST030T LED20/850 23W 220-240V I MB BK	-	Fashion proof optic beam angle 36°	-	-

Essential Smart Bright Projector

Order Code	Full Product Name	CE mark	Optical cover/ lens type	ENEC mark	Flammability mark
911401720712	ST030T LED30/850 35W 220-240V I NB BK	-	Fashion proof optic beam angle 24°	-	-
911401720722	ST030T LED30/850 35W 220-240V I MB BK	-	Fashion proof optic beam angle 36°	-	-
911401714212	ST030T LED8/830 8W 220-240V I NB WH	CE mark	Fashion proof optic beam angle 24°	-	NO
911401714222	ST030T LED8/840 8W 220-240V I NB WH	CE mark	Fashion proof optic beam angle 24°	-	NO
911401714232	ST030T LED8/830 8W 220-240V I MB WH	CE mark	Fashion proof optic beam angle 36°	-	-
911401714242	ST030T LED8/840 8W 220-240V I MB WH	CE mark	Fashion proof optic beam angle 36°	-	-
911401714252	ST030T LED12/830 14W 220-240V I NB WH	CE mark	Fashion proof optic beam angle 24°	-	-
911401714262	ST030T LED12/840 14W 220-240V I NB WH	CE mark	Fashion proof optic beam angle 24°	-	NO
911401714272	ST030T LED12/830 14W 220-240V I MB WH	CE mark	Fashion proof optic beam angle 36°	-	NO
911401714282	ST030T LED12/840 14W 220-240V I MB WH	CE mark	Fashion proof optic beam angle 36°	-	-
911401714292	ST030T LED20/830 23W 220-240V I NB WH	CE mark	Fashion proof optic beam angle 24°	-	-
911401714302	ST030T LED20/840 23W 220-240V I NB WH	CE mark	Fashion proof optic beam angle 24°	-	-
911401714312	ST030T LED20/830 23W 220-240V I MB WH	CE mark	Fashion proof optic beam angle 36°	-	-

Order Code	Full Product Name	CE mark	Optical cover/ lens type	ENEC mark	Flammability mark
911401714322	ST030T LED20/840 23W 220-240V I MB WH	CE mark	Fashion proof optic beam angle 36°	-	NO
911401714332	ST030T LED30/830 35W 220-240V I NB WH	CE mark	Fashion proof optic beam angle 24°	-	NO
911401714342	ST030T LED30/840 35W 220-240V I NB WH	CE mark	Fashion proof optic beam angle 24°	-	-
911401714352	ST030T LED30/830 35W 220-240V I MB WH	CE mark	Fashion proof optic beam angle 36°	-	-
911401714362	ST030T LED30/840 35W 220-240V I MB WH	CE mark	Fashion proof optic beam angle 36°	-	-
911401720572	ST030T LED8/850 8W 220-240V I NB WH	-	Fashion proof optic beam angle 24°	-	-
911401720582	ST030T LED8/850 8W 220-240V I MB WH	-	Fashion proof optic beam angle 36°	-	-
911401720592	ST030T LED12/850 14W 220-240V I NB WH	-	Fashion proof optic beam angle 24°	-	-
911401720602	ST030T LED12/850 14W 220-240V I MB WH	-	Fashion proof optic beam angle 36°	-	-
911401720612	ST030T LED20/850 23W 220-240V I NB WH	-	Fashion proof optic beam angle 24°	-	-
911401720622	ST030T LED20/850 23W 220-240V I MB WH	-	Fashion proof optic beam angle 36°	-	-
911401720632	ST030T LED30/850 35W 220-240V I NB WH	-	Fashion proof optic beam angle 24°	-	-
911401720642	ST030T LED30/850 35W 220-240V I MB WH	-	Fashion proof optic beam angle 36°	-	-

General Information (2/2)

Order Code	Full Product Name	Optic type
911401714052	ST030T LED8/830 8W 220-240V I NB BK CN	-
911401714372	ST030T LED8/830 8W 220-240V I NB BK	-
911401714382	ST030T LED8/840 8W 220-240V I NB BK	-
911401714392	ST030T LED8/830 8W 220-240V I MB BK	-
911401714402	ST030T LED8/840 8W 220-240V I MB BK	No
911401714412	ST030T LED12/830 14W 220-240V I NB BK	No
911401714422	ST030T LED12/840 14W 220-240V I NB BK	No
911401714432	ST030T LED12/830 14W 220-240V I MB BK	No

Order Code	Full Product Name	Optic type
911401714452	ST030T LED20/830 23W 220-240V I NB BK	-
911401714462	ST030T LED20/840 23W 220-240V I NB BK	No
911401714472	ST030T LED20/830 23W 220-240V I MB BK	-
911401714482	ST030T LED20/840 23W 220-240V I MB BK	-
911401714492	ST030T LED30/830 35W 220-240V I NB BK	-
911401714502	ST030T LED30/840 35W 220-240V I NB BK	No
911401714512	ST030T LED30/830 35W 220-240V I MB BK	-
911401714522	ST030T LED30/840 35W 220-240V I MB BK	No

Essential Smart Bright Projector

Order Code	Full Product Name	Optic type
911401720652	ST030T LED8/850 8W 220-240V I NB BK	-
911401720662	ST030T LED8/850 8W 220-240V I MB BK	-
911401720672	ST030T LED12/850 14W 220-240V I NB BK	-
911401720682	ST030T LED12/850 14W 220-240V I MB BK	-
911401720692	ST030T LED20/850 23W 220-240V I NB BK	-
911401720702	ST030T LED20/850 23W 220-240V I MB BK	-
911401720712	ST030T LED30/850 35W 220-240V I NB BK	-
911401720722	ST030T LED30/850 35W 220-240V I MB BK	-
911401714212	ST030T LED8/830 8W 220-240V I NB WH	No
911401714222	ST030T LED8/840 8W 220-240V I NB WH	No
911401714232	ST030T LED8/830 8W 220-240V I MB WH	-
911401714242	ST030T LED8/840 8W 220-240V I MB WH	-
911401714252	ST030T LED12/830 14W 220-240V I NB WH	-
911401714262	ST030T LED12/840 14W 220-240V I NB WH	No
911401714272	ST030T LED12/830 14W 220-240V I MB WH	No
911401714282	ST030T LED12/840 14W 220-240V I MB WH	-

Order Code	Full Product Name	Optic type
911401714292	ST030T LED20/830 23W 220-240V I NB WH	-
911401714302	ST030T LED20/840 23W 220-240V I NB WH	-
911401714312	ST030T LED20/830 23W 220-240V I MB WH	-
911401714322	ST030T LED20/840 23W 220-240V I MB WH	No
911401714332	ST030T LED30/830 35W 220-240V I NB WH	No
911401714342	ST030T LED30/840 35W 220-240V I NB WH	-
911401714352	ST030T LED30/830 35W 220-240V I MB WH	-
911401714362	ST030T LED30/840 35W 220-240V I MB WH	-
911401720572	ST030T LED8/850 8W 220-240V I NB WH	-
911401720582	ST030T LED8/850 8W 220-240V I MB WH	-
911401720592	ST030T LED12/850 14W 220-240V I NB WH	-
911401720602	ST030T LED12/850 14W 220-240V I MB WH	-
911401720612	ST030T LED20/850 23W 220-240V I NB WH	-
911401720622	ST030T LED20/850 23W 220-240V I MB WH	-
911401720632	ST030T LED30/850 35W 220-240V I NB WH	-
911401720642	ST030T LED30/850 35W 220-240V I MB WH	-

Initial Performance (IEC Compliant) (1/2)

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Colour Temperature	Initial LED luminaire efficacy	Initial luminous flux
911401714052	ST030T LED8/830 8W 220-240V I NB BK CN	SDCM<5	3000 K	100 lm/W	800 lm
911401714372	ST030T LED8/830 8W 220-240V I NB BK	SDCM<5	3000 K	100 lm/W	800 lm
911401714382	ST030T LED8/840 8W 220-240V I NB BK	SDCM<5	4000 K	100 lm/W	800 lm
911401714392	ST030T LED8/830 8W 220-240V I MB BK	SDCM<5	3000 K	100 lm/W	800 lm
911401714402	ST030T LED8/840 8W 220-240V I MB BK	SDCM<5	4000 K	100 lm/W	800 lm
911401714412	ST030T LED12/830 14W 220-240V I NB BK	SDCM<5	3000 K	85.71 lm/W	1200 lm
911401714422	ST030T LED12/840 14W 220-240V I NB BK	SDCM<5	4000 K	85.71 lm/W	1200 lm
911401714432	ST030T LED12/830 14W	SDCM<5	3000 K	85.71 lm/W	1200 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Colour Temperature	Initial LED luminaire efficacy	Initial luminous flux
911401714452	ST030T LED20/830 23W 220-240V I NB BK	SDCM<5	3000 K	52.17 lm/W	1200 lm
911401714462	ST030T LED20/840 23W 220-240V I NB BK	SDCM<5	4000 K	86.96 lm/W	2000 lm
911401714472	ST030T LED20/830 23W 220-240V I MB BK	SDCM<5	3000 K	86.96 lm/W	2000 lm
911401714482	ST030T LED20/840 23W 220-240V I MB BK	SDCM<5	4000 K	86.96 lm/W	2000 lm
911401714492	ST030T LED30/830 35W 220-240V I NB BK	SDCM<5	3000 K	57.14 lm/W	2000 lm
911401714502	ST030T LED30/840 35W 220-240V I NB BK	SDCM<5	4000 K	85.71 lm/W	3000 lm
911401714512	ST030T LED30/830 35W 220-240V I MB BK	SDCM<5	3000 K	85.71 lm/W	3000 lm

Essential Smart Bright Projector

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Colour Temperature	Initial LED luminaire efficacy	Initial luminous flux
911401714522	ST030T LED30/840 35W 220-240V I MB BK	SDCM<5	4000 K	85.71 lm/W	3000 lm
911401720652	ST030T LED8/850 8W 220-240V I NB BK	SDCM<6	5000 K	100 lm/W	800 lm
911401720662	ST030T LED8/850 8W 220-240V I MB BK	SDCM<6	5000 K	100 lm/W	800 lm
911401720672	ST030T LED12/850 14W 220-240V I NB BK	SDCM<6	5000 K	85.71 lm/W	1200 lm
911401720682	ST030T LED12/850 14W 220-240V I MB BK	SDCM<6	5000 K	85.71 lm/W	1200 lm
911401720692	ST030T LED20/850 23W 220-240V I NB BK	SDCM<6	5000 K	86.96 lm/W	2000 lm
911401720702	ST030T LED20/850 23W 220-240V I MB BK	SDCM<6	5000 K	86.96 lm/W	2000 lm
911401720712	ST030T LED30/850 35W 220-240V I NB BK	SDCM<6	5000 K	100 lm/W	3500 lm
911401720722	ST030T LED30/850 35W 220-240V I MB BK	SDCM<6	5000 K	100 lm/W	3500 lm
911401714212	ST030T LED8/830 8W 220-240V I NB WH	SDCM<5	3000 K	100 lm/W	800 lm
911401714222	ST030T LED8/840 8W 220-240V I NB WH	SDCM<5	4000 K	100 lm/W	800 lm
911401714232	ST030T LED8/830 8W 220-240V I MB WH	SDCM<5	3000 K	100 lm/W	800 lm
911401714242	ST030T LED8/840 8W	SDCM<5	4000 K	100 lm/W	800 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Colour Temperature	Initial LED luminaire efficacy	Initial luminous flux
	220-240V I MB WH				
911401714252	ST030T LED12/830 14W 220-240V I NB WH	SDCM<5	3000 K	85.71 lm/W	1200 lm
911401714262	ST030T LED12/840 14W 220-240V I NB WH	SDCM<5	4000 K	85.71 lm/W	1200 lm
911401714272	ST030T LED12/830 14W 220-240V I MB WH	SDCM<5	3000 K	85.71 lm/W	1200 lm
911401714282	ST030T LED12/840 14W 220-240V I MB WH	SDCM<5	4000 K	85.71 lm/W	1200 lm
911401714292	ST030T LED20/830 23W 220-240V I NB WH	SDCM<5	3000 K	86.96 lm/W	2000 lm
911401714302	ST030T LED20/840 23W 220-240V I NB WH	SDCM<5	4000 K	86.96 lm/W	2000 lm
911401714312	ST030T LED20/830 23W 220-240V I MB WH	SDCM<5	3000 K	86.96 lm/W	2000 lm
911401714322	ST030T LED20/840 23W 220-240V I MB WH	SDCM<5	4000 K	86.96 lm/W	2000 lm
911401714332	ST030T LED30/830 35W 220-240V I NB WH	SDCM<5	3000 K	85.71 lm/W	3000 lm
911401714342	ST030T LED30/840 35W 220-240V I NB WH	SDCM<5	4000 K	85.71 lm/W	3000 lm
911401714352	ST030T LED30/830 35W 220-240V I MB WH	SDCM<5	3000 K	85.71 lm/W	3000 lm
911401714362	ST030T LED30/840 35W 220-240V I MB WH	SDCM<5	4000 K	85.71 lm/W	3000 lm

Essential Smart Bright Projector

	Full Product	Initial	Init. Corr.	Initial LED	Initial
Order Code	Name	chromaticity	Colour Temperature	luminaire efficacy	luminous flux
911401720572	ST030T LED8/850 8W 220-240V I NB WH	SDCM<6	5000 K	100 lm/W	800 lm
911401720582	ST030T LED8/850 8W 220-240V I MB WH	SDCM<6	5000 K	100 lm/W	800 lm
911401720592	ST030T LED12/850 14W 220-240V I NB WH	SDCM<6	5000 K	85.71 lm/W	1200 lm
911401720602	ST030T LED12/850 14W 220-240V I MB WH	SDCM<6	5000 K	85.71 lm/W	1200 lm

	Full Product	Initial	Init. Corr.	Initial LED	Initial
Order Code	Name	chromaticity	Colour Temperature	luminaire efficacy	luminous flux
911401720612	ST030T LED20/850 23W 220-240V I NB WH	SDCM<6	5000 K	86.96 lm/W	2000 lm
911401720622	ST030T LED20/850 23W 220-240V I MB WH	SDCM<6	5000 K	86.96 lm/W	2000 lm
911401720632	ST030T LED30/850 35W 220-240V I NB WH	SDCM<6	5000 K	100 lm/W	3500 lm
911401720642	ST030T LED30/850 35W 220-240V I MB WH	SDCM<6	5000 K	100 lm/W	3500 lm

Initial Performance (IEC Compliant) (2/2)

Order Code	Full Product Name	Initial input power
911401714052	ST030T LED8/830 8W 220-240V I NB BK CN	8 W
911401714372	ST030T LED8/830 8W 220-240V I NB BK	8 W
911401714382	ST030T LED8/840 8W 220-240V I NB BK	8 W
911401714392	ST030T LED8/830 8W 220-240V I MB BK	8 W
911401714402	ST030T LED8/840 8W 220-240V I MB BK	8 W
911401714412	ST030T LED12/830 14W 220-240V I NB BK	14 W
911401714422	ST030T LED12/840 14W 220-240V I NB BK	14 W
911401714432	ST030T LED12/830 14W 220-240V I MB BK	14 W
911401714452	ST030T LED20/830 23W 220-240V I NB BK	23 W
911401714462	ST030T LED20/840 23W 220-240V I NB BK	23 W
911401714472	ST030T LED20/830 23W 220-240V I MB BK	23 W
911401714482	ST030T LED20/840 23W 220-240V I MB BK	23 W
911401714492	ST030T LED30/830 35W 220-240V I NB BK	35 W
911401714502	ST030T LED30/840 35W 220-240V I NB BK	35 W
911401714512	ST030T LED30/830 35W 220-240V I MB BK	35 W
911401714522	ST030T LED30/840 35W 220-240V I MB BK	35 W
911401720652	ST030T LED8/850 8W 220-240V I NB BK	8 W
911401720662	ST030T LED8/850 8W 220-240V I MB BK	8 W
911401720672	ST030T LED12/850 14W 220-240V I NB BK	14 W
911401720682	ST030T LED12/850 14W 220-240V I MB BK	14 W
911401720692	ST030T LED20/850 23W 220-240V I NB BK	23 W
911401720702	ST030T LED20/850 23W 220-240V I MB BK	23 W
911401720712	ST030T LED30/850 35W 220-240V I NB BK	35 W
911401720722	ST030T LED30/850 35W 220-240V I MB BK	35 W

Order Code	Full Product Name	Initial input power
911401714212	ST030T LED8/830 8W 220-240V I NB WH	8 W
911401714222	ST030T LED8/840 8W 220-240V I NB WH	8 W
911401714232	ST030T LED8/830 8W 220-240V I MB WH	8 W
911401714242	ST030T LED8/840 8W 220-240V I MB WH	8 W
911401714252	ST030T LED12/830 14W 220-240V I NB WH	14 W
911401714262	ST030T LED12/840 14W 220-240V I NB WH	14 W
911401714272	ST030T LED12/830 14W 220-240V I MB WH	14 W
911401714282	ST030T LED12/840 14W 220-240V I MB WH	14 W
911401714292	ST030T LED20/830 23W 220-240V I NB WH	23 W
911401714302	ST030T LED20/840 23W 220-240V I NB WH	23 W
911401714312	ST030T LED20/830 23W 220-240V I MB WH	23 W
911401714322	ST030T LED20/840 23W 220-240V I MB WH	23 W
911401714332	ST030T LED30/830 35W 220-240V I NB WH	35 W
911401714342	ST030T LED30/840 35W 220-240V I NB WH	35 W
911401714352	ST030T LED30/830 35W 220-240V I MB WH	35 W
911401714362	ST030T LED30/840 35W 220-240V I MB WH	35 W
911401720572	ST030T LED8/850 8W 220-240V I NB WH	8 W
911401720582	ST030T LED8/850 8W 220-240V I MB WH	8 W
911401720592	ST030T LED12/850 14W 220-240V I NB WH	14 W
911401720602	ST030T LED12/850 14W 220-240V I MB WH	14 W
911401720612	ST030T LED20/850 23W 220-240V I NB WH	23 W
911401720622	ST030T LED20/850 23W 220-240V I MB WH	23 W
911401720632	ST030T LED30/850 35W 220-240V I NB WH	35 W
911401720642	ST030T LED30/850 35W 220-240V I MB WH	35 W

Mechanical and Housing

Order Code	Full Product Name	Colour
911401714052	ST030T LED8/830 8W 220-240V I NB BK CN	black

Order Code	Full Product Name	Colour
911401714372	ST030T LED8/830 8W 220-240V I NB BK	black

Essential Smart Bright Projector

Order Code	Full Product Name	Colour
911401714382	ST030T LED8/840 8W 220-240V I NB BK	black
911401714392	ST030T LED8/830 8W 220-240V I MB BK	black
911401714402	ST030T LED8/840 8W 220-240V I MB BK	black
911401714412	ST030T LED12/830 14W 220-240V I NB BK	black
911401714422	ST030T LED12/840 14W 220-240V I NB BK	black
911401714432	ST030T LED12/830 14W 220-240V I MB BK	black
911401714452	ST030T LED20/830 23W 220-240V I NB BK	black
911401714462	ST030T LED20/840 23W 220-240V I NB BK	black
911401714472	ST030T LED20/830 23W 220-240V I MB BK	black
911401714482	ST030T LED20/840 23W 220-240V I MB BK	black
911401714492	ST030T LED30/830 35W 220-240V I NB BK	black
911401714502	ST030T LED30/840 35W 220-240V I NB BK	black
911401714512	ST030T LED30/830 35W 220-240V I MB BK	black
911401714522	ST030T LED30/840 35W 220-240V I MB BK	black
911401720652	ST030T LED8/850 8W 220-240V I NB BK	black
911401720662	ST030T LED8/850 8W 220-240V I MB BK	black
911401720672	ST030T LED12/850 14W 220-240V I NB BK	black
911401720682	ST030T LED12/850 14W 220-240V I MB BK	black
911401720692	ST030T LED20/850 23W 220-240V I NB BK	black
911401720702	ST030T LED20/850 23W 220-240V I MB BK	black
911401720712	ST030T LED30/850 35W 220-240V I NB BK	black
911401720722	ST030T LED30/850 35W 220-240V I MB BK	black
911401714212	ST030T LED8/830 8W 220-240V I NB WH	White

Order Code	Full Product Name	Colour
911401714222	ST030T LED8/840 8W 220-240V I NB WH	White
911401714232	ST030T LED8/830 8W 220-240V I MB WH	White
911401714242	ST030T LED8/840 8W 220-240V I MB WH	White
911401714252	ST030T LED12/830 14W 220-240V I NB WH	White
911401714262	ST030T LED12/840 14W 220-240V I NB WH	White
911401714272	ST030T LED12/830 14W 220-240V I MB WH	White
911401714282	ST030T LED12/840 14W 220-240V I MB WH	White
911401714292	ST030T LED20/830 23W 220-240V I NB WH	White
911401714302	ST030T LED20/840 23W 220-240V I NB WH	White
911401714312	ST030T LED20/830 23W 220-240V I MB WH	White
911401714322	ST030T LED20/840 23W 220-240V I MB WH	White
911401714332	ST030T LED30/830 35W 220-240V I NB WH	White
911401714342	ST030T LED30/840 35W 220-240V I NB WH	White
911401714352	ST030T LED30/830 35W 220-240V I MB WH	White
911401714362	ST030T LED30/840 35W 220-240V I MB WH	White
911401720572	ST030T LED8/850 8W 220-240V I NB WH	White
911401720582	ST030T LED8/850 8W 220-240V I MB WH	White
911401720592	ST030T LED12/850 14W 220-240V I NB WH	White
911401720602	ST030T LED12/850 14W 220-240V I MB WH	White
911401720612	ST030T LED20/850 23W 220-240V I NB WH	White
911401720622	ST030T LED20/850 23W 220-240V I MB WH	White
911401720632	ST030T LED30/850 35W 220-240V I NB WH	White
911401720642	ST030T LED30/850 35W 220-240V I MB WH	White

