



Essential SmartBright LED Projector is value for money product with high efficacy, good quality and reliability. It offers diverse configurations from 800lm to 3000lm output, and better beam performance with lens design.

Essential Smart Bright Projector

It could apply to shopping mall, retail store, It's an ideal product family to distribute in trade market

Essential Smart Bright Projector

Benefits

- Full range of lumen output from 800lm to 3000lm
- Reliability and safety: meets national and international regulation
- Energy saving: High system efficacy with lower power consumption

Features

- System efficiency, up to 85lm/W
- CRI 80, SDCM <5
- Beam Angle: 24 degree, 36 degree
- CCT: 3000K, 4000K, 5000K(G.C)
- High reliability, 20Khrs (L70B50@25°C)
- Mounting Type : 1C Track

Application

- Retail shop
- Fashion store
- Shopping mall

Versions



ST030T

ST030T

Essential Smart Bright Projector

Application Conditions

Ambient temperature range -20 to +40 °C

Approval and Application

Mech. impact protection code IK03

Ingress protection code IP20

Controls and Dimming

Dimmable No

Operating and Electrical

Input Voltage 220 to 240 V

General Information

Driver included Yes

Number of gear units 1 unit

Initial Performance (IEC Compliant)

Init. Color Rendering Index >80

Luminous flux tolerance +/-10%

Application Conditions

Order Code	Full Product Name	Suitable for random switching
911401713892	ST030T LED8/830 8W 220-240V I NB WH CN	-
911401713902	ST030T LED8/840 8W 220-240V I NB WH CN	-
911401713912	ST030T LED8/830 8W 220-240V I MB WH CN	-
911401713922	ST030T LED8/840 8W 220-240V I MB WH CN	-
911401713932	ST030T LED12/830 14W 220-240V I NB WH CN	-
911401713942	ST030T LED12/840 14W 220-240V I NB WH CN	No
911401713952	ST030T LED12/830 14W 220-240V I MB WH CN	-
911401713962	ST030T LED12/840 14W 220-240V I MB WH CN	-
911401713972	ST030T LED20/830 23W 220-240V I NB WH CN	-
911401713982	ST030T LED20/840 23W 220-240V I NB WH CN	-
911401713992	ST030T LED20/830 23W 220-240V I MB WH CN	-
911401714002	ST030T LED20/840 23W 220-240V I MB WH CN	No
911401714012	ST030T LED30/830 35W 220-240V I NB WH CN	-
911401714022	ST030T LED30/840 35W 220-240V I NB WH CN	No
911401714032	ST030T LED30/830 35W 220-240V I MB WH CN	-
911401714042	ST030T LED30/840 35W 220-240V I MB WH CN	-
911401714212	ST030T LED8/830 8W 220-240V I NB WH	No
911401714222	ST030T LED8/840 8W 220-240V I NB WH	No
911401714232	ST030T LED8/830 8W 220-240V I MB WH	-
911401714242	ST030T LED8/840 8W 220-240V I MB WH	-
911401714252	ST030T LED12/830 14W 220-240V I NB WH	-
911401714262	ST030T LED12/840 14W 220-240V I NB WH	No
911401714272	ST030T LED12/830 14W 220-240V I MB WH	No
911401714282	ST030T LED12/840 14W 220-240V I MB WH	-
911401714292	ST030T LED20/830 23W 220-240V I NB WH	-
911401714302	ST030T LED20/840 23W 220-240V I NB WH	-
911401714312	ST030T LED20/830 23W 220-240V I MB WH	-
911401714322	ST030T LED20/840 23W 220-240V I MB WH	No
911401714332	ST030T LED30/830 35W 220-240V I NB WH	No
911401714342	ST030T LED30/840 35W 220-240V I NB WH	-
911401714352	ST030T LED30/830 35W 220-240V I MB WH	-
911401714362	ST030T LED30/840 35W 220-240V I MB WH	-
911401714532	ST030T LED6/830 6W UNV II NB WH TW	-
911401714542	ST030T LED6/840 6W UNV II NB WH TW	-
911401714552	ST030T LED6/850 6W UNV II NB WH TW	-
911401714562	ST030T LED6/830 6W UNV II MB WH TW	-
911401714572	ST030T LED6/840 6W UNV II MB WH TW	-
911401714582	ST030T LED6/850 6W UNV II MB WH TW	-
911401714592	ST030T LED12/830 14W UNV II NB WH TW	-
911401714602	ST030T LED12/840 14W UNV II NB WH TW	-
911401714612	ST030T LED12/850 14W UNV II NB WH TW	-
911401714622	ST030T LED12/830 14W UNV II MB WH TW	-
911401714632	ST030T LED12/840 14W UNV II MB WH TW	-
911401714642	ST030T LED12/850 14W UNV II MB WH TW	-
911401714652	ST030T LED20/830 24W UNV II NB WH TW	-
911401714662	ST030T LED20/840 24W UNV II NB WH TW	-
911401714672	ST030T LED20/850 24W UNV II NB WH TW	-
911401714682	ST030T LED20/830 24W UNV II MB WH TW	-
911401714692	ST030T LED20/840 24W UNV II MB WH TW	-
911401714702	ST030T LED20/850 24W UNV II MB WH TW	-
911401720412	ST030T LED8/850 8W 220-240V I NB WH CN	-

Essential Smart Bright Projector

Order Code	Full Product Name	Suitable for random switching
911401720422	ST030T LED8/850 8W 220-240V I MB WH CN	-
911401720432	ST030T LED12/850 14W 220-240V I NB WH CN	-
911401720442	ST030T LED12/850 14W 220-240V I MB WH CN	-
911401720452	ST030T LED20/850 23W 220-240V I NB WH CN	-
911401720462	ST030T LED20/850 23W 220-240V I MB WH CN	-
911401720472	ST030T LED30/850 35W 220-240V I NB WH CN	-
911401720482	ST030T LED30/850 35W 220-240V I MB WH CN	-
911401720572	ST030T LED8/850 8W 220-240V I NB WH	-
911401720582	ST030T LED8/850 8W 220-240V I MB WH	-
911401720592	ST030T LED12/850 14W 220-240V I NB WH	-
911401720602	ST030T LED12/850 14W 220-240V I MB WH	-
911401720612	ST030T LED20/850 23W 220-240V I NB WH	-
911401720622	ST030T LED20/850 23W 220-240V I MB WH	-
911401720632	ST030T LED30/850 35W 220-240V I NB WH	-
911401720642	ST030T LED30/850 35W 220-240V I MB WH	-
911401714052	ST030T LED8/830 8W 220-240V I NB BK CN	-
911401714062	ST030T LED8/840 8W 220-240V I NB BK CN	-
911401714072	ST030T LED8/830 8W 220-240V I MB BK CN	No
911401714082	ST030T LED8/840 8W 220-240V I MB BK CN	No
911401714092	ST030T LED12/830 14W 220-240V I NB BK CN	-
911401714102	ST030T LED12/840 14W 220-240V I NB BK CN	No
911401714112	ST030T LED12/830 14W 220-240V I MB BK CN	-
911401714122	ST030T LED12/840 14W 220-240V I MB BK CN	No
911401714132	ST030T LED20/830 23W 220-240V I NB BK CN	-
911401714142	ST030T LED20/840 23W 220-240V I NB BK CN	No
911401714152	ST030T LED20/830 23W 220-240V I MB BK CN	-
911401714162	ST030T LED20/840 23W 220-240V I MB BK CN	No
911401714172	ST030T LED30/830 35W 220-240V I NB BK CN	-
911401714182	ST030T LED30/840 35W 220-240V I NB BK CN	No
911401714192	ST030T LED30/830 35W 220-240V I MB BK CN	No
911401714202	ST030T LED30/840 35W 220-240V I MB BK CN	-
911401714372	ST030T LED8/830 8W 220-240V I NB BK	-
911401714382	ST030T LED8/840 8W 220-240V I NB BK	-
911401714392	ST030T LED8/830 8W 220-240V I MB BK	-
911401714402	ST030T LED8/840 8W 220-240V I MB BK	No
911401714412	ST030T LED12/830 14W 220-240V I NB BK	No
911401714422	ST030T LED12/840 14W 220-240V I NB BK	No
911401714432	ST030T LED12/830 14W 220-240V I MB BK	No
911401714452	ST030T LED20/830 23W 220-240V I NB BK	-
911401714462	ST030T LED20/840 23W 220-240V I NB BK	No
911401714472	ST030T LED20/830 23W 220-240V I MB BK	-
911401714482	ST030T LED20/840 23W 220-240V I MB BK	-
911401714492	ST030T LED30/830 35W 220-240V I NB BK	-
911401714502	ST030T LED30/840 35W 220-240V I NB BK	No
911401714512	ST030T LED30/830 35W 220-240V I MB BK	-
911401714522	ST030T LED30/840 35W 220-240V I MB BK	No
911401714712	ST030T LED6/830 6W UNV II NB BK TW	-
911401714722	ST030T LED6/840 6W UNV II NB BK TW	-
911401714732	ST030T LED6/850 6W UNV II NB BK TW	-
911401714742	ST030T LED6/830 6W UNV II MB BK TW	-
911401714752	ST030T LED6/840 6W UNV II MB BK TW	-
911401714762	ST030T LED6/850 6W UNV II MB BK TW	-

Essential Smart Bright Projector

Order Code	Full Product Name	Suitable for random switching
911401714772	ST030T LED12/830 14W UNV II NB BK TW	-
911401714782	ST030T LED12/840 14W UNV II NB BK TW	-
911401714792	ST030T LED12/850 14W UNV II NB BK TW	-
911401714802	ST030T LED12/830 14W UNV II MB BK TW	-
911401714812	ST030T LED12/840 14W UNV II MB BK TW	-
911401714822	ST030T LED12/850 14W UNV II MB BK TW	-
911401714832	ST030T LED20/830 24W UNV II NB BK TW	-
911401714842	ST030T LED20/840 24W UNV II NB BK TW	-
911401714852	ST030T LED20/850 24W UNV II NB BK TW	-
911401714862	ST030T LED20/830 24W UNV II MB BK TW	-
911401714872	ST030T LED20/840 24W UNV II MB BK TW	-
911401714882	ST030T LED20/850 24W UNV II MB BK TW	-
911401720492	ST030T LED8/850 8W 220-240V I NB BK CN	-
911401720502	ST030T LED8/850 8W 220-240V I MB BK CN	-
911401720512	ST030T LED12/850 14W 220-240V I NB BK CN	-
911401720522	ST030T LED12/850 14W 220-240V I MB BK CN	-
911401720532	ST030T LED20/850 23W 220-240V I NB BK CN	-
911401720542	ST030T LED20/850 23W 220-240V I MB BK CN	-
911401720552	ST030T LED30/850 35W 220-240V I NB BK CN	-
911401720562	ST030T LED30/850 35W 220-240V I MB BK CN	-
911401720652	ST030T LED8/850 8W 220-240V I NB BK	-
911401720662	ST030T LED8/850 8W 220-240V I MB BK	-
911401720672	ST030T LED12/850 14W 220-240V I NB BK	-
911401720682	ST030T LED12/850 14W 220-240V I MB BK	-
911401720692	ST030T LED20/850 23W 220-240V I NB BK	-
911401720702	ST030T LED20/850 23W 220-240V I MB BK	-
911401720712	ST030T LED30/850 35W 220-240V I NB BK	-
911401720722	ST030T LED30/850 35W 220-240V I MB BK	-

General Information (1/2)

Order Code	Full Product Name	CE mark	Protection class IEC	Optical cover/ lens type	ENEC mark	Order Code	Full Product Name	CE mark	Protection class IEC	Optical cover/ lens type	ENEC mark
911401713892	ST030T LED8/830 8W 220-240V I NB WH CN	-	Safety class I	Fashion proof optic beam angle 24°	-	911401713952	ST030T LED12/830 14W 220-240V I MB WH CN	-	Safety class I	Fashion proof optic beam angle 36°	-
911401713902	ST030T LED8/840 8W 220-240V I NB WH CN	-	Safety class I	Fashion proof optic beam angle 24°	-	911401713962	ST030T LED12/840 14W 220-240V I MB WH CN	-	Safety class I	Fashion proof optic beam angle 36°	-
911401713912	ST030T LED8/830 8W 220-240V I MB WH CN	-	Safety class I	Fashion proof optic beam angle 36°	-	911401713972	ST030T LED20/830 23W 220-240V I NB WH CN	-	Safety class I	Fashion proof optic beam angle 24°	-
911401713922	ST030T LED8/840 8W 220-240V I MB WH CN	-	Safety class I	Fashion proof optic beam angle 36°	-	911401713982	ST030T LED20/840 23W 220-240V I NB WH CN	-	Safety class I	Fashion proof optic beam angle 24°	-
911401713932	ST030T LED12/830 14W 220-240V I NB WH CN	-	Safety class I	Fashion proof optic beam angle 24°	-	911401713992	ST030T LED20/830 23W 220-240V I MB WH CN	-	Safety class I	Fashion proof optic beam angle 36°	-
911401713942	ST030T LED12/840 14W 220-240V I NB WH CN	-	Safety class I	Fashion proof optic beam angle 24°	-	911401714002	ST030T LED20/840 23W 220-240V I MB WH CN	-	Safety class I	Fashion proof optic beam angle 36°	-

Essential Smart Bright Projector

Order Code	Full Product Name	CE mark	Protection class IEC	Optical cover/ lens type	ENEC mark
911401714012	ST030T LED30/830 35W 220-240V I NB WH CN	-	Safety class I	Fashion proof optic beam angle 24°	-
911401714022	ST030T LED30/840 35W 220-240V I NB WH CN	-	Safety class I	Fashion proof optic beam angle 24°	-
911401714032	ST030T LED30/830 35W 220-240V I MB WH CN	-	Safety class I	Fashion proof optic beam angle 36°	-
911401714042	ST030T LED30/840 35W 220-240V I MB WH CN	-	Safety class I	Fashion proof optic beam angle 36°	-
911401714212	ST030T LED8/830 8W 220-240V I NB WH	CE mark	Safety class I	Fashion proof optic beam angle 24°	-
911401714222	ST030T LED8/840 8W 220-240V I NB WH	CE mark	Safety class I	Fashion proof optic beam angle 24°	-
911401714232	ST030T LED8/830 8W 220-240V I MB WH	CE mark	Safety class I	Fashion proof optic beam angle 36°	-
911401714242	ST030T LED8/840 8W 220-240V I MB WH	CE mark	Safety class I	Fashion proof optic beam angle 36°	-
911401714252	ST030T LED12/830 14W 220-240V I NB WH	CE mark	Safety class I	Fashion proof optic beam angle 24°	-
911401714262	ST030T LED12/840 14W 220-240V I NB WH	CE mark	Safety class I	Fashion proof optic beam angle 24°	-
911401714272	ST030T LED12/830 14W 220-240V I MB WH	CE mark	Safety class I	Fashion proof optic beam angle 36°	-
911401714282	ST030T LED12/840 14W 220-240V I MB WH	CE mark	Safety class I	Fashion proof optic beam angle 36°	-
911401714292	ST030T LED20/830 23W 220-240V I NB WH	CE mark	Safety class I	Fashion proof optic beam angle 24°	-
911401714302	ST030T LED20/840 23W 220-240V I NB WH	CE mark	Safety class I	Fashion proof optic beam angle 24°	-
911401714312	ST030T LED20/830 23W 220-240V I MB WH	CE mark	Safety class I	Fashion proof optic beam angle 36°	-
911401714322	ST030T LED20/840 23W 220-240V I MB WH	CE mark	Safety class I	Fashion proof optic beam angle 36°	-
911401714332	ST030T LED30/830 35W 220-240V I NB WH	CE mark	Safety class I	Fashion proof optic beam angle 24°	-

Order Code	Full Product Name	CE mark	Protection class IEC	Optical cover/ lens type	ENEC mark
911401714342	ST030T LED30/840 35W 220-240V I NB WH	CE mark	Safety class I	Fashion proof optic beam angle 24°	-
911401714352	ST030T LED30/830 35W 220-240V I MB WH	CE mark	Safety class I	Fashion proof optic beam angle 36°	-
911401714362	ST030T LED30/840 35W 220-240V I MB WH	CE mark	Safety class I	Fashion proof optic beam angle 36°	-
911401714532	ST030T LED6/830 6W UNV II NB WH TW	-	Safety class II	Fashion proof optic beam angle 24°	-
911401714542	ST030T LED6/840 6W UNV II NB WH TW	-	Safety class II	Fashion proof optic beam angle 24°	-
911401714552	ST030T LED6/850 6W UNV II NB WH TW	-	Safety class II	Fashion proof optic beam angle 24°	-
911401714562	ST030T LED6/830 6W UNV II MB WH TW	-	Safety class II	Fashion proof optic beam angle 36°	-
911401714572	ST030T LED6/840 6W UNV II MB WH TW	-	Safety class II	Fashion proof optic beam angle 36°	-
911401714582	ST030T LED6/850 6W UNV II MB WH TW	-	Safety class II	Fashion proof optic beam angle 36°	-
911401714592	ST030T LED12/830 14W UNV II NB WH TW	-	Safety class II	Fashion proof optic beam angle 24°	-
911401714602	ST030T LED12/840 14W UNV II NB WH TW	-	Safety class II	Fashion proof optic beam angle 24°	-
911401714612	ST030T LED12/850 14W UNV II NB WH TW	-	Safety class II	Fashion proof optic beam angle 24°	-
911401714622	ST030T LED12/830 14W UNV II MB WH TW	-	Safety class II	Fashion proof optic beam angle 36°	-
911401714632	ST030T LED12/840 14W UNV II MB WH TW	-	Safety class II	Fashion proof optic beam angle 36°	-
911401714642	ST030T LED12/850 14W UNV II MB WH TW	-	Safety class II	Fashion proof optic beam angle 36°	-
911401714652	ST030T LED20/830 24W UNV II NB WH TW	-	Safety class II	Fashion proof optic beam angle 24°	-
911401714662	ST030T LED20/840 24W UNV II NB WH TW	-	Safety class II	Fashion proof optic beam angle 24°	-

Essential Smart Bright Projector

Order Code	Full Product Name	CE mark	Protection class IEC	Optical cover/ lens type	ENEC mark	Order Code	Full Product Name	CE mark	Protection class IEC	Optical cover/ lens type	ENEC mark
911401714672	ST030T LED20/850 24W UNV II NB WH TW	-	Safety class II	Fashion proof optic beam angle 24°	-	911401720622	ST030T LED20/850 23W 220-240V I MB WH	-	Safety class I	Fashion proof optic beam angle 36°	-
911401714682	ST030T LED20/830 24W UNV II MB WH TW	-	Safety class II	Fashion proof optic beam angle 36°	-	911401720632	ST030T LED30/850 35W 220-240V I NB WH	-	Safety class I	Fashion proof optic beam angle 24°	-
911401714692	ST030T LED20/840 24W UNV II MB WH TW	-	Safety class II	Fashion proof optic beam angle 36°	-	911401720642	ST030T LED30/850 35W 220-240V I MB WH	-	Safety class I	Fashion proof optic beam angle 36°	-
911401714702	ST030T LED20/850 24W UNV II MB WH TW	-	Safety class II	Fashion proof optic beam angle 36°	-	911401714052	ST030T LED8/830 8W 220-240V I NB BK CN	-	Safety class I	Fashion proof optic beam angle 24°	-
911401720412	ST030T LED8/850 8W 220-240V I NB WH CN	-	Safety class I	Fashion proof optic beam angle 24°	-	911401714062	ST030T LED8/840 8W 220-240V I NB BK CN	-	Safety class I	Fashion proof optic beam angle 24°	-
911401720422	ST030T LED8/850 8W 220-240V I MB WH CN	-	Safety class I	Fashion proof optic beam angle 36°	-	911401714072	ST030T LED8/830 8W 220-240V I MB BK CN	-	Safety class I	Fashion proof optic beam angle 36°	-
911401720432	ST030T LED12/850 14W 220-240V I NB WH CN	-	Safety class I	Fashion proof optic beam angle 24°	-	911401714082	ST030T LED8/840 8W 220-240V I MB BK CN	-	Safety class I	Fashion proof optic beam angle 36°	-
911401720442	ST030T LED12/850 14W 220-240V I MB WH CN	-	Safety class I	Fashion proof optic beam angle 36°	-	911401714092	ST030T LED12/830 14W 220-240V I NB BK CN	-	Safety class I	Fashion proof optic beam angle 24°	-
911401720452	ST030T LED20/850 23W 220-240V I NB WH CN	-	Safety class I	Fashion proof optic beam angle 24°	-	911401714102	ST030T LED12/840 14W 220-240V I NB BK CN	-	Safety class I	Fashion proof optic beam angle 24°	-
911401720462	ST030T LED20/850 23W 220-240V I MB WH CN	-	Safety class I	Fashion proof optic beam angle 36°	-	911401714112	ST030T LED12/830 14W 220-240V I MB BK CN	-	Safety class I	Fashion proof optic beam angle 36°	-
911401720472	ST030T LED30/850 35W 220-240V I NB WH CN	-	Safety class I	Fashion proof optic beam angle 24°	-	911401714122	ST030T LED12/840 14W 220-240V I MB BK CN	-	Safety class I	Fashion proof optic beam angle 36°	-
911401720482	ST030T LED30/850 35W 220-240V I MB WH CN	-	Safety class I	Fashion proof optic beam angle 36°	-	911401714132	ST030T LED20/830 23W 220-240V I NB BK CN	-	Safety class I	Fashion proof optic beam angle 24°	-
911401720572	ST030T LED8/850 8W 220-240V I NB WH	-	Safety class I	Fashion proof optic beam angle 24°	-	911401714142	ST030T LED20/840 23W 220-240V I NB BK CN	-	Safety class I	Fashion proof optic beam angle 24°	-
911401720582	ST030T LED8/850 8W 220-240V I MB WH	-	Safety class I	Fashion proof optic beam angle 36°	-	911401714152	ST030T LED20/830 23W 220-240V I MB BK CN	-	Safety class I	Fashion proof optic beam angle 36°	-
911401720592	ST030T LED12/850 14W 220-240V I NB WH	-	Safety class I	Fashion proof optic beam angle 24°	-	911401714162	ST030T LED20/840 23W 220-240V I MB BK CN	-	Safety class I	Fashion proof optic beam angle 36°	-
911401720602	ST030T LED12/850 14W 220-240V I MB WH	-	Safety class I	Fashion proof optic beam angle 36°	-	911401714172	ST030T LED30/830 35W 220-240V I NB BK CN	-	Safety class I	Fashion proof optic beam angle 24°	-
911401720612	ST030T LED20/850 23W 220-240V I NB WH	-	Safety class I	Fashion proof optic beam angle 24°	-	911401714182	ST030T LED30/840 35W 220-240V I NB BK CN	-	Safety class I	Fashion proof optic beam angle 24°	-

Essential Smart Bright Projector

Order Code	Full Product Name	CE mark	Protection class IEC	Optical cover/ lens type	ENEC mark	Order Code	Full Product Name	CE mark	Protection class IEC	Optical cover/ lens type	ENEC mark
911401714192	ST030T LED30/830 35W 220-240V I MB BK CN	-	Safety class I	Fashion proof optic beam angle 36°	-	911401714712	ST030T LED6/830 6W UNV II NB BK TW	-	Safety class II	Fashion proof optic beam angle 24°	-
911401714202	ST030T LED30/840 35W 220-240V I MB BK CN	-	Safety class I	Fashion proof optic beam angle 36°	-	911401714722	ST030T LED6/840 6W UNV II NB BK TW	-	Safety class II	Fashion proof optic beam angle 24°	-
911401714372	ST030T LED8/830 8W 220-240V I NB BK	CE mark	Safety class I	Fashion proof optic beam angle 24°	-	911401714732	ST030T LED6/850 6W UNV II NB BK TW	-	Safety class II	Fashion proof optic beam angle 24°	-
911401714382	ST030T LED8/840 8W 220-240V I NB BK	CE mark	Safety class I	Fashion proof optic beam angle 24°	-	911401714742	ST030T LED6/830 6W UNV II MB BK TW	-	Safety class II	Fashion proof optic beam angle 36°	-
911401714392	ST030T LED8/830 8W 220-240V I MB BK	CE mark	Safety class I	Fashion proof optic beam angle 36°	-	911401714752	ST030T LED6/840 6W UNV II MB BK TW	-	Safety class II	Fashion proof optic beam angle 36°	-
911401714402	ST030T LED8/840 8W 220-240V I MB BK	CE mark	Safety class I	Fashion proof optic beam angle 36°	-	911401714762	ST030T LED6/850 6W UNV II MB BK TW	-	Safety class II	Fashion proof optic beam angle 36°	-
911401714412	ST030T LED12/830 14W 220-240V I NB BK	CE mark	Safety class I	Fashion proof optic beam angle 24°	-	911401714772	ST030T LED12/830 14W UNV II NB BK TW	-	Safety class II	Fashion proof optic beam angle 24°	-
911401714422	ST030T LED12/840 14W 220-240V I NB BK	CE mark	Safety class I	Fashion proof optic beam angle 24°	-	911401714782	ST030T LED12/840 14W UNV II NB BK TW	-	Safety class II	Fashion proof optic beam angle 24°	-
911401714432	ST030T LED12/830 14W 220-240V I MB BK	CE mark	Safety class I	Fashion proof optic beam angle 36°	-	911401714792	ST030T LED12/850 14W UNV II NB BK TW	-	Safety class II	Fashion proof optic beam angle 24°	-
911401714452	ST030T LED20/830 23W 220-240V I NB BK	CE mark	Safety class I	Fashion proof optic beam angle 24°	-	911401714802	ST030T LED12/830 14W UNV II MB BK TW	-	Safety class II	Fashion proof optic beam angle 36°	-
911401714462	ST030T LED20/840 23W 220-240V I NB BK	CE mark	Safety class I	Fashion proof optic beam angle 24°	-	911401714812	ST030T LED12/840 14W UNV II MB BK TW	-	Safety class II	Fashion proof optic beam angle 36°	-
911401714472	ST030T LED20/830 23W 220-240V I MB BK	CE mark	Safety class I	Fashion proof optic beam angle 36°	-	911401714822	ST030T LED12/850 14W UNV II MB BK TW	-	Safety class II	Fashion proof optic beam angle 36°	-
911401714482	ST030T LED20/840 23W 220-240V I MB BK	CE mark	Safety class I	Fashion proof optic beam angle 36°	-	911401714832	ST030T LED20/830 24W UNV II NB BK TW	-	Safety class II	Fashion proof optic beam angle 24°	-
911401714492	ST030T LED30/830 35W 220-240V I NB BK	CE mark	Safety class I	Fashion proof optic beam angle 24°	-	911401714842	ST030T LED20/840 24W UNV II NB BK TW	-	Safety class II	Fashion proof optic beam angle 24°	-
911401714502	ST030T LED30/840 35W 220-240V I NB BK	CE mark	Safety class I	Fashion proof optic beam angle 24°	-	911401714852	ST030T LED20/850 24W UNV II NB BK TW	-	Safety class II	Fashion proof optic beam angle 24°	-
911401714512	ST030T LED30/830 35W 220-240V I MB BK	CE mark	Safety class I	Fashion proof optic beam angle 36°	-	911401714862	ST030T LED20/830 24W UNV II MB BK TW	-	Safety class II	Fashion proof optic beam angle 36°	-
911401714522	ST030T LED30/840 35W 220-240V I MB BK	CE mark	Safety class I	Fashion proof optic beam angle 36°	-	911401714872	ST030T LED20/840 24W UNV II MB BK TW	-	Safety class II	Fashion proof optic beam angle 36°	-

Essential Smart Bright Projector

Order Code	Full Product Name	CE mark	Protection class IEC	Optical cover/ lens type	ENEC mark
911401714882	ST030T LED20/850 24W UNV II MB BK TW	-	Safety class II	Fashion proof optic beam angle 36°	-
911401720492	ST030T LED8/850 8W 220-240V I NB BK CN	-	Safety class I	Fashion proof optic beam angle 24°	-
911401720502	ST030T LED8/850 8W 220-240V I MB BK CN	-	Safety class I	Fashion proof optic beam angle 36°	-
911401720512	ST030T LED12/850 14W 220-240V I NB BK CN	-	Safety class I	Fashion proof optic beam angle 24°	-
911401720522	ST030T LED12/850 14W 220-240V I MB BK CN	-	Safety class I	Fashion proof optic beam angle 36°	-
911401720532	ST030T LED20/850 23W 220-240V I NB BK CN	-	Safety class I	Fashion proof optic beam angle 24°	-
911401720542	ST030T LED20/850 23W 220-240V I MB BK CN	-	Safety class I	Fashion proof optic beam angle 36°	-
911401720552	ST030T LED30/850 35W 220-240V I NB BK CN	-	Safety class I	Fashion proof optic beam angle 24°	-
911401720562	ST030T LED30/850 35W 220-240V I MB BK CN	-	Safety class I	Fashion proof optic beam angle 36°	-

Order Code	Full Product Name	CE mark	Protection class IEC	Optical cover/ lens type	ENEC mark
911401720652	ST030T LED8/850 8W 220-240V I NB BK	-	Safety class I	Fashion proof optic beam angle 24°	-
911401720662	ST030T LED8/850 8W 220-240V I MB BK	-	Safety class I	Fashion proof optic beam angle 36°	-
911401720672	ST030T LED12/850 14W 220-240V I NB BK	-	Safety class I	Fashion proof optic beam angle 24°	-
911401720682	ST030T LED12/850 14W 220-240V I MB BK	-	Safety class I	Fashion proof optic beam angle 36°	-
911401720692	ST030T LED20/850 23W 220-240V I NB BK	-	Safety class I	Fashion proof optic beam angle 24°	-
911401720702	ST030T LED20/850 23W 220-240V I MB BK	-	Safety class I	Fashion proof optic beam angle 36°	-
911401720712	ST030T LED30/850 35W 220-240V I NB BK	-	Safety class I	Fashion proof optic beam angle 24°	-
911401720722	ST030T LED30/850 35W 220-240V I MB BK	-	Safety class I	Fashion proof optic beam angle 36°	-

General Information (2/2)

Order Code	Full Product Name	Flammability mark	Optic type
911401713892	ST030T LED8/830 8W 220-240V I NB WH CN	-	-
911401713902	ST030T LED8/840 8W 220-240V I NB WH CN	-	-
911401713912	ST030T LED8/830 8W 220-240V I MB WH CN	-	-
911401713922	ST030T LED8/840 8W 220-240V I MB WH CN	-	-
911401713932	ST030T LED12/830 14W 220-240V I NB WH CN	-	-
911401713942	ST030T LED12/840 14W 220-240V I NB WH CN	-	-
911401713952	ST030T LED12/830 14W 220-240V I MB WH CN	-	-
911401713962	ST030T LED12/840 14W 220-240V I MB WH CN	-	-
911401713972	ST030T LED20/830 23W 220-240V I NB WH CN	-	-

Order Code	Full Product Name	Flammability mark	Optic type
911401713982	ST030T LED20/840 23W 220-240V I NB WH CN	-	-
911401713992	ST030T LED20/830 23W 220-240V I MB WH CN	-	-
911401714002	ST030T LED20/840 23W 220-240V I MB WH CN	-	-
911401714012	ST030T LED30/830 35W 220-240V I NB WH CN	-	-
911401714022	ST030T LED30/840 35W 220-240V I NB WH CN	-	-
911401714032	ST030T LED30/830 35W 220-240V I MB WH CN	-	-
911401714042	ST030T LED30/840 35W 220-240V I MB WH CN	-	-
911401714212	ST030T LED8/830 8W 220-240V I NB WH	-	-
911401714222	ST030T LED8/840 8W 220-240V I NB WH	-	-
911401714232	ST030T LED8/830 8W 220-240V I MB WH	-	-
911401714242	ST030T LED8/840 8W 220-240V I MB WH	-	-

Essential Smart Bright Projector

Order Code	Full Product Name	Flammability mark	Optic type
911401714252	ST030T LED12/830 14W 220-240V I NB WH	-	-
911401714262	ST030T LED12/840 14W 220-240V I NB WH	-	-
911401714272	ST030T LED12/830 14W 220-240V I MB WH	-	-
911401714282	ST030T LED12/840 14W 220-240V I MB WH	-	-
911401714292	ST030T LED20/830 23W 220-240V I NB WH	-	-
911401714302	ST030T LED20/840 23W 220-240V I NB WH	-	-
911401714312	ST030T LED20/830 23W 220-240V I MB WH	-	-
911401714322	ST030T LED20/840 23W 220-240V I MB WH	-	-
911401714332	ST030T LED30/830 35W 220-240V I NB WH	-	-
911401714342	ST030T LED30/840 35W 220-240V I NB WH	-	-
911401714352	ST030T LED30/830 35W 220-240V I MB WH	-	-
911401714362	ST030T LED30/840 35W 220-240V I MB WH	-	-
911401714532	ST030T LED6/830 6W UNV II NB WH TW	-	-
911401714542	ST030T LED6/840 6W UNV II NB WH TW	-	-
911401714552	ST030T LED6/850 6W UNV II NB WH TW	-	-
911401714562	ST030T LED6/830 6W UNV II MB WH TW	-	-
911401714572	ST030T LED6/840 6W UNV II MB WH TW	-	-
911401714582	ST030T LED6/850 6W UNV II MB WH TW	-	-
911401714592	ST030T LED12/830 14W UNV II NB WH TW	-	-
911401714602	ST030T LED12/840 14W UNV II NB WH TW	-	-
911401714612	ST030T LED12/850 14W UNV II NB WH TW	-	-
911401714622	ST030T LED12/830 14W UNV II MB WH TW	-	-
911401714632	ST030T LED12/840 14W UNV II MB WH TW	-	-
911401714642	ST030T LED12/850 14W UNV II MB WH TW	-	-
911401714652	ST030T LED20/830 24W UNV II NB WH TW	-	-
911401714662	ST030T LED20/840 24W UNV II NB WH TW	-	-
911401714672	ST030T LED20/850 24W UNV II NB WH TW	-	-
911401714682	ST030T LED20/830 24W UNV II MB WH TW	-	-
911401714692	ST030T LED20/840 24W UNV II MB WH TW	-	-
911401714702	ST030T LED20/850 24W UNV II MB WH TW	-	-

Order Code	Full Product Name	Flammability mark	Optic type
911401720412	ST030T LED8/850 8W 220-240V I NB WH CN	-	-
911401720422	ST030T LED8/850 8W 220-240V I MB WH CN	-	-
911401720432	ST030T LED12/850 14W 220-240V I NB WH CN	-	-
911401720442	ST030T LED12/850 14W 220-240V I MB WH CN	-	-
911401720452	ST030T LED20/850 23W 220-240V I NB WH CN	-	-
911401720462	ST030T LED20/850 23W 220-240V I MB WH CN	-	-
911401720472	ST030T LED30/850 35W 220-240V I NB WH CN	-	-
911401720482	ST030T LED30/850 35W 220-240V I MB WH CN	-	-
911401720572	ST030T LED8/850 8W 220-240V I NB WH	-	-
911401720582	ST030T LED8/850 8W 220-240V I MB WH	-	-
911401720592	ST030T LED12/850 14W 220-240V I NB WH	-	-
911401720602	ST030T LED12/850 14W 220-240V I MB WH	-	-
911401720612	ST030T LED20/850 23W 220-240V I NB WH	-	-
911401720622	ST030T LED20/850 23W 220-240V I MB WH	-	-
911401720632	ST030T LED30/850 35W 220-240V I NB WH	-	-
911401720642	ST030T LED30/850 35W 220-240V I MB WH	-	-
911401714052	ST030T LED8/830 8W 220-240V I NB BK CN	-	-
911401714062	ST030T LED8/840 8W 220-240V I NB BK CN	-	-
911401714072	ST030T LED8/830 8W 220-240V I MB BK CN	-	-
911401714082	ST030T LED8/840 8W 220-240V I MB BK CN	-	-
911401714092	ST030T LED12/830 14W 220-240V I NB BK CN	-	-
911401714102	ST030T LED12/840 14W 220-240V I NB BK CN	-	-
911401714112	ST030T LED12/830 14W 220-240V I MB BK CN	-	-
911401714122	ST030T LED12/840 14W 220-240V I MB BK CN	-	-
911401714132	ST030T LED20/830 23W 220-240V I NB BK CN	-	-
911401714142	ST030T LED20/840 23W 220-240V I NB BK CN	-	-

Essential Smart Bright Projector

Order Code	Full Product Name	Flammability mark	Optic type
911401714152	ST030T LED20/830 23W 220-240V I MB BK CN	-	-
911401714162	ST030T LED20/840 23W 220-240V I MB BK CN	-	-
911401714172	ST030T LED30/830 35W 220-240V I NB BK CN	-	-
911401714182	ST030T LED30/840 35W 220-240V I NB BK CN	-	-
911401714192	ST030T LED30/830 35W 220-240V I MB BK CN	-	-
911401714202	ST030T LED30/840 35W 220-240V I MB BK CN	-	-
911401714372	ST030T LED8/830 8W 220-240V I NB BK	-	-
911401714382	ST030T LED8/840 8W 220-240V I NB BK	-	-
911401714392	ST030T LED8/830 8W 220-240V I MB BK	-	-
911401714402	ST030T LED8/840 8W 220-240V I MB BK	-	-
911401714412	ST030T LED12/830 14W 220-240V I NB BK	-	-
911401714422	ST030T LED12/840 14W 220-240V I NB BK	-	-
911401714432	ST030T LED12/830 14W 220-240V I MB BK	-	-
911401714452	ST030T LED20/830 23W 220-240V I NB BK	-	-
911401714462	ST030T LED20/840 23W 220-240V I NB BK	-	-
911401714472	ST030T LED20/830 23W 220-240V I MB BK	-	-
911401714482	ST030T LED20/840 23W 220-240V I MB BK	-	-
911401714492	ST030T LED30/830 35W 220-240V I NB BK	-	-
911401714502	ST030T LED30/840 35W 220-240V I NB BK	-	-
911401714512	ST030T LED30/830 35W 220-240V I MB BK	-	-
911401714522	ST030T LED30/840 35W 220-240V I MB BK	-	-
911401714712	ST030T LED6/830 6W UNV II NB BK TW	-	-
911401714722	ST030T LED6/840 6W UNV II NB BK TW	-	-
911401714732	ST030T LED6/850 6W UNV II NB BK TW	-	-
911401714742	ST030T LED6/830 6W UNV II MB BK TW	-	-
911401714752	ST030T LED6/840 6W UNV II MB BK TW	-	-
911401714762	ST030T LED6/850 6W UNV II MB BK TW	-	-
911401714772	ST030T LED12/830 14W UNV II NB BK TW	-	-

Order Code	Full Product Name	Flammability mark	Optic type
911401714782	ST030T LED12/840 14W UNV II NB BK TW	-	-
911401714792	ST030T LED12/850 14W UNV II NB BK TW	-	-
911401714802	ST030T LED12/830 14W UNV II MB BK TW	-	-
911401714812	ST030T LED12/840 14W UNV II MB BK TW	-	-
911401714822	ST030T LED12/850 14W UNV II MB BK TW	-	-
911401714832	ST030T LED20/830 24W UNV II NB BK TW	-	-
911401714842	ST030T LED20/840 24W UNV II NB BK TW	-	-
911401714852	ST030T LED20/850 24W UNV II NB BK TW	-	-
911401714862	ST030T LED20/830 24W UNV II MB BK TW	-	-
911401714872	ST030T LED20/840 24W UNV II MB BK TW	-	-
911401714882	ST030T LED20/850 24W UNV II MB BK TW	-	-
911401720492	ST030T LED8/850 8W 220-240V I NB BK CN	-	-
911401720502	ST030T LED8/850 8W 220-240V I MB BK CN	-	-
911401720512	ST030T LED12/850 14W 220-240V I NB BK CN	-	-
911401720522	ST030T LED12/850 14W 220-240V I MB BK CN	-	-
911401720532	ST030T LED20/850 23W 220-240V I NB BK CN	-	-
911401720542	ST030T LED20/850 23W 220-240V I MB BK CN	-	-
911401720552	ST030T LED30/850 35W 220-240V I NB BK CN	-	-
911401720562	ST030T LED30/850 35W 220-240V I MB BK CN	-	-
911401720652	ST030T LED8/850 8W 220-240V I NB BK	-	-
911401720662	ST030T LED8/850 8W 220-240V I MB BK	-	-
911401720672	ST030T LED12/850 14W 220-240V I NB BK	-	-
911401720682	ST030T LED12/850 14W 220-240V I MB BK	-	-
911401720692	ST030T LED20/850 23W 220-240V I NB BK	-	-
911401720702	ST030T LED20/850 23W 220-240V I MB BK	-	-
911401720712	ST030T LED30/850 35W 220-240V I NB BK	-	-
911401720722	ST030T LED30/850 35W 220-240V I MB BK	-	-

Initial Performance (IEC Compliant) (1/2)

Essential Smart Bright Projector

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
911401713892	ST030T LED8/830 8W 220-240V I NB WH CN	SDCM<5	3000 K	100 lm/W	800 lm
911401713902	ST030T LED8/840 8W 220-240V I NB WH CN	SDCM<5	4000 K	100 lm/W	800 lm
911401713912	ST030T LED8/830 8W 220-240V I MB WH CN	SDCM<5	3000 K	100 lm/W	800 lm
911401713922	ST030T LED8/840 8W 220-240V I MB WH CN	SDCM<5	4000 K	100 lm/W	800 lm
911401713932	ST030T LED12/830 14W 220-240V I NB WH CN	SDCM<5	3000 K	85.714 lm/W	1200 lm
911401713942	ST030T LED12/840 14W 220-240V I NB WH CN	SDCM<5	4000 K	85.714 lm/W	1200 lm
911401713952	ST030T LED12/830 14W 220-240V I MB WH CN	SDCM<5	3000 K	85.714 lm/W	1200 lm
911401713962	ST030T LED12/840 14W 220-240V I MB WH CN	SDCM<5	4000 K	85.714 lm/W	1200 lm
911401713972	ST030T LED20/830 23W 220-240V I NB WH CN	SDCM<5	3000 K	86.957 lm/W	2000 lm
911401713982	ST030T LED20/840 23W 220-240V I NB WH CN	SDCM<5	4000 K	86.957 lm/W	2000 lm
911401713992	ST030T LED20/830 23W 220-240V I MB WH CN	SDCM<5	3000 K	86.957 lm/W	2000 lm
911401714002	ST030T LED20/840 23W 220-240V I MB WH CN	SDCM<5	4000 K	86.957 lm/W	2000 lm
911401714012	ST030T LED30/830 35W	SDCM<5	3000 K	85.714 lm/W	3000 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
	220-240V I NB WH CN				
911401714022	ST030T LED30/840 35W 220-240V I NB WH CN	SDCM<5	4000 K	85.714 lm/W	3000 lm
911401714032	ST030T LED30/830 35W 220-240V I MB WH CN	SDCM<5	3000 K	85.714 lm/W	3000 lm
911401714042	ST030T LED30/840 35W 220-240V I MB WH CN	SDCM<5	4000 K	85.714 lm/W	3000 lm
911401714212	ST030T LED8/830 8W 220-240V I NB WH	SDCM<5	3000 K	100 lm/W	800 lm
911401714222	ST030T LED8/840 8W 220-240V I NB WH	SDCM<5	4000 K	100 lm/W	800 lm
911401714232	ST030T LED8/830 8W 220-240V I MB WH	SDCM<5	3000 K	100 lm/W	800 lm
911401714242	ST030T LED8/840 8W 220-240V I MB WH	SDCM<5	4000 K	100 lm/W	800 lm
911401714252	ST030T LED12/830 14W 220-240V I NB WH	SDCM<5	3000 K	85.714 lm/W	1200 lm
911401714262	ST030T LED12/840 14W 220-240V I NB WH	SDCM<5	4000 K	85.714 lm/W	1200 lm
911401714272	ST030T LED12/830 14W 220-240V I MB WH	SDCM<5	3000 K	85.714 lm/W	1200 lm
911401714282	ST030T LED12/840 14W 220-240V I MB WH	SDCM<5	4000 K	85.714 lm/W	1200 lm
911401714292	ST030T LED20/830 23W 220-240V I NB WH	SDCM<5	3000 K	86.957 lm/W	2000 lm

Essential Smart Bright Projector

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
911401714302	ST030T LED20/840 23W 220-240V I NB WH	SDCM<5	4000 K	86.957 lm/W	2000 lm
911401714312	ST030T LED20/830 23W 220-240V I MB WH	SDCM<5	3000 K	86.957 lm/W	2000 lm
911401714322	ST030T LED20/840 23W 220-240V I MB WH	SDCM<5	4000 K	86.957 lm/W	2000 lm
911401714332	ST030T LED30/830 35W 220-240V I NB WH	SDCM<5	3000 K	85.714 lm/W	3000 lm
911401714342	ST030T LED30/840 35W 220-240V I NB WH	SDCM<5	4000 K	85.714 lm/W	3000 lm
911401714352	ST030T LED30/830 35W 220-240V I MB WH	SDCM<5	3000 K	85.714 lm/W	3000 lm
911401714362	ST030T LED30/840 35W 220-240V I MB WH	SDCM<5	4000 K	85.714 lm/W	3000 lm
911401714532	ST030T LED6/830 6W UNV II NB WH TW	SDCM<5	3000 K	500 lm/W	3000 lm
911401714542	ST030T LED6/840 6W UNV II NB WH TW	SDCM<5	4000 K	100 lm/W	600 lm
911401714552	ST030T LED6/850 6W UNV II NB WH TW	SDCM<6	5000 K	100 lm/W	600 lm
911401714562	ST030T LED6/830 6W UNV II MB WH TW	SDCM<5	3000 K	100 lm/W	600 lm
911401714572	ST030T LED6/840 6W UNV II MB WH TW	SDCM<5	4000 K	100 lm/W	600 lm
911401714582	ST030T LED6/850 6W	SDCM<6	5000 K	100 lm/W	600 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
	UNV II MB WH TW				
911401714592	ST030T LED12/830 14W UNV II NB WH TW	SDCM<5	3000 K	85.714 lm/W	1200 lm
911401714602	ST030T LED12/840 14W UNV II NB WH TW	SDCM<5	4000 K	85.714 lm/W	1200 lm
911401714612	ST030T LED12/850 14W UNV II NB WH TW	SDCM<6	5000 K	85.714 lm/W	1200 lm
911401714622	ST030T LED12/830 14W UNV II MB WH TW	SDCM<5	3000 K	85.714 lm/W	1200 lm
911401714632	ST030T LED12/840 14W UNV II MB WH TW	SDCM<5	4000 K	85.714 lm/W	1200 lm
911401714642	ST030T LED12/850 14W UNV II MB WH TW	SDCM<6	5000 K	85.714 lm/W	1200 lm
911401714652	ST030T LED20/830 24W UNV II NB WH TW	SDCM<5	3000 K	83.333 lm/W	2000 lm
911401714662	ST030T LED20/840 24W UNV II NB WH TW	SDCM<5	4000 K	83.333 lm/W	2000 lm
911401714672	ST030T LED20/850 24W UNV II NB WH TW	SDCM<6	5000 K	83.333 lm/W	2000 lm
911401714682	ST030T LED20/830 24W UNV II MB WH TW	SDCM<5	3000 K	83.333 lm/W	2000 lm
911401714692	ST030T LED20/840 24W UNV II MB WH TW	SDCM<5	4000 K	83.333 lm/W	2000 lm
911401714702	ST030T LED20/850 24W UNV II MB WH TW	SDCM<6	5000 K	83.333 lm/W	2000 lm

Essential Smart Bright Projector

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
911401720412	ST030T LED8/850 8W 220-240V I NB WH CN	SDCM<6	5000 K	100 lm/W	800 lm
911401720422	ST030T LED8/850 8W 220-240V I MB WH CN	SDCM<6	5000 K	100 lm/W	800 lm
911401720432	ST030T LED12/850 14W 220-240V I NB WH CN	SDCM<6	5000 K	85.714 lm/W	1200 lm
911401720442	ST030T LED12/850 14W 220-240V I MB WH CN	SDCM<6	5000 K	85.714 lm/W	1200 lm
911401720452	ST030T LED20/850 23W 220-240V I NB WH CN	SDCM<6	5000 K	86.957 lm/W	2000 lm
911401720462	ST030T LED20/850 23W 220-240V I MB WH CN	SDCM<6	5000 K	86.957 lm/W	2000 lm
911401720472	ST030T LED30/850 35W 220-240V I NB WH CN	SDCM<6	5000 K	100 lm/W	3500 lm
911401720482	ST030T LED30/850 35W 220-240V I MB WH CN	SDCM<6	5000 K	100 lm/W	3500 lm
911401720572	ST030T LED8/850 8W 220-240V I NB WH	SDCM<6	5000 K	100 lm/W	800 lm
911401720582	ST030T LED8/850 8W 220-240V I MB WH	SDCM<6	5000 K	100 lm/W	800 lm
911401720592	ST030T LED12/850 14W 220-240V I NB WH	SDCM<6	5000 K	85.714 lm/W	1200 lm
911401720602	ST030T LED12/850 14W 220-240V I MB WH	SDCM<6	5000 K	85.714 lm/W	1200 lm
911401720612	ST030T LED20/850 23W	SDCM<6	5000 K	86.957 lm/W	2000 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
	220-240V I NB WH				
911401720622	ST030T LED20/850 23W 220-240V I MB WH	SDCM<6	5000 K	86.957 lm/W	2000 lm
911401720632	ST030T LED30/850 35W 220-240V I NB WH	SDCM<6	5000 K	100 lm/W	3500 lm
911401720642	ST030T LED30/850 35W 220-240V I MB WH	SDCM<6	5000 K	100 lm/W	3500 lm
911401714052	ST030T LED8/830 8W 220-240V I NB BK CN	SDCM<5	3000 K	100 lm/W	800 lm
911401714062	ST030T LED8/840 8W 220-240V I NB BK CN	SDCM<5	4000 K	100 lm/W	800 lm
911401714072	ST030T LED8/830 8W 220-240V I MB BK CN	SDCM<5	3000 K	100 lm/W	800 lm
911401714082	ST030T LED8/840 8W 220-240V I MB BK CN	SDCM<5	4000 K	100 lm/W	800 lm
911401714092	ST030T LED12/830 14W 220-240V I NB BK CN	SDCM<5	3000 K	85.714 lm/W	1200 lm
911401714102	ST030T LED12/840 14W 220-240V I NB BK CN	SDCM<5	4000 K	85.714 lm/W	1200 lm
911401714112	ST030T LED12/830 14W 220-240V I MB BK CN	SDCM<5	3000 K	85.714 lm/W	1200 lm
911401714122	ST030T LED12/840 14W 220-240V I MB BK CN	SDCM<5	4000 K	85.714 lm/W	1200 lm
911401714132	ST030T LED20/830 23W 220-240V I NB BK CN	SDCM<5	3000 K	86.957 lm/W	2000 lm

Essential Smart Bright Projector

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
911401714142	ST030T LED20/840 23W 220-240V I NB BK CN	SDCM<5	4000 K	86.957 lm/W	2000 lm
911401714152	ST030T LED20/830 23W 220-240V I MB BK CN	SDCM<5	3000 K	86.957 lm/W	2000 lm
911401714162	ST030T LED20/840 23W 220-240V I MB BK CN	SDCM<5	4000 K	86.957 lm/W	2000 lm
911401714172	ST030T LED30/830 35W 220-240V I NB BK CN	SDCM<5	3000 K	85.714 lm/W	3000 lm
911401714182	ST030T LED30/840 35W 220-240V I NB BK CN	SDCM<5	4000 K	85.714 lm/W	3000 lm
911401714192	ST030T LED30/830 35W 220-240V I MB BK CN	SDCM<5	3000 K	85.714 lm/W	3000 lm
911401714202	ST030T LED30/840 35W 220-240V I MB BK CN	SDCM<5	4000 K	85.714 lm/W	3000 lm
911401714372	ST030T LED8/830 8W 220-240V I NB BK	SDCM<5	3000 K	100 lm/W	800 lm
911401714382	ST030T LED8/840 8W 220-240V I NB BK	SDCM<5	4000 K	100 lm/W	800 lm
911401714392	ST030T LED8/830 8W 220-240V I MB BK	SDCM<5	3000 K	100 lm/W	800 lm
911401714402	ST030T LED8/840 8W 220-240V I MB BK	SDCM<5	4000 K	100 lm/W	800 lm
911401714412	ST030T LED12/830 14W 220-240V I NB BK	SDCM<5	3000 K	85.714 lm/W	1200 lm
911401714422	ST030T LED12/840 14W	SDCM<5	4000 K	85.714 lm/W	1200 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
	220-240V I NB BK				
911401714432	ST030T LED12/830 14W 220-240V I MB BK	SDCM<5	3000 K	85.714 lm/W	1200 lm
911401714452	ST030T LED20/830 23W 220-240V I NB BK	SDCM<5	3000 K	52.174 lm/W	1200 lm
911401714462	ST030T LED20/840 23W 220-240V I NB BK	SDCM<5	4000 K	86.957 lm/W	2000 lm
911401714472	ST030T LED20/830 23W 220-240V I MB BK	SDCM<5	3000 K	86.957 lm/W	2000 lm
911401714482	ST030T LED20/840 23W 220-240V I MB BK	SDCM<5	4000 K	86.957 lm/W	2000 lm
911401714492	ST030T LED30/830 35W 220-240V I NB BK	SDCM<5	3000 K	57.143 lm/W	2000 lm
911401714502	ST030T LED30/840 35W 220-240V I NB BK	SDCM<5	4000 K	85.714 lm/W	3000 lm
911401714512	ST030T LED30/830 35W 220-240V I MB BK	SDCM<5	3000 K	85.714 lm/W	3000 lm
911401714522	ST030T LED30/840 35W 220-240V I MB BK	SDCM<5	4000 K	85.714 lm/W	3000 lm
911401714712	ST030T LED6/830 6W UNV II NB BK TW	SDCM<5	3000 K	100 lm/W	600 lm
911401714722	ST030T LED6/840 6W UNV II NB BK TW	SDCM<5	4000 K	100 lm/W	600 lm
911401714732	ST030T LED6/850 6W UNV II NB BK TW	SDCM<6	5000 K	100 lm/W	600 lm
911401714742	ST030T LED6/830 6W UNV II MB BK TW	SDCM<5	3000 K	100 lm/W	600 lm

Essential Smart Bright Projector

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
911401714752	ST030T LED6/840 6W UNV II MB BK TW	SDCM<5	4000 K	100 lm/W	600 lm
911401714762	ST030T LED6/850 6W UNV II MB BK TW	SDCM<6	5000 K	100 lm/W	600 lm
911401714772	ST030T LED12/830 14W UNV II NB BK TW	SDCM<5	3000 K	85.714 lm/W	1200 lm
911401714782	ST030T LED12/840 14W UNV II NB BK TW	SDCM<5	4000 K	85.714 lm/W	1200 lm
911401714792	ST030T LED12/850 14W UNV II NB BK TW	SDCM<6	5000 K	85.714 lm/W	1200 lm
911401714802	ST030T LED12/830 14W UNV II MB BK TW	SDCM<5	3000 K	85.714 lm/W	1200 lm
911401714812	ST030T LED12/840 14W UNV II MB BK TW	SDCM<5	4000 K	85.714 lm/W	1200 lm
911401714822	ST030T LED12/850 14W UNV II MB BK TW	SDCM<6	5000 K	85.714 lm/W	1200 lm
911401714832	ST030T LED20/830 24W UNV II NB BK TW	SDCM<5	3000 K	83.333 lm/W	2000 lm
911401714842	ST030T LED20/840 24W UNV II NB BK TW	SDCM<5	4000 K	83.333 lm/W	2000 lm
911401714852	ST030T LED20/850 24W UNV II NB BK TW	SDCM<6	5000 K	83.333 lm/W	2000 lm
911401714862	ST030T LED20/830 24W UNV II MB BK TW	SDCM<5	3000 K	83.333 lm/W	2000 lm
911401714872	ST030T LED20/840 24W UNV II MB BK TW	SDCM<5	4000 K	83.333 lm/W	2000 lm
911401714882	ST030T LED20/850 24W UNV II MB BK TW	SDCM<6	5000 K	83.333 lm/W	2000 lm
911401720492	ST030T LED8/850 8W 220-240V I NB BK CN	SDCM<6	5000 K	100 lm/W	800 lm
911401720502	ST030T LED8/850 8W 220-240V I MB BK CN	SDCM<6	5000 K	100 lm/W	800 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
911401720512	ST030T LED12/850 14W 220-240V I NB BK CN	SDCM<6	5000 K	85.714 lm/W	1200 lm
911401720522	ST030T LED12/850 14W 220-240V I MB BK CN	SDCM<6	5000 K	85.714 lm/W	1200 lm
911401720532	ST030T LED20/850 23W 220-240V I NB BK CN	SDCM<6	5000 K	86.957 lm/W	2000 lm
911401720542	ST030T LED20/850 23W 220-240V I MB BK CN	SDCM<6	5000 K	86.957 lm/W	2000 lm
911401720552	ST030T LED30/850 35W 220-240V I NB BK CN	SDCM<6	5000 K	100 lm/W	3500 lm
911401720562	ST030T LED30/850 35W 220-240V I MB BK CN	SDCM<6	5000 K	100 lm/W	3500 lm
911401720652	ST030T LED8/850 8W 220-240V I NB BK	SDCM<6	5000 K	100 lm/W	800 lm
911401720662	ST030T LED8/850 8W 220-240V I MB BK	SDCM<6	5000 K	100 lm/W	800 lm
911401720672	ST030T LED12/850 14W 220-240V I NB BK	SDCM<6	5000 K	85.714 lm/W	1200 lm
911401720682	ST030T LED12/850 14W 220-240V I MB BK	SDCM<6	5000 K	85.714 lm/W	1200 lm
911401720692	ST030T LED20/850 23W 220-240V I NB BK	SDCM<6	5000 K	86.957 lm/W	2000 lm
911401720702	ST030T LED20/850 23W 220-240V I MB BK	SDCM<6	5000 K	86.957 lm/W	2000 lm
911401720712	ST030T LED30/850 35W	SDCM<6	5000 K	100 lm/W	3500 lm

Essential Smart Bright Projector

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
	220-240V I NB BK				
911401720722	ST030T LED30/850 35W	SDCM<6	5000 K	100 lm/W	3500 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
	220-240V I MB BK				

Initial Performance (IEC Compliant) (2/2)

Order Code	Full Product Name	Initial input power
911401713892	ST030T LED8/830 8W 220-240V I NB WH CN	8 W
911401713902	ST030T LED8/840 8W 220-240V I NB WH CN	8 W
911401713912	ST030T LED8/830 8W 220-240V I MB WH CN	8 W
911401713922	ST030T LED8/840 8W 220-240V I MB WH CN	8 W
911401713932	ST030T LED12/830 14W 220-240V I NB WH CN	14 W
911401713942	ST030T LED12/840 14W 220-240V I NB WH CN	14 W
911401713952	ST030T LED12/830 14W 220-240V I MB WH CN	14 W
911401713962	ST030T LED12/840 14W 220-240V I MB WH CN	14 W
911401713972	ST030T LED20/830 23W 220-240V I NB WH CN	23 W
911401713982	ST030T LED20/840 23W 220-240V I NB WH CN	23 W
911401713992	ST030T LED20/830 23W 220-240V I MB WH CN	23 W
911401714002	ST030T LED20/840 23W 220-240V I MB WH CN	23 W
911401714012	ST030T LED30/830 35W 220-240V I NB WH CN	35 W
911401714022	ST030T LED30/840 35W 220-240V I NB WH CN	35 W
911401714032	ST030T LED30/830 35W 220-240V I MB WH CN	35 W
911401714042	ST030T LED30/840 35W 220-240V I MB WH CN	35 W
911401714212	ST030T LED8/830 8W 220-240V I NB WH	8 W
911401714222	ST030T LED8/840 8W 220-240V I NB WH	8 W
911401714232	ST030T LED8/830 8W 220-240V I MB WH	8 W
911401714242	ST030T LED8/840 8W 220-240V I MB WH	8 W
911401714252	ST030T LED12/830 14W 220-240V I NB WH	14 W
911401714262	ST030T LED12/840 14W 220-240V I NB WH	14 W
911401714272	ST030T LED12/830 14W 220-240V I MB WH	14 W
911401714282	ST030T LED12/840 14W 220-240V I MB WH	14 W
911401714292	ST030T LED20/830 23W 220-240V I NB WH	23 W
911401714302	ST030T LED20/840 23W 220-240V I NB WH	23 W
911401714312	ST030T LED20/830 23W 220-240V I MB WH	23 W
911401714322	ST030T LED20/840 23W 220-240V I MB WH	23 W
911401714332	ST030T LED30/830 35W 220-240V I NB WH	35 W
911401714342	ST030T LED30/840 35W 220-240V I NB WH	35 W
911401714352	ST030T LED30/830 35W 220-240V I MB WH	35 W
911401714362	ST030T LED30/840 35W 220-240V I MB WH	35 W
911401714532	ST030T LED6/830 6W UNV II NB WH TW	6 W
911401714542	ST030T LED6/840 6W UNV II NB WH TW	6 W
911401714552	ST030T LED6/850 6W UNV II NB WH TW	6 W
911401714562	ST030T LED6/830 6W UNV II MB WH TW	6 W
911401714572	ST030T LED6/840 6W UNV II MB WH TW	6 W
911401714582	ST030T LED6/850 6W UNV II MB WH TW	6 W
911401714592	ST030T LED12/830 14W UNV II NB WH TW	14 W
911401714602	ST030T LED12/840 14W UNV II NB WH TW	14 W
911401714612	ST030T LED12/850 14W UNV II NB WH TW	14 W
911401714622	ST030T LED12/830 14W UNV II MB WH TW	14 W

Order Code	Full Product Name	Initial input power
911401714632	ST030T LED12/840 14W UNV II MB WH TW	14 W
911401714642	ST030T LED12/850 14W UNV II MB WH TW	14 W
911401714652	ST030T LED20/830 24W UNV II NB WH TW	24 W
911401714662	ST030T LED20/840 24W UNV II NB WH TW	24 W
911401714672	ST030T LED20/850 24W UNV II NB WH TW	24 W
911401714682	ST030T LED20/830 24W UNV II MB WH TW	24 W
911401714692	ST030T LED20/840 24W UNV II MB WH TW	24 W
911401714702	ST030T LED20/850 24W UNV II MB WH TW	24 W
911401720412	ST030T LED8/850 8W 220-240V I NB WH CN	8 W
911401720422	ST030T LED8/850 8W 220-240V I MB WH CN	8 W
911401720432	ST030T LED12/850 14W 220-240V I NB WH CN	14 W
911401720442	ST030T LED12/850 14W 220-240V I MB WH CN	14 W
911401720452	ST030T LED20/850 23W 220-240V I NB WH CN	23 W
911401720462	ST030T LED20/850 23W 220-240V I MB WH CN	23 W
911401720472	ST030T LED30/850 35W 220-240V I NB WH CN	35 W
911401720482	ST030T LED30/850 35W 220-240V I MB WH CN	35 W
911401720572	ST030T LED8/850 8W 220-240V I NB WH	8 W
911401720582	ST030T LED8/850 8W 220-240V I MB WH	8 W
911401720592	ST030T LED12/850 14W 220-240V I NB WH	14 W
911401720602	ST030T LED12/850 14W 220-240V I MB WH	14 W
911401720612	ST030T LED20/850 23W 220-240V I NB WH	23 W
911401720622	ST030T LED20/850 23W 220-240V I MB WH	23 W
911401720632	ST030T LED30/850 35W 220-240V I NB WH	35 W
911401720642	ST030T LED30/850 35W 220-240V I MB WH	35 W
911401714052	ST030T LED8/830 8W 220-240V I NB BK CN	8 W
911401714062	ST030T LED8/840 8W 220-240V I NB BK CN	8 W
911401714072	ST030T LED8/830 8W 220-240V I MB BK CN	8 W
911401714082	ST030T LED8/840 8W 220-240V I MB BK CN	8 W
911401714092	ST030T LED12/830 14W 220-240V I NB BK CN	14 W
911401714102	ST030T LED12/840 14W 220-240V I NB BK CN	14 W
911401714112	ST030T LED12/830 14W 220-240V I MB BK CN	14 W
911401714122	ST030T LED12/840 14W 220-240V I MB BK CN	14 W
911401714132	ST030T LED20/830 23W 220-240V I NB BK CN	23 W
911401714142	ST030T LED20/840 23W 220-240V I NB BK CN	23 W
911401714152	ST030T LED20/830 23W 220-240V I MB BK CN	23 W
911401714162	ST030T LED20/840 23W 220-240V I MB BK CN	23 W
911401714172	ST030T LED30/830 35W 220-240V I NB BK CN	35 W
911401714182	ST030T LED30/840 35W 220-240V I NB BK CN	35 W
911401714192	ST030T LED30/830 35W 220-240V I MB BK CN	35 W
911401714202	ST030T LED30/840 35W 220-240V I MB BK CN	35 W
911401714372	ST030T LED8/830 8W 220-240V I NB BK	8 W
911401714382	ST030T LED8/840 8W 220-240V I NB BK	8 W

Essential Smart Bright Projector

Order Code	Full Product Name	Initial input power
911401714392	STO30T LED8/830 8W 220-240V I MB BK	8 W
911401714402	STO30T LED8/840 8W 220-240V I MB BK	8 W
911401714412	STO30T LED12/830 14W 220-240V I NB BK	14 W
911401714422	STO30T LED12/840 14W 220-240V I NB BK	14 W
911401714432	STO30T LED12/830 14W 220-240V I MB BK	14 W
911401714452	STO30T LED20/830 23W 220-240V I NB BK	23 W
911401714462	STO30T LED20/840 23W 220-240V I NB BK	23 W
911401714472	STO30T LED20/830 23W 220-240V I MB BK	23 W
911401714482	STO30T LED20/840 23W 220-240V I MB BK	23 W
911401714492	STO30T LED30/830 35W 220-240V I NB BK	35 W
911401714502	STO30T LED30/840 35W 220-240V I NB BK	35 W
911401714512	STO30T LED30/830 35W 220-240V I MB BK	35 W
911401714522	STO30T LED30/840 35W 220-240V I MB BK	35 W
911401714712	STO30T LED6/830 6W UNV II NB BK TW	6 W
911401714722	STO30T LED6/840 6W UNV II NB BK TW	6 W
911401714732	STO30T LED6/850 6W UNV II NB BK TW	6 W
911401714742	STO30T LED6/830 6W UNV II MB BK TW	6 W
911401714752	STO30T LED6/840 6W UNV II MB BK TW	6 W
911401714762	STO30T LED6/850 6W UNV II MB BK TW	6 W
911401714772	STO30T LED12/830 14W UNV II NB BK TW	14 W
911401714782	STO30T LED12/840 14W UNV II NB BK TW	14 W
911401714792	STO30T LED12/850 14W UNV II NB BK TW	14 W
911401714802	STO30T LED12/830 14W UNV II MB BK TW	14 W
911401714812	STO30T LED12/840 14W UNV II MB BK TW	14 W

Order Code	Full Product Name	Initial input power
911401714822	STO30T LED12/850 14W UNV II MB BK TW	14 W
911401714832	STO30T LED20/830 24W UNV II NB BK TW	24 W
911401714842	STO30T LED20/840 24W UNV II NB BK TW	24 W
911401714852	STO30T LED20/850 24W UNV II NB BK TW	24 W
911401714862	STO30T LED20/830 24W UNV II MB BK TW	24 W
911401714872	STO30T LED20/840 24W UNV II MB BK TW	24 W
911401714882	STO30T LED20/850 24W UNV II MB BK TW	24 W
911401720492	STO30T LED8/850 8W 220-240V I NB BK CN	8 W
911401720502	STO30T LED8/850 8W 220-240V I MB BK CN	8 W
911401720512	STO30T LED12/850 14W 220-240V I NB BK CN	14 W
911401720522	STO30T LED12/850 14W 220-240V I MB BK CN	14 W
911401720532	STO30T LED20/850 23W 220-240V I NB BK CN	23 W
911401720542	STO30T LED20/850 23W 220-240V I MB BK CN	23 W
911401720552	STO30T LED30/850 35W 220-240V I NB BK CN	35 W
911401720562	STO30T LED30/850 35W 220-240V I MB BK CN	35 W
911401720652	STO30T LED8/850 8W 220-240V I NB BK	8 W
911401720662	STO30T LED8/850 8W 220-240V I MB BK	8 W
911401720672	STO30T LED12/850 14W 220-240V I NB BK	14 W
911401720682	STO30T LED12/850 14W 220-240V I MB BK	14 W
911401720692	STO30T LED20/850 23W 220-240V I NB BK	23 W
911401720702	STO30T LED20/850 23W 220-240V I MB BK	23 W
911401720712	STO30T LED30/850 35W 220-240V I NB BK	35 W
911401720722	STO30T LED30/850 35W 220-240V I MB BK	35 W

Mechanical and Housing

Order Code	Full Product Name	Color
911401713892	STO30T LED8/830 8W 220-240V I NB WH CN	White
911401713902	STO30T LED8/840 8W 220-240V I NB WH CN	White
911401713912	STO30T LED8/830 8W 220-240V I MB WH CN	White
911401713922	STO30T LED8/840 8W 220-240V I MB WH CN	White
911401713932	STO30T LED12/830 14W 220-240V I NB WH CN	White
911401713942	STO30T LED12/840 14W 220-240V I NB WH CN	White
911401713952	STO30T LED12/830 14W 220-240V I MB WH CN	White
911401713962	STO30T LED12/840 14W 220-240V I MB WH CN	White
911401713972	STO30T LED20/830 23W 220-240V I NB WH CN	White
911401713982	STO30T LED20/840 23W 220-240V I NB WH CN	White
911401713992	STO30T LED20/830 23W 220-240V I MB WH CN	White
911401714002	STO30T LED20/840 23W 220-240V I MB WH CN	White
911401714012	STO30T LED30/830 35W 220-240V I NB WH CN	White
911401714022	STO30T LED30/840 35W 220-240V I NB WH CN	White
911401714032	STO30T LED30/830 35W 220-240V I MB WH CN	White
911401714042	STO30T LED30/840 35W 220-240V I MB WH CN	White
911401714212	STO30T LED8/830 8W 220-240V I NB WH	White
911401714222	STO30T LED8/840 8W 220-240V I NB WH	White
911401714232	STO30T LED8/830 8W 220-240V I MB WH	White
911401714242	STO30T LED8/840 8W 220-240V I MB WH	White
911401714252	STO30T LED12/830 14W 220-240V I NB WH	White
911401714262	STO30T LED12/840 14W 220-240V I NB WH	White
911401714272	STO30T LED12/830 14W 220-240V I MB WH	White
911401714282	STO30T LED12/840 14W 220-240V I MB WH	White

Order Code	Full Product Name	Color
911401714292	STO30T LED20/830 23W 220-240V I NB WH	White
911401714302	STO30T LED20/840 23W 220-240V I NB WH	White
911401714312	STO30T LED20/830 23W 220-240V I MB WH	White
911401714322	STO30T LED20/840 23W 220-240V I MB WH	White
911401714332	STO30T LED30/830 35W 220-240V I NB WH	White
911401714342	STO30T LED30/840 35W 220-240V I NB WH	White
911401714352	STO30T LED30/830 35W 220-240V I MB WH	White
911401714362	STO30T LED30/840 35W 220-240V I MB WH	White
911401714532	STO30T LED6/830 6W UNV II NB WH TW	White
911401714542	STO30T LED6/840 6W UNV II NB WH TW	White
911401714552	STO30T LED6/850 6W UNV II NB WH TW	White
911401714562	STO30T LED6/830 6W UNV II MB WH TW	White
911401714572	STO30T LED6/840 6W UNV II MB WH TW	White
911401714582	STO30T LED6/850 6W UNV II MB WH TW	White
911401714592	STO30T LED12/830 14W UNV II NB WH TW	White
911401714602	STO30T LED12/840 14W UNV II NB WH TW	White
911401714612	STO30T LED12/850 14W UNV II NB WH TW	White
911401714622	STO30T LED12/830 14W UNV II MB WH TW	White
911401714632	STO30T LED12/840 14W UNV II MB WH TW	White
911401714642	STO30T LED12/850 14W UNV II MB WH TW	White
911401714652	STO30T LED20/830 24W UNV II NB WH TW	White
911401714662	STO30T LED20/840 24W UNV II NB WH TW	White
911401714672	STO30T LED20/850 24W UNV II NB WH TW	White
911401714682	STO30T LED20/830 24W UNV II MB WH TW	White

Essential Smart Bright Projector

Order Code	Full Product Name	Color	Order Code	Full Product Name	Color
911401714692	ST030T LED20/840 24W UNV II MB WH TW	White	911401714462	ST030T LED20/840 23W 220-240V I NB BK	black
911401714702	ST030T LED20/850 24W UNV II MB WH TW	White	911401714472	ST030T LED20/830 23W 220-240V I MB BK	black
911401720412	ST030T LED8/850 8W 220-240V I NB WH CN	White	911401714482	ST030T LED20/840 23W 220-240V I MB BK	black
911401720422	ST030T LED8/850 8W 220-240V I MB WH CN	White	911401714492	ST030T LED30/830 35W 220-240V I NB BK	black
911401720432	ST030T LED12/850 14W 220-240V I NB WH CN	White	911401714502	ST030T LED30/840 35W 220-240V I NB BK	black
911401720442	ST030T LED12/850 14W 220-240V I MB WH CN	White	911401714512	ST030T LED30/830 35W 220-240V I MB BK	black
911401720452	ST030T LED20/850 23W 220-240V I NB WH CN	White	911401714522	ST030T LED30/840 35W 220-240V I MB BK	black
911401720462	ST030T LED20/850 23W 220-240V I MB WH CN	White	911401714712	ST030T LED6/830 6W UNV II NB BK TW	black
911401720472	ST030T LED30/850 35W 220-240V I NB WH CN	White	911401714722	ST030T LED6/840 6W UNV II NB BK TW	black
911401720482	ST030T LED30/850 35W 220-240V I MB WH CN	White	911401714732	ST030T LED6/850 6W UNV II NB BK TW	black
911401720572	ST030T LED8/850 8W 220-240V I NB WH	White	911401714742	ST030T LED6/830 6W UNV II MB BK TW	black
911401720582	ST030T LED8/850 8W 220-240V I MB WH	White	911401714752	ST030T LED6/840 6W UNV II MB BK TW	black
911401720592	ST030T LED12/850 14W 220-240V I NB WH	White	911401714762	ST030T LED6/850 6W UNV II MB BK TW	black
911401720602	ST030T LED12/850 14W 220-240V I MB WH	White	911401714772	ST030T LED12/830 14W UNV II NB BK TW	black
911401720612	ST030T LED20/850 23W 220-240V I NB WH	White	911401714782	ST030T LED12/840 14W UNV II NB BK TW	black
911401720622	ST030T LED20/850 23W 220-240V I MB WH	White	911401714792	ST030T LED12/850 14W UNV II NB BK TW	black
911401720632	ST030T LED30/850 35W 220-240V I NB WH	White	911401714802	ST030T LED12/830 14W UNV II MB BK TW	black
911401720642	ST030T LED30/850 35W 220-240V I MB WH	White	911401714812	ST030T LED12/840 14W UNV II MB BK TW	black
911401714052	ST030T LED8/830 8W 220-240V I NB BK CN	black	911401714822	ST030T LED12/850 14W UNV II MB BK TW	black
911401714062	ST030T LED8/840 8W 220-240V I NB BK CN	black	911401714832	ST030T LED20/830 24W UNV II NB BK TW	black
911401714072	ST030T LED8/830 8W 220-240V I MB BK CN	black	911401714842	ST030T LED20/840 24W UNV II NB BK TW	black
911401714082	ST030T LED8/840 8W 220-240V I MB BK CN	black	911401714852	ST030T LED20/850 24W UNV II NB BK TW	black
911401714092	ST030T LED12/830 14W 220-240V I NB BK CN	black	911401714862	ST030T LED20/830 24W UNV II MB BK TW	black
911401714102	ST030T LED12/840 14W 220-240V I NB BK CN	black	911401714872	ST030T LED20/840 24W UNV II MB BK TW	black
911401714112	ST030T LED12/830 14W 220-240V I MB BK CN	black	911401714882	ST030T LED20/850 24W UNV II MB BK TW	black
911401714122	ST030T LED12/840 14W 220-240V I MB BK CN	black	911401720492	ST030T LED8/850 8W 220-240V I NB BK CN	black
911401714132	ST030T LED20/830 23W 220-240V I NB BK CN	black	911401720502	ST030T LED8/850 8W 220-240V I MB BK CN	black
911401714142	ST030T LED20/840 23W 220-240V I NB BK CN	black	911401720512	ST030T LED12/850 14W 220-240V I NB BK CN	black
911401714152	ST030T LED20/830 23W 220-240V I MB BK CN	black	911401720522	ST030T LED12/850 14W 220-240V I MB BK CN	black
911401714162	ST030T LED20/840 23W 220-240V I MB BK CN	black	911401720532	ST030T LED20/850 23W 220-240V I NB BK CN	black
911401714172	ST030T LED30/830 35W 220-240V I NB BK CN	black	911401720542	ST030T LED20/850 23W 220-240V I MB BK CN	black
911401714182	ST030T LED30/840 35W 220-240V I NB BK CN	black	911401720552	ST030T LED30/850 35W 220-240V I NB BK CN	black
911401714192	ST030T LED30/830 35W 220-240V I MB BK CN	black	911401720562	ST030T LED30/850 35W 220-240V I MB BK CN	black
911401714202	ST030T LED30/840 35W 220-240V I MB BK CN	black	911401720652	ST030T LED8/850 8W 220-240V I NB BK	black
911401714372	ST030T LED8/830 8W 220-240V I NB BK	black	911401720662	ST030T LED8/850 8W 220-240V I MB BK	black
911401714382	ST030T LED8/840 8W 220-240V I NB BK	black	911401720672	ST030T LED12/850 14W 220-240V I NB BK	black
911401714392	ST030T LED8/830 8W 220-240V I MB BK	black	911401720682	ST030T LED12/850 14W 220-240V I MB BK	black
911401714402	ST030T LED8/840 8W 220-240V I MB BK	black	911401720692	ST030T LED20/850 23W 220-240V I NB BK	black
911401714412	ST030T LED12/830 14W 220-240V I NB BK	black	911401720702	ST030T LED20/850 23W 220-240V I MB BK	black
911401714422	ST030T LED12/840 14W 220-240V I NB BK	black	911401720712	ST030T LED30/850 35W 220-240V I NB BK	black
911401714432	ST030T LED12/830 14W 220-240V I MB BK	black	911401720722	ST030T LED30/850 35W 220-240V I MB BK	black
911401714452	ST030T LED20/830 23W 220-240V I NB BK	black			

Essential Smart Bright Projector

