



# Affordability and energy savings - all in one lamp

## CorePro LED PL 4pin 2pin

The CorePro LED Type A - Ballast Driven (Plug and Play) InstantFit CFL-ni is a great LED solution suitable for replacing both 2-pin and 4-pin CFL fluorescent lamps, using an existing ballast. Both vertical and horizontal options are available with the horizontal version having a rotatable end cap to ensure the light is correctly aimed.

### Benefits

- Offers lowest cost of installation and easiest upgrade fluorescent CFL's to LED technology
- Dimmable product available for additional savings
- Reliable performance - color and lumen maintenance with excellent lighting uniformity

### Features

- Average life rating of 50,000 hours with unmatched ballast compatibility
- Shatter-resistant polycarbonate construction
- Philips proprietary safety features
- DLC, NSF and RoHS listed
- Conventional form factor to fit into existing luminaires

### Application

- Office & Industrial
- Residential & Retail
- Hospitality & Healthcare


# CorePro LED PL 4pin 2pin

## Versions



G24q/GX24q

## Dimensional drawing



Product	D1	D2	A1	A2	A3
10.5PL-C/T LED/26V-3000 IF	24.3 mm	29 mm	99.9 mm	109.9 mm	125.5 mm
4P 10/1					

