



Affordable simple installation, no hidden costs and maximum install/maintenance savings

CorePro LEDtube MainsFit T8

Philips CorePro MainsFit (UL Type-B) T8 LED lamps use a double-ended design which significantly simplifies installation, saving installation time and costs. This ballast bypass product replaces either T8 or T12 lamps in fixtures containing shunted or non-shunted G13 (medium bi-pin) lamp holders for over 40% energy savings.

Benefits

- Reliable performance - color and lumen maintenance
- Double-ended design installs in about half the time as single-ended type-B solutions
- Reduces lighting complexity - integrated driver

Features

- Operates on both shunted and non-shunted sockets, which means no need to replace sockets
- DLC, NSF and RoHS listed
- Philips proprietary safety features
- Available shatter-resistant polycarbonate construction
- 5-year warranty and 50,000-hour life standard

CorePro LEDtube MainsFit T8

Application


- Office and Retail
- Industrial and warehouses
- Parking lots and covered car parks

Versions



G13 Medium Bi-Pin Fluorescent

Dimensional drawing



Product	D	A1	A2	A3
16.5T8/COR/48-840/MF21/G/347V 25/1	26 mm	1199.4 mm	1206.5 mm	1213.6 mm
16.5T8/COR/48-850/MF21/G/347V 25/1	26 mm	1199.4 mm	1206.5 mm	1213.6 mm
16.5T8/COR/48-835/MF20/G/347V 25/1	26 mm	1199.4 mm	1206.5 mm	1213.6 mm

A3

Product	D1	D2	A1	A2	A3
14T8PRO/48-835/BB17/G 10/1 FB	25.7 mm	28 mm	1198 mm	1205 mm	1212 mm
14T8PRO/48-830/BB17/G 10/1 FB	25.7 mm	28 mm	1198 mm	1205 mm	1212 mm
16.5T8PRO/48-835/BB20/G 10/1 FB	25.7 mm	26 mm	1200 mm	1207 mm	1214 mm

CorePro LEDtube MainsFit T8

Controls and Dimming	
Dimmable	No
Operating and Electrical	
Input Frequency	50 to 60 Hz
Starting Time (Nom)	0.5 s
General Information	
Cap-Base	G13
Nominal Lifetime (Nom)	50000 h
Rated Lifetime (Hours)	50000 h
Switching Cycle	50000X
Light Technical	
Beam Angle (Nom)	240 °
Color Rendering Index (Nom)	80
Llmf At End Of Nominal Lifetime (Nom)	70 %
Rated Beam Angle	240 °
Temperature	
T-Ambient (Max)	45 °C
T-Ambient (Min)	-20 °C
T-Storage (Min)	-40 °C

Operating and Electrical

Order Code	Full Product Name	Voltage (Nom)	Power (Rated) (Nom)
471755	16.5T8PRO/48-835/BB20/G 10/1 FB	120-277 V	16.5 W
477315	14T8PRO/48-830/BB17/G 10/1 FB	120-277 V	14 W
477323	14T8PRO/48-835/BB17/G 10/1 FB	120-277 V	14 W
554675	16.5T8/COR/48-835/MF20/G/347V 25/1	347 V	16.5 W
554683	16.5T8/COR/48-840/MF21/G/347V 25/1	347 V	16.5 W
554691	16.5T8/COR/48-850/MF21/G/347V 25/1	347 V	16.5 W

Light Technical

Order Code	Full Product Name	Color Code	Correlated Color	Luminous Flux (Nom)	Luminous Flux (Rated) (Nom)
			Temperature (Nom)		
471755	16.5T8PRO/48-835/BB20/G 10/1 FB	835	3500 K	2000 lm	2000 lm
477315	14T8PRO/48-830/BB17/G 10/1 FB	830	3000 K	1700 lm	1700 lm
477323	14T8PRO/48-835/BB17/G 10/1 FB	835	3500 K	1700 lm	1700 lm
554675	16.5T8/COR/48-835/MF20/G/347V 25/1	835	3500 K	2000 lm	2000 lm

Order Code	Full Product Name	Color Code	Correlated Color	Luminous Flux (Nom)	Luminous Flux (Rated) (Nom)
			Temperature (Nom)		
554683	16.5T8/COR/48-840/MF21/G/347V 25/1	841	4000 K	2100 lm	2100 lm
554691	16.5T8/COR/48-850/MF21/G/347V 25/1	850	5000 K	2100 lm	2100 lm

Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)	T-Storage (Max)
471755	16.5T8PRO/48-835/BB20/G 10/1 FB	70 °C	65 °C
477315	14T8PRO/48-830/BB17/G 10/1 FB	70 °C	65 °C
477323	14T8PRO/48-835/BB17/G 10/1 FB	70 °C	65 °C
554675	16.5T8/COR/48-835/MF20/G/347V 25/1	55 °C	85 °C
554683	16.5T8/COR/48-840/MF21/G/347V 25/1	55 °C	85 °C

Order Code	Full Product Name	T-Case Maximum (Nom)	T-Storage (Max)
554691	16.5T8/COR/48-850/MF21/G/347V 25/1	55 °C	85 °C

CorePro LEDtube MainsFit T8

