



The best compatibility and energy savings - all in one lamp

MasterClass LEDtube InstantFit T5

The Masterclass LED Type A - Ballast Driven (Plug and Play) InstantFit TLED is a great LED solution suitable for replacing T5 fluorescent lamps, using an existing ballast.

Benefits

- Offers lowest cost of installation and easiest upgrade fluorescent T8's to LED lighting technology
- True T5 size fits conventional applications
- 2ft and 3ft lamps operate on both HE and HO ballasts

Features

- Average life rating of 50,000 hours
- Philips proprietary safety features
- DLC, NSF and RoHS listed
- Available shatter-resistant polycarbonate construction

Application

- Office and Retail
- Industrial and warehouses
- Parking lots and covered car parks


MasterClass LEDtube InstantFit T5

Versions



G5

Dimensional drawing



Product	D1	D2	A1	A2	A3
24T5HO/46-830/ IF33/P/DIM 10/1	15.2 mm	17.8 mm	1147.8 mm	1154.9 mm	1162 mm

