



The best compatibility and energy savings - all in one lamp

MasterClass LEDtube InstantFit T8

The Masterclass LED Type A - Ballast Driven (Plug and Play) InstantFit TLED is a great LED solution suitable for replacing T8 fluorescent lamps, using an existing ballast. Specific lamps can also be used on Philips Xitanium driver for Type C applications.

Benefits

- Offers lowest cost of installation and easiest upgrade fluorescent T8's to LED lighting technology
- Dimmable product available for additional savings
- Reliable performance - color and lumen maintenance

Features


- Average life rating of 50,000 hours, with specific lamps up to 70,000 hours
- Compatibility with over 200 ballasts and drivers
- Philips proprietary safety features
- DLC, NSF and RoHS listed
- Available shatter-resistant polycarbonate construction

Application

- Office and Retail
- Industrial and warehouses
- Parking lots and covered car parks

MasterClass LEDtube InstantFit T8

Versions




G13

FA8

G13


G13



G13

MasterClass LEDtube InstantFit T8


Dimensional drawing



Product	D1	D2	A1	A2	A3
15.5T8/MAS/48-830/IF23/P 25/1	25.7 mm	28 mm	1198.1 mm	1205.2 mm	1212.3 mm
16.5T8 LED/48-3500 IF 10/1 UHO	25.68 mm	28 mm	1198 mm	1205 mm	1212 mm
10T8 LED/48-3000 IF 1PK 10/1	25.7 mm	26.3 mm	1198.1 mm	1205.2 mm	1212.3 mm
10T8 LED/48-4000 IF 1PK 10/1	25.7 mm	26.3 mm	1198.1 mm	1205.2 mm	1212.3 mm
10T8 LED/48-3500 IF 1PK 10/1	25.7 mm	26.3 mm	1198.1 mm	1205.2 mm	1212.3 mm
10T8 LED/48-2700 IF 1PK 10/1	25.7 mm	26.3 mm	1198.1 mm	1205.2 mm	1212.3 mm
13T8 LED/48-4000 IF DIM 1PK 10/1	25.7 mm	26.3 mm	1198.1 mm	1205.2 mm	1212.3 mm
13T8 LED/48-3500 IF DIM 1PK 10/1	25.7 mm	26.3 mm	1198.1 mm	1205.2 mm	1212.3 mm
13T8 LED/48-3000 IF DIM 1PK 10/1	25.7 mm	26.3 mm	1198.1 mm	1205.2 mm	1212.3 mm
13T8 LED/48-5000 IF DIM 1PK 10/1	25.7 mm	26.3 mm	1198.1 mm	1205.2 mm	1212.3 mm
9T8 LED/36-5000 IF 10/1	25.7 mm	26.3 mm	893.4 mm	900.5 mm	907.6 mm
7T8 LED/24-4000 IF 10/1	25.7 mm	26.3 mm	588.6 mm	595.7 mm	602.8 mm
9T8 LED/36-3500 IF 10/1	25.7 mm	26.3 mm	893.4 mm	900.5 mm	907.6 mm
7T8 LED/24-5000 IF 10/1	25.7 mm	26.3 mm	588.6 mm	595.7 mm	602.8 mm
7T8 LED/24-3500 IF 10/1	25.7 mm	26.3 mm	588.6 mm	595.7 mm	602.8 mm
7T8 LED/24-3000 IF 10/1	25.7 mm	26.3 mm	588.6 mm	595.7 mm	602.8 mm
9T8 LED/36-4000 IF 10/1	25.7 mm	26.3 mm	893.4 mm	900.5 mm	907.6 mm
9T8 LED/36-3000 IF 10/1	25.7 mm	26.3 mm	893.4 mm	900.5 mm	907.6 mm
16.5T8 LED/48-3000 IF 10/1 UHO	25.68 mm	28 mm	1198 mm	1205 mm	1212 mm
16.5T8 LED/48-5000 IF 10/1 UHO	25.68 mm	28 mm	1198 mm	1205 mm	1212 mm

MasterClass LEDtube InstantFit T8

Dimensional drawing



Product	D1	D2	B	A1	D
13T8 LED/24-4000 IF-6U 10/1	25.7 mm	28 mm	152 mm	570 mm	27.8 mm
13T8 LED/24-5000 IF-6U 10/1	25.7 mm	28 mm	152 mm	570 mm	27.8 mm
13T8 LED/24-3000 IF-6U 10/1	25.7 mm	28 mm	152 mm	570 mm	27.8 mm
13T8 LED/24-3500 IF-6U 10/1	25.7 mm	28 mm	152 mm	570 mm	27.8 mm

Product	D	A1	A2	A3
35T8/96-6500 IF FA8 10/1	27.9 mm	2366.9 mm	2375.2 mm	2383.5 mm
35T8/96-3000 IF FA8 10/1	27.9 mm	2366.9 mm	2375.2 mm	2383.5 mm

General Information

Switching Cycle 50000X

Light Technical

Llmf At End Of Nominal Lifetime (Nom) 70 %

Temperature

T-Storage (Max) 65 °C

T-Storage (Min) -40 °C

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h	Energy Efficiency Label (EEL)
929001226704	16.5T8 LED/48-3500 IF 10/1 UHO	20 kWh	A+
929001226904	16.5T8 LED/48-5000 IF 10/1 UHO	20 kWh	A+
929001304404	16.5T8 LED/48-3000 IF 10/1 UHO	20 kWh	-
929001307704	35T8/96-3000 IF FA8 10/1	-	-
929001314704	35T8/96-6500 IF FA8 10/1	-	-
929001310804	7T8 LED/24-3000 IF 10/1	-	Not applicable
929001310904	7T8 LED/24-3500 IF 10/1	-	-
929001311004	7T8 LED/24-4000 IF 10/1	-	-
929001311104	7T8 LED/24-5000 IF 10/1	-	-
929001311304	9T8 LED/36-3000 IF 10/1	-	Not applicable
929001311404	9T8 LED/36-3500 IF 10/1	-	Not applicable

Order Code	Full Product Name	Energy Consumption kWh/1000 h	Energy Efficiency Label (EEL)
929001311504	9T8 LED/36-4000 IF 10/1	-	Not applicable
929001311604	9T8 LED/36-5000 IF 10/1	-	Not applicable
929001311804	13T8 LED/24-3000 IF-6U 10/1	-	-
929001311904	13T8 LED/24-3500 IF-6U 10/1	-	-
929001312004	13T8 LED/24-4000 IF-6U 10/1	-	-
929001312104	13T8 LED/24-5000 IF-6U 10/1	-	-
929001397104	10T8 LED/48-2700 IF 1PK 10/1	-	-
929001397204	10T8 LED/48-3000 IF 1PK 10/1	-	-
929001397304	10T8 LED/48-3500 IF 1PK 10/1	-	-
929001397404	10T8 LED/48-4000 IF 1PK 10/1	-	-

MasterClass LEDtube InstantFit T8

Order Code	Full Product Name	Energy Consumption kWh/1000 h	Energy Efficiency Label (EEL)
929001397604	13T8 LED/48-3000 IF DIM 1PK 10/1	-	-
929001397704	13T8 LED/48-3500 IF DIM 1PK 10/1	-	-
929001397804	13T8 LED/48-4000 IF DIM 1PK 10/1	-	-

Controls and Dimming

Order Code	Full Product Name	Dimmable
929001226704	16.5T8 LED/48-3500 IF 10/1 UHO	No
929001226904	16.5T8 LED/48-5000 IF 10/1 UHO	No
929001304404	16.5T8 LED/48-3000 IF 10/1 UHO	No
929001307704	35T8/96-3000 IF FA8 10/1	No
929001314704	35T8/96-6500 IF FA8 10/1	No
929001310804	7T8 LED/24-3000 IF 10/1	No
929001310904	7T8 LED/24-3500 IF 10/1	No
929001311004	7T8 LED/24-4000 IF 10/1	No
929001311104	7T8 LED/24-5000 IF 10/1	No
929001311304	9T8 LED/36-3000 IF 10/1	No
929001311404	9T8 LED/36-3500 IF 10/1	No
929001311504	9T8 LED/36-4000 IF 10/1	No
929001311604	9T8 LED/36-5000 IF 10/1	No

Operating and Electrical

Order Code	Full Product Name	Voltage (Nom)	Power (Rated) (Nom)	Starting Time (Nom)
929001226704	16.5T8 LED/48-3500 IF 10/1 UHO	50 to 60 Hz	120-277 V	16.5 W -
929001226904	16.5T8 LED/48-5000 IF 10/1 UHO	50 to 60 Hz	120-277 V	16.5 W 0.5 s
929001304404	16.5T8 LED/48-3000 IF 10/1 UHO	50 to 60 Hz	120-277, 347 V	16.5 W 0.5 s
929001307704	35T8/96-3000 IF FA8 10/1	50000-64000 Hz	280-410 V	35 W -
929001314704	35T8/96-6500 IF FA8 10/1	50000-64000 Hz	280-410 V	35 W -
929001310804	7T8 LED/24-3000 IF 10/1	20000-120000 Hz	120-277, 347 V	7 W 0.5 s
929001310904	7T8 LED/24-3500 IF 10/1	20000-120000 Hz	120-277, 347 V	7 W 0.5 s
929001311004	7T8 LED/24-4000 IF 10/1	20000-120000 Hz	120-277, 347 V	7 W 0.5 s
929001311104	7T8 LED/24-5000 IF 10/1	20000-120000 Hz	120-277, 347 V	7 W 0.5 s

Order Code	Full Product Name	Energy Consumption kWh/1000 h	Energy Efficiency Label (EEL)
929001397904	13T8 LED/48-5000 IF DIM 1PK 10/1	-	-
929002016204	15.5T8/MAS/48-830/IF23/P 25/1	-	-

Order Code	Full Product Name	Dimmable
929001311804	13T8 LED/24-3000 IF-6U 10/1	No
929001311904	13T8 LED/24-3500 IF-6U 10/1	No
929001312004	13T8 LED/24-4000 IF-6U 10/1	No
929001312104	13T8 LED/24-5000 IF-6U 10/1	No
929001397104	10T8 LED/48-2700 IF 1PK 10/1	No
929001397204	10T8 LED/48-3000 IF 1PK 10/1	No
929001397304	10T8 LED/48-3500 IF 1PK 10/1	No
929001397404	10T8 LED/48-4000 IF 1PK 10/1	No
929001397604	13T8 LED/48-3000 IF DIM 1PK 10/1	Yes
929001397704	13T8 LED/48-3500 IF DIM 1PK 10/1	Yes
929001397804	13T8 LED/48-4000 IF DIM 1PK 10/1	Yes
929001397904	13T8 LED/48-5000 IF DIM 1PK 10/1	Yes
929002016204	15.5T8/MAS/48-830/IF23/P 25/1	No

Order Code	Full Product Name	Voltage (Nom)	Power (Rated) (Nom)	Starting Time (Nom)
929001311304	9T8 LED/36-3000 IF 10/1	20000-120000 Hz	120-277, 347 V	9 W 0.5 s
929001311404	9T8 LED/36-3500 IF 10/1	20000-120000 Hz	120-277, 347 V	9 W 0.5 s
929001311504	9T8 LED/36-4000 IF 10/1	20000-120000 Hz	120-277, 347 V	9 W 0.5 s
929001311604	9T8 LED/36-5000 IF 10/1	20000-120000 Hz	120-277, 347 V	9 W 0.5 s
929001311804	13T8 LED/24-3000 IF-6U 10/1	20000-120000 Hz	120-277, 347 V	13 W 0.5 s
929001311904	13T8 LED/24-3500 IF-6U 10/1	20000-120000 Hz	120-277, 347 V	13 W 0.5 s
929001312004	13T8 LED/24-4000 IF-6U 10/1	20000-120000 Hz	120-277, 347 V	13 W 0.5 s
929001312104	13T8 LED/24-5000 IF-6U 10/1	20000-120000 Hz	120-277, 347 V	13 W 0.5 s

MasterClass LEDtube InstantFit T8

	Full Product		Voltage	Power	Starting
Order Code	Name	Input Frequency	(Nom)	(Rated) (Nom)	Time (Nom)
929001397104	10T8 LED/ 48-2700 IF 1PK 10/1	20000-120000 Hz	120-277V; 347 V	10 W	0.5 s
929001397204	10T8 LED/ 48-3000 IF 1PK 10/1	20000-120000 Hz	120-277V; 347 V	10 W	0.5 s
929001397304	10T8 LED/ 48-3500 IF 1PK 10/1	20000-120000 Hz	120-277V; 347 V	10 W	0.5 s
929001397404	10T8 LED/ 48-4000 IF 1PK 10/1	20000-120000 Hz	120-277V; 347 V	10 W	0.5 s
929001397604	13T8 LED/ 48-3000 IF DIM 1PK 10/1	20000-120000 Hz	120-277V; 347 V	13 W	0.5 s

	Full Product		Voltage	Power	Starting
Order Code	Name	Input Frequency	(Nom)	(Rated) (Nom)	Time (Nom)
929001397704	13T8 LED/ 48-3500 IF DIM 1PK 10/1	20000-120000 Hz	120-277V; 347 V	13 W	0.5 s
929001397804	13T8 LED/ 48-4000 IF DIM 1PK 10/1	20000-120000 Hz	120-277V; 347 V	13 W	0.5 s
929001397904	13T8 LED/ 48-5000 IF DIM 1PK 10/1	20000-120000 Hz	120-277V; 347 V	13 W	0.5 s
929002016204	15.5T8/MAS/ 48-830/IF23/P 25/1	50 to 60 Hz	120-277 V	15.5 W	0.5 s

General Information

		Cap-	Nominal	Rated
Order Code	Full Product Name	Base	Lifetime (Nom)	Lifetime (Hours)
929001226704	16.5T8 LED/48-3500 IF 10/1 UHO	G13	70000 h	70000 h
929001226904	16.5T8 LED/48-5000 IF 10/1 UHO	G13	70000 h	70000 h
929001304404	16.5T8 LED/48-3000 IF 10/1 UHO	G13	70000 h	70000 h
929001307704	35T8/96-3000 IF FA8 10/1	FA8	50000 h	50000 h
929001314704	35T8/96-6500 IF FA8 10/1	FA8	50000 h	50000 h
929001310804	7T8 LED/24-3000 IF 10/1	G13	50000 h	50000 h
929001310904	7T8 LED/24-3500 IF 10/1	G13	50000 h	50000 h
929001311004	7T8 LED/24-4000 IF 10/1	G13	50000 h	50000 h
929001311104	7T8 LED/24-5000 IF 10/1	G13	50000 h	50000 h
929001311304	9T8 LED/36-3000 IF 10/1	G13	50000 h	50000 h
929001311404	9T8 LED/36-3500 IF 10/1	G13	50000 h	50000 h
929001311504	9T8 LED/36-4000 IF 10/1	G13	50000 h	50000 h
929001311604	9T8 LED/36-5000 IF 10/1	G13	50000 h	50000 h
929001311804	13T8 LED/24-3000 IF-6U 10/1	G13	50000 h	50000 h
929001311904	13T8 LED/24-3500 IF-6U 10/1	G13	50000 h	50000 h

		Cap-	Nominal	Rated
Order Code	Full Product Name	Base	Lifetime (Nom)	Lifetime (Hours)
929001312004	13T8 LED/24-4000 IF-6U 10/1	G13	50000 h	50000 h
929001312104	13T8 LED/24-5000 IF-6U 10/1	G13	50000 h	50000 h
929001397104	10T8 LED/48-2700 IF 1PK 10/1	G13	70000 h	70000 h
929001397204	10T8 LED/48-3000 IF 1PK 10/1	G13	70000 h	70000 h
929001397304	10T8 LED/48-3500 IF 1PK 10/1	G13	70000 h	70000 h
929001397404	10T8 LED/48-4000 IF 1PK 10/1	G13	70000 h	70000 h
929001397604	13T8 LED/48-3000 IF DIM 1PK 10/1	G13	70000 h	70000 h
929001397704	13T8 LED/48-3500 IF DIM 1PK 10/1	G13	70000 h	70000 h
929001397804	13T8 LED/48-4000 IF DIM 1PK 10/1	G13	70000 h	70000 h
929001397904	13T8 LED/48-5000 IF DIM 1PK 10/1	G13	70000 h	70000 h
929002016204	15.5T8/MAS/48-830/IF23/P 25/1	G13	70000 h	70000 h

Light Technical (1/2)

		Beam						
Order Code	Full Product Name	Angle (Max)	Beam Angle (Nom)	Color Code	Correlated Color Temperature (Nom)	Color Rendering Index (Nom)	Luminous Flux (Nom)	Luminous Flux (Rated) (Nom)
929001226704	16.5T8 LED/48-3500 IF 10/1 UHO	-	-	835	3500 K	82	2400 lm	2400 lm
929001226904	16.5T8 LED/48-5000 IF 10/1 UHO	-	160 °	850	5000 K	82	2500 lm	2500 lm
929001304404	16.5T8 LED/48-3000 IF 10/1 UHO	160 °	160 °	830	3000 K	82	2300 lm	2300 lm
929001307704	35T8/96-3000 IF FA8 10/1	-	-	830	3000 K	82	3900 lm	3900 lm

MasterClass LEDtube InstantFit T8

Order Code	Full Product Name	Beam	Beam Angle (Nom)	Color Code	Correlated Color Temperature (Nom)	Color Rendering Index (Nom)	Luminous Flux (Nom)	Luminous Flux (Rated) (Nom)
		Angle (Max)						
929001314704	35T8/96-6500 IF FA8 10/1	-	-	865	6500 K	82	4200 lm	4200 lm
929001310804	7T8 LED/24-3000 IF 10/1	-	-	830	3000 K	82	1050 lm	1050 lm
929001310904	7T8 LED/24-3500 IF 10/1	-	-	835	3500 K	82	1050 lm	1050 lm
929001311004	7T8 LED/24-4000 IF 10/1	-	-	840	4000 K	82	1150 lm	1150 lm
929001311104	7T8 LED/24-5000 IF 10/1	-	-	850	5000 K	82	1150 lm	1150 lm
929001311304	9T8 LED/36-3000 IF 10/1	-	-	830	3000 K	82	1100 lm	1100 lm
929001311404	9T8 LED/36-3500 IF 10/1	-	-	835	3500 K	82	1100 lm	1100 lm
929001311504	9T8 LED/36-4000 IF 10/1	-	-	840	4000 K	82	1200 lm	1200 lm
929001311604	9T8 LED/36-5000 IF 10/1	-	-	850	5000 K	82	1200 lm	1200 lm
929001311804	13T8 LED/24-3000 IF-6U 10/1	-	-	830	3000 K	82	2000 lm	2000 lm
929001311904	13T8 LED/24-3500 IF-6U 10/1	-	-	835	3500 K	82	2000 lm	2000 lm
929001312004	13T8 LED/24-4000 IF-6U 10/1	-	-	840	4000 K	82	2100 lm	2100 lm
929001312104	13T8 LED/24-5000 IF-6U 10/1	-	-	850	5000 K	82	2100 lm	2100 lm
929001397104	10T8 LED/48-2700 IF 1PK 10/1	-	-	827	2700 K	82	1400 lm	1400 lm
929001397204	10T8 LED/48-3000 IF 1PK 10/1	-	-	830	3000 K	82	1500 lm	1500 lm
929001397304	10T8 LED/48-3500 IF 1PK 10/1	-	-	835	3500 K	82	1500 lm	1500 lm
929001397404	10T8 LED/48-4000 IF 1PK 10/1	-	-	840	4000 K	82	1600 lm	1600 lm
929001397604	13T8 LED/48-3000 IF DIM 1PK 10/1	-	-	830	3000 K	82	2000 lm	2000 lm
929001397704	13T8 LED/48-3500 IF DIM 1PK 10/1	-	-	835	3500 K	82	2000 lm	2000 lm
929001397804	13T8 LED/48-4000 IF DIM 1PK 10/1	-	-	840	4000 K	82	2100 lm	2100 lm
929001397904	13T8 LED/48-5000 IF DIM 1PK 10/1	-	-	850	5000 K	82	2100 lm	2100 lm
929002016204	15.5T8/MAS/48-830/IF23/P 25/1	-	180 °	830	3000 K	80	2300 lm	2300 lm

Light Technical (2/2)







Order Code	Full Product Name	Rated Beam Angle	Order Code	Full Product Name	Rated Beam Angle
929001226704	16.5T8 LED/48-3500 IF 10/1 UHO	-	929001311804	13T8 LED/24-3000 IF-6U 10/1	-
929001226904	16.5T8 LED/48-5000 IF 10/1 UHO	160 °	929001311904	13T8 LED/24-3500 IF-6U 10/1	-
929001304404	16.5T8 LED/48-3000 IF 10/1 UHO	160 °	929001312004	13T8 LED/24-4000 IF-6U 10/1	-
929001307704	35T8/96-3000 IF FA8 10/1	-	929001312104	13T8 LED/24-5000 IF-6U 10/1	-
929001314704	35T8/96-6500 IF FA8 10/1	-	929001397104	10T8 LED/48-2700 IF 1PK 10/1	-
929001310804	7T8 LED/24-3000 IF 10/1	-	929001397204	10T8 LED/48-3000 IF 1PK 10/1	-
929001310904	7T8 LED/24-3500 IF 10/1	-	929001397304	10T8 LED/48-3500 IF 1PK 10/1	-
929001311004	7T8 LED/24-4000 IF 10/1	-	929001397404	10T8 LED/48-4000 IF 1PK 10/1	-
929001311104	7T8 LED/24-5000 IF 10/1	-	929001397604	13T8 LED/48-3000 IF DIM 1PK 10/1	-
929001311304	9T8 LED/36-3000 IF 10/1	-	929001397704	13T8 LED/48-3500 IF DIM 1PK 10/1	-
929001311404	9T8 LED/36-3500 IF 10/1	-	929001397804	13T8 LED/48-4000 IF DIM 1PK 10/1	-
929001311504	9T8 LED/36-4000 IF 10/1	-	929001397904	13T8 LED/48-5000 IF DIM 1PK 10/1	-
929001311604	9T8 LED/36-5000 IF 10/1	-	929002016204	15.5T8/MAS/48-830/IF23/P 25/1	180 °

Temperature

Order Code	Full Product Name	T-Case			Order Code	Full Product Name	T-Case		
		T-Ambient (Max)	T-Ambient (Min)	Maximum (Nom)			T-Ambient (Max)	T-Ambient (Min)	Maximum (Nom)
929001226704	16.5T8 LED/48-3500 IF 10/1 UHO	-	-	45 °C	929001304404	16.5T8 LED/48-3000 IF 10/1 UHO	55 °C	-20 °C	45 °C
929001226904	16.5T8 LED/48-5000 IF 10/1 UHO	-	-	45 °C	929001307704	35T8/96-3000 IF FA8 10/1	-	-	-
					929001314704	35T8/96-6500 IF FA8 10/1	-	-	-

MasterClass LEDtube InstantFit T8

Order Code	Full Product Name	T-Ambient (Max)	T-Ambient (Min)	T-Case Maximum (Nom)
929001310804	7T8 LED/24-3000 IF 10/1	45 °C	-20 °C	50 °C
929001310904	7T8 LED/24-3500 IF 10/1	45 °C	-20 °C	50 °C
929001311004	7T8 LED/24-4000 IF 10/1	45 °C	-20 °C	50 °C
929001311104	7T8 LED/24-5000 IF 10/1	45 °C	-20 °C	50 °C
929001311304	9T8 LED/36-3000 IF 10/1	45 °C	-20 °C	50 °C
929001311404	9T8 LED/36-3500 IF 10/1	45 °C	-20 °C	50 °C
929001311504	9T8 LED/36-4000 IF 10/1	45 °C	-20 °C	50 °C
929001311604	9T8 LED/36-5000 IF 10/1	45 °C	-20 °C	50 °C
929001311804	13T8 LED/24-3000 IF-6U 10/1	45 °C	-20 °C	50 °C
929001311904	13T8 LED/24-3500 IF-6U 10/1	45 °C	-20 °C	50 °C
929001312004	13T8 LED/24-4000 IF-6U 10/1	45 °C	-20 °C	50 °C
929001312104	13T8 LED/24-5000 IF-6U 10/1	45 °C	-20 °C	50 °C
929001397104	10T8 LED/48-2700 IF 1PK 10/1	45 °C	-20 °C	50 °C
929001397204	10T8 LED/48-3000 IF 1PK 10/1	45 °C	-20 °C	50 °C
929001397304	10T8 LED/48-3500 IF 1PK 10/1	45 °C	-20 °C	50 °C
929001397404	10T8 LED/48-4000 IF 1PK 10/1	45 °C	-20 °C	50 °C
929001397604	13T8 LED/48-3000 IF DIM 1PK 10/1	45 °C	-20 °C	50 °C
929001397704	13T8 LED/48-3500 IF DIM 1PK 10/1	45 °C	-20 °C	50 °C
929001397804	13T8 LED/48-4000 IF DIM 1PK 10/1	45 °C	-20 °C	50 °C
929001397904	13T8 LED/48-5000 IF DIM 1PK 10/1	45 °C	-20 °C	50 °C
929002016204	15.5T8/MAS/48-830/ IF23/P 25/1	55 °C	-20 °C	50 °C



MasterClass LEDtube InstantFit T8

