



For every project where light really matters: reliable and easy to install

Coreline Highbay Gen4

CoreLine Highbay Gen4 delivers on the CoreLine promise of innovative, easy-to-use and high-quality luminaires. A reliable, highly efficient luminaire with a very long-lifetime, it delivers great savings on energy and requires less maintenance. At the same time, CoreLine Highbay is very easy to handle. The luminaire can be installed on your existing grid and the electrical connection is a straightforward task, with no need to open the luminaire and an external IP65 connector. With a choice of two beam angles: narrow and wide beam, you can adjust your lighting plan to suit your exact needs. This range also includes Interact Ready luminaires with integrated wireless communications and integrated movement and daylight sensors. So CoreLine Highbay Gen4 is ready to be used with any Interact connected lighting system.

Benefits

- Saves on energy and maintenance costs
- Easy installation thanks to single suspension hook and external connector, with additional mounting bracket for more flexibility
- Ideal for general application projects, with a robust design and a high water and dust-proof rating (IP65)

Coreline Highbay Gen4

Features

- High efficiency of up to 145 lm/W
- Long service lifetime of 50 K hrs at L80
- A single-point mounting system for ease of installation
- Low glare rating and colour rendering of ≥ 80
- Suitable for replacement of 250 W/400 W conventional lamps

Application

- General manufacturing
- Warehouses and logistical centres
- High-ceilinged lounges
- Exhibition halls

