



A TLED solution for your application

T8

Our TLEDs are available in InstantFit (Type A / Type C) or MainsFit (Ballast bypass / Type B) versions. The InstantFit lamps work on a broad variety of ballasts and LED drivers. Only InstantFit has over 15,000 lamp & ballast combinations delivering even light output, energy savings and a long lifetime. Our MainsFit products feature a double-ended design, simplifying installation while a proprietary safety circuit minimizes a shock risk. Lamp sizes range from 2-foot to 8-foot and U-bend with a variety of lumen outputs.

Benefits

- Minimizes overall lighting costs
- Offers cheapest and easiest upgrade to LED lighting technology
- Excellent compatibility with existing ballasts

Features

- InstantFit works with over 350 ballasts and drivers
- Lifetime of up to 70,000 hours & a limited warranty of up to 7-years
- Plug-and-play, ballast bypass or UL Type C options available
- Shatter-resistant, polycarbonate tubes available
- All T8 replacement TLEDs are NSF certified and most are DLC certified


Application

- Office and Shopping
- Industrial and warehouses
- Parking lots and covered car parks

Versions



FA8



G13



2G13 Tube, double-ended Frosted



G13




Medium Bi-Pin Fluorescent Tube,
double-ended Frosted



Medium Bi-Pin Fluorescent Tube,
double-ended Frosted



Medium Bi-Pin Fluorescent Tube,
double-ended Frosted




Medium Bi-Pin Fluorescent Tube,
double-ended Frosted



FA8



Medium Bi-Pin Fluorescent Tube,
double-ended Frosted



Medium Bi-Pin Fluorescent Tube,
double-ended Frosted




G13




Medium Bi-Pin Fluorescent Tube,
double-ended Frosted



Medium Bi-Pin Fluorescent Tube,
double-ended Frosted



FA8 Tube, double-ended Frosted




R17d (RDC) Tube, double-ended
Frosted



Medium Bi-Pin Fluorescent Tube,
double-ended Frosted


Dimensional drawing



Product	D1	D2	A1	A2	A3
14.5T8/COR/48-5CCT/ MF18/G/DIM 25/1	25.7 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm
14T8/COR/48-840/ IF21/G/DIM 10/1	25.7 mm	28 mm	1198 mm	1205 mm	1212 mm
14T8/COR/48-850/ IF21/G/DIM 10/1	25.7 mm	28 mm	1198 mm	1205 mm	1212 mm
14T8/COR/48-830/ IF20/G/DIM 10/1	25.7 mm	28 mm	1198 mm	1205 mm	1212 mm
14T8/COR/48-835/ IF20/G/DIM 10/1	25.7 mm	28 mm	1198 mm	1205 mm	1212 mm
12T8/COR/48-840/MF18/G 10/1	25.7 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm
12T8/COR/48-835/MF17/G 10/1	25.7 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm
9.9T8/COR/48-840/ MF16/G 10/1	25.7 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm
12T8/COR/48-830/MF17/G 10/1	25.7 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm
9.9T8/COR/48-835/ MF15/G 10/1	25.7 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm
9.9T8/COR/48-850/ MF16/G 10/1	25.7 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm
14.5T8/COR/48-830/ MF20/G 10/1	25.7 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm
14.5T8/COR/48-850/ MF21/G 10/1	25.7 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm
12T8/COR/48-850/MF18/G 10/1	25.7 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm
14.5T8/COR/48-840/ MF21/G 10/1	25.7 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm
14.5T8/COR/48-835/ MF20/G 10/1	25.7 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm
16.5T8/CNG/48-840/ MF21/G 25/1	25.7 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm
16.5T8/CNG/48-835/ MF20/G 25/1	25.7 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm
16.5T8/CNG/48-850/ MF21/G 25/1	25.7 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm
14.5T8/CNG/48-840/ MF18/G 25/1	25.7 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm
14.5T8/CNG/48-835/ MF17/G 25/1	25.7 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm
14.5T8/CNG/48-865/ MF18/G 25/1	25.7 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm
14.5T8/CNG/48-850/ MF18/G 25/1	25.7 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm
9.9T8/COR/48-850/ MF16/G/DIM 25/1	25.7 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm
12T8/COR/48-830/ MF17/G/DIM 25/1	25.7 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm

Dimensional drawing



Product	D1	D2	A1	A2	A3
12T8/COR/48-835/ MF17/G/DIM 25/1	25.7 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm
12T8/COR/48-840/ MF18/G/DIM 25/1	25.7 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm
9.9T8/COR/48-835/ MF15/G/DIM 25/1	25.7 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm
9.9T8/COR/48-840/ MF16/G/DIM 25/1	25.7 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm
12T8/COR/48-850/ MF18/G/DIM 25/1	25.7 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm



Product	D1	D2	A1	A2	A3
15.5T8/MAS/48-830/ IF23/P/DIM 25/1	25.7 mm	28 mm	1198.1 mm	1205.2 mm	1212.3 mm
8.5T8/MAS/36-830/ IF13/P/DIM 10/1	25.7 mm	26.3 mm	893.4 mm	900.5 mm	907.6 mm
8.5T8/MAS/36-840/ IF14/P/DIM 10/1	25.7 mm	26.3 mm	893.4 mm	900.5 mm	907.6 mm
7T8/MAS/24-830/ IF10/P/DIM 10/1	25.7 mm	26.3 mm	588.6 mm	595.7 mm	602.8 mm
8.5T8/MAS/36-850/ IF14/P/DIM 10/1	25.7 mm	26.3 mm	893.4 mm	900.5 mm	907.6 mm
8.5T8/MAS/36-835/ IF13/P/DIM 10/1	25.7 mm	26.3 mm	893.4 mm	900.5 mm	907.6 mm
7T8/MAS/24-835/ IF10/P/DIM 10/1	25.7 mm	26.3 mm	588.6 mm	595.7 mm	602.8 mm
7T8/MAS/24-840/ IF11/P/DIM 10/1	25.7 mm	26.3 mm	588.6 mm	595.7 mm	602.8 mm
7T8/MAS/24-850/ IF11/P/DIM 10/1	25.7 mm	26.3 mm	588.6 mm	595.7 mm	602.8 mm
8.9T8/MAS/48-830/ IF15/P/DIM 10/1	25.7 mm	26.3 mm	1198.1 mm	1205.2 mm	1212.3 mm
8.9T8/MAS/48-850/ IF16/P/DIM 10/1	25.7 mm	26.3 mm	1198.1 mm	1205.2 mm	1212.3 mm
8.9T8/MAS/48-835/ IF15/P/DIM 10/1	25.7 mm	26.3 mm	1198.1 mm	1205.2 mm	1212.3 mm
8.9T8/MAS/48-840/ IF16/P/DIM 10/1	25.7 mm	26.3 mm	1198.1 mm	1205.2 mm	1212.3 mm
13T8/MAS/48-850/ IF21/P/DIM 10/1	25.7 mm	26.3 mm	1198.1 mm	1205.2 mm	1212.3 mm
13T8/MAS/48-835/ IF20/P/DIM 10/1	25.7 mm	26.3 mm	1198.1 mm	1205.2 mm	1212.3 mm
13T8/MAS/48-840/ IF21/P/DIM 10/1	25.7 mm	26.3 mm	1198.1 mm	1205.2 mm	1212.3 mm
13T8/MAS/48-830/ IF20/P/DIM 10/1	25.7 mm	26.3 mm	1198.1 mm	1205.2 mm	1212.3 mm
15.5T8/MAS/48-850/ IF25/P/DIM 25/1	25.7 mm	28 mm	1198.1 mm	1205.2 mm	1212.3 mm

Dimensional drawing

Product	D1	D2	A1	A2	A3
15.5T8/MAS/48-835/ IF24/P/DIM 25/1	25.7 mm	28 mm	1198.1 mm	1205.2 mm	1212.3 mm
15.5T8/MAS/48-840/ IF25/P/DIM 25/1	25.7 mm	28 mm	1198.1 mm	1205.2 mm	1212.3 mm






Product	D1	D2	A1	A2	A3
12.5T8/COR/48-850/ FF18/G/DIM 25/1	25.7 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm
12.5T8/COR/48-840/ FF18/G/DIM 25/1	25.7 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm
12.5T8/COR/48-835/ FF17/G/DIM 25/1	25.7 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm
14.5T8/MAS/48-835/ MF20/P 10/1	25.7 mm	28 mm	1198 mm	1205 mm	1212 mm
10.5T8/MAS/48-835/ MF15/P/DIM 25/1	25.7 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm
10.5T8/MAS/48-840/ MF16/P/DIM 25/1	25.7 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm
14.5T8/MAS/48-835/ MF20/P/DIM 25/1	25.7 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm
14.5T8/MAS/48-830/ MF20/P/DIM 25/1	25.7 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm
10.5T8/MAS/48-850/ MF16/P/DIM 25/1	25.7 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm
14.5T8/MAS/48-840/ MF21/P/DIM 25/1	25.7 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm
16.5T8/MAS/48-835/ MF24/P/DIM 25/1	25.7 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm
14.5T8/MAS/48-850/ MF21/P/DIM 25/1	25.7 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm
16.5T8/MAS/48-840/ MF25/P/DIM 25/1	25.7 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm
16.5T8/MAS/48-850/ MF25/P/DIM 25/1	25.7 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm

Product	D	A1	A2	A3
11.5T8/COR/36-850/ MF14/G 10/1	25.9 mm	894.3 mm	900.5 mm	908.8 mm
11.5T8/COR/36-835/ MF13/G 10/1	25.9 mm	894.3 mm	900.5 mm	908.8 mm
11.5T8/COR/36-830/ MF13/G 10/1	25.9 mm	894.3 mm	900.5 mm	908.8 mm
8.5T8/COR/24-850/ MF11/G 10/1	25.9 mm	589.5 mm	595.7 mm	604 mm
11.5T8/COR/36-840/ MF14/G 10/1	25.9 mm	894.3 mm	900.5 mm	908.8 mm
8.5T8/COR/24-835/ MF11/G 10/1	25.9 mm	589.5 mm	595.7 mm	604 mm

Dimensional drawing

Product	D	A1	A2	A3
8.5T8/COR/24-830/ MF11/G 10/1	25.9 mm	589.5 mm	595.7 mm	604 mm
8.5T8/COR/24-840/ MF11/G 10/1	25.9 mm	589.5 mm	595.7 mm	604 mm
15T8/COR/48-835/ MF20/G/120-347V 25/1	25.7 mm	29 mm	1198.2 mm	1205.3 mm 1212.4 mm
15T8/COR/48-840/ MF21/G/120-347V 25/1	25.7 mm	29 mm	1198.2 mm	1205.3 mm 1212.4 mm
15T8/COR/48-850/ MF21/G/120-347V 25/1	25.7 mm	29 mm	1198.2 mm	1205.3 mm 1212.4 mm






Product	D1	D2	B	A1	D
15.5T8-6U/COR/24-830/ MF20/G 10/1	25.7 mm	28.1 mm	152 mm	570 mm	27.9 mm
15.5T8-6U/COR/24-840/MF21/G 10/1	25.7 mm	28.1 mm	152 mm	570 mm	27.9 mm
15.5T8-6U/COR/24-835/ MF20/G 10/1	25.7 mm	28.1 mm	152 mm	570 mm	27.9 mm
15.5T8-6U/COR/24-850/MF21/G 10/1	25.7 mm	28.1 mm	152 mm	570 mm	27.9 mm

Product	D1	D2	A1	A2	A3
13T8-6U/MAS/24-850/ IF21/P/DIM 10/1	25.7 mm	28 mm	152 mm	570 mm	27.8 mm
13T8-6U/MAS/24-830/ IF20/P/DIM 10/1	25.7 mm	28 mm	152 mm	570 mm	27.8 mm
13T8-6U/MAS/24-840/ IF21/P/DIM 10/1	25.7 mm	28 mm	152 mm	570 mm	27.8 mm
13T8-6U/MAS/24-835/ IF20/P/DIM 10/1	25.7 mm	28 mm	152 mm	570 mm	27.8 mm

Product	D2	A1	A2	A3
42T8HO/COR/96-840/ MF54/G/FA8 10/1	27.9 mm	2369.8 mm	2378.7 mm	2387.8 mm
33T8/COR/96-840/ MF44/G/FA8 10/1	27.9 mm	2369.8 mm	2378.7 mm	2387.8 mm
42T8HO/COR/96-850/ MF54/G/FA8 10/1	27.9 mm	2369.8 mm	2378.7 mm	2387.8 mm
33T8/COR/96-850/ MF44/G/FA8 10/1	27.9 mm	2369.8 mm	2378.7 mm	2387.8 mm

Dimensional drawing



Product	D2	A1	A2	A3
42T8HO/COR/96-840/ MF54/G/R17d 10/1	27.9 mm	2369.8 mm	2378.7 mm	2385.3 mm
42T8HO/COR/96-850/ MF54/G/R17d 10/1	27.9 mm	2369.8 mm	2378.7 mm	2385.3 mm

Product	D	A1	A2	A3	
35T8/96-3500 IF FA8	27.9	2366.9	2375.2	2383.5	
10/1	mm	mm	mm	mm	
35T8/96-4000 IF FA8	27.9	2366.9	2375.2	2383.5	
10/1	mm	mm	mm	mm	
30T8/COR/96-835/ IF39/G/FA8 10/1	25.5	28 mm	2366.9	2375.8	2384.7
	mm		mm	mm	mm
30T8/COR/96-840/ IF42/G/FA8 10/1	25.5	28 mm	2366.9	2375.8	2384.7
	mm		mm	mm	mm
30T8/COR/96-850/ IF42/G/FA8 10/1	25.5	28 mm	2366.9	2375.8	2384.7
	mm		mm	mm	mm

Product	D1	D2	A1	A2	A3
16T8/LED/48-840/IF18/G 25/1	25.7 mm	28 mm	1198 mm	1205 mm	1212 mm
16T8/LED/48-850/IF18/G 25/1	25.7 mm	28 mm	1198 mm	1205 mm	1212 mm
10T8/COR/48-835/ IF15/G/DIM 10/1	25.7 mm	28 mm	1198.1 mm	1205.2 mm	1212.3 mm
10T8/COR/48-850/ IF16/G/DIM 10/1	25.7 mm	28 mm	1198.1 mm	1205.2 mm	1212.3 mm
10T8/COR/48-840/ IF16/G/DIM 10/1	25.7 mm	28 mm	1198.1 mm	1205.2 mm	1212.3 mm
10T8/COR/48-830/ IF15/G/DIM 10/1	25.7 mm	28 mm	1198.1 mm	1205.2 mm	1212.3 mm

Light technical

Llmf At End Of Nominal Lifetime	70 %
(Nom)	

Mechanical and housing

Bulb Finish	Frosted
Bulb Shape	Tube, double-ended

Temperature

T-Ambient (Min)	-20 °C
T-Storage (Max)	65 °C
T-Storage (Min)	-40 °C

Approval and application

Order Code	Full Product Name	Energy Consumption kWh/ 1000 h
469247	35T8/96-3500 IF FA8 10/1	- kWh
469254	35T8/96-4000 IF FA8 10/1	- kWh
470096	14T8/COR/48-830/IF20/G/DIM 10/1	- kWh
470104	14T8/COR/48-835/IF20/G/DIM 10/1	- kWh
470112	14T8/COR/48-840/IF21/G/DIM 10/1	- kWh
470120	14T8/COR/48-850/IF21/G/DIM 10/1	- kWh
553230	10T8/COR/48-840/IF16/G/DIM 10/1	- kWh
553248	10T8/COR/48-850/IF16/G/DIM 10/1	- kWh
553214	10T8/COR/48-830/IF15/G/DIM 10/1	- kWh
553222	10T8/COR/48-835/IF15/G/DIM 10/1	- kWh
473926	13T8/MAS/48-830/IF20/P/DIM 10/1	- kWh
473934	13T8/MAS/48-835/IF20/P/DIM 10/1	- kWh
473942	13T8/MAS/48-840/IF21/P/DIM 10/1	- kWh
473958	13T8/MAS/48-850/IF21/P/DIM 10/1	- kWh
545178	15.5T8/MAS/48-830/IF23/P/DIM 25/1	- kWh
533372	15.5T8/MAS/48-835/IF24/P/DIM 25/1	- kWh
545194	15.5T8/MAS/48-840/IF25/P/DIM 25/1	- kWh
545200	15.5T8/MAS/48-850/IF25/P/DIM 25/1	- kWh
565580	8.9T8/MAS/48-830/IF15/P/DIM 10/1	- kWh
565598	8.9T8/MAS/48-835/IF15/P/DIM 10/1	- kWh
565606	8.9T8/MAS/48-840/IF16/P/DIM 10/1	- kWh
565614	8.9T8/MAS/48-850/IF16/P/DIM 10/1	- kWh
533018	30T8/COR/96-835/IF39/G/FA8 10/1	- kWh
533026	30T8/COR/96-840/IF42/G/FA8 10/1	- kWh
533034	30T8/COR/96-850/IF42/G/FA8 10/1	- kWh
535450	8.5T8/COR/24-830/MF11/G 10/1	- kWh
535468	8.5T8/COR/24-835/MF11/G 10/1	- kWh
535476	8.5T8/COR/24-840/MF11/G 10/1	- kWh
535484	8.5T8/COR/24-850/MF11/G 10/1	- kWh
535492	11.5T8/COR/36-830/MF13/G 10/1	- kWh
535500	11.5T8/COR/36-835/MF13/G 10/1	- kWh
535518	11.5T8/COR/36-840/MF14/G 10/1	- kWh
535526	11.5T8/COR/36-850/MF14/G 10/1	- kWh
535534	15.5T8-6U/COR/24-830/MF20/G 10/1	- kWh
535542	15.5T8-6U/COR/24-835/MF20/G 10/1	- kWh

Order Code	Full Product Name	Energy Consumption kWh/ 1000 h
535559	15.5T8-6U/COR/24-840/MF21/G 10/1	- kWh
535567	15.5T8-6U/COR/24-850/MF21/G 10/1	- kWh
542084	16T8/LED/48-840/IF18/G 25/1	- kWh
542092	16T8/LED/48-850/IF18/G 25/1	- kWh
539858	8.5T8/MAS/36-830/IF13/P/DIM 10/1	- kWh
539874	8.5T8/MAS/36-840/IF14/P/DIM 10/1	- kWh
539882	8.5T8/MAS/36-850/IF14/P/DIM 10/1	- kWh
539866	8.5T8/MAS/36-835/IF13/P/DIM 10/1	- kWh
541813	7T8/MAS/24-830/IF10/P/DIM 10/1	- kWh
541821	7T8/MAS/24-835/IF10/P/DIM 10/1	- kWh
541839	7T8/MAS/24-840/IF11/P/DIM 10/1	- kWh
541847	7T8/MAS/24-850/IF11/P/DIM 10/1	- kWh
541854	13T8-6U/MAS/24-830/IF20/P/DIM 10/1	- kWh
541862	13T8-6U/MAS/24-835/IF20/P/DIM 10/1	- kWh
541870	13T8-6U/MAS/24-840/IF21/P/DIM 10/1	- kWh
541888	13T8-6U/MAS/24-850/IF21/P/DIM 10/1	- kWh
600189	12.5T8/COR/48-840/FF18/G/DIM 25/1	-
600197	12.5T8/COR/48-850/FF18/G/DIM 25/1	-
560193	12.5T8/COR/48-835/FF17/G/DIM 25/1	-
575522	14.5T8/MAS/48-835/MF20/P 10/1	-
579441	10.5T8/MAS/48-835/MF15/P/DIM 25/1	-
579458	10.5T8/MAS/48-840/MF16/P/DIM 25/1	-
579466	10.5T8/MAS/48-850/MF16/P/DIM 25/1	-
579474	14.5T8/MAS/48-830/MF20/P/DIM 25/1	-
579482	14.5T8/MAS/48-835/MF20/P/DIM 25/1	-
579490	14.5T8/MAS/48-840/MF21/P/DIM 25/1	-
579508	14.5T8/MAS/48-850/MF21/P/DIM 25/1	-
579516	16.5T8/MAS/48-835/MF24/P/DIM 25/1	-
579524	16.5T8/MAS/48-840/MF25/P/DIM 25/1	-
579532	16.5T8/MAS/48-850/MF25/P/DIM 25/1	-
563452	9.9T8/COR/48-835/MF15/G 10/1	- kWh
563460	9.9T8/COR/48-840/MF16/G 10/1	- kWh
563478	9.9T8/COR/48-850/MF16/G 10/1	- kWh
563486	12T8/COR/48-830/MF17/G 10/1	- kWh
563494	12T8/COR/48-835/MF17/G 10/1	- kWh

Order Code	Full Product Name	Energy Consumption kWh/ 1000 h
563502	12T8/COR/48-840/MF18/G 10/1	- kWh
563510	12T8/COR/48-850/MF18/G 10/1	- kWh
563528	14.5T8/COR/48-830/MF20/G 10/1	- kWh
563536	14.5T8/COR/48-835/MF20/G 10/1	- kWh
563544	14.5T8/COR/48-840/MF21/G 10/1	- kWh
563551	14.5T8/COR/48-850/MF21/G 10/1	- kWh
579318	9.9T8/COR/48-835/MF15/G/DIM 25/1	-
579326	9.9T8/COR/48-840/MF16/G/DIM 25/1	-
579334	9.9T8/COR/48-850/MF16/G/DIM 25/1	-
579342	12T8/COR/48-830/MF17/G/DIM 25/1	-
579359	12T8/COR/48-835/MF17/G/DIM 25/1	-
579383	12T8/COR/48-840/MF18/G/DIM 25/1	-
579391	12T8/COR/48-850/MF18/G/DIM 25/1	-
575134	42T8HO/COR/96-840/MF54/G/FA8 10/1	-
575142	42T8HO/COR/96-850/MF54/G/FA8 10/1	-

Order Code	Full Product Name	Energy Consumption kWh/ 1000 h
575720	33T8/COR/96-840/MF44/G/FA8 10/1	-
575738	33T8/COR/96-850/MF44/G/FA8 10/1	-
575746	42T8HO/COR/96-840/MF54/G/R17d 10/1	-
575753	42T8HO/COR/96-850/MF54/G/R17d 10/1	-
577767	14.5T8/CNG/48-835/MF17/G 25/1	-
577775	14.5T8/CNG/48-840/MF18/G 25/1	-
577783	14.5T8/CNG/48-850/MF18/G 25/1	-
577791	14.5T8/CNG/48-865/MF18/G 25/1	-
579045	16.5T8/CNG/48-835/MF20/G 25/1	-
579052	16.5T8/CNG/48-840/MF21/G 25/1	-
579060	16.5T8/CNG/48-850/MF21/G 25/1	-
579284	15T8/COR/48-835/MF20/G/120-347V 25/1	-
579292	15T8/COR/48-840/MF21/G/120-347V 25/1	-
579300	15T8/COR/48-850/MF21/G/120-347V 25/1	-
579672	14.5T8/COR/48-5CCT/MF18/G/DIM 25/1	-

Controls and dimming

Order Code	Full Product Name	Dimmable
469247	35T8/96-3500 IF FA8 10/1	No
469254	35T8/96-4000 IF FA8 10/1	No
470096	14T8/COR/48-830/IF20/G/DIM 10/1	Yes
470104	14T8/COR/48-835/IF20/G/DIM 10/1	Yes
470112	14T8/COR/48-840/IF21/G/DIM 10/1	Yes
470120	14T8/COR/48-850/IF21/G/DIM 10/1	Yes
553230	10T8/COR/48-840/IF16/G/DIM 10/1	Yes
553248	10T8/COR/48-850/IF16/G/DIM 10/1	Yes
553214	10T8/COR/48-830/IF15/G/DIM 10/1	Yes
553222	10T8/COR/48-835/IF15/G/DIM 10/1	Yes
473926	13T8/MAS/48-830/IF20/P/DIM 10/1	Only with specific dimmers
473934	13T8/MAS/48-835/IF20/P/DIM 10/1	Only with specific dimmers
473942	13T8/MAS/48-840/IF21/P/DIM 10/1	Only with specific dimmers
473958	13T8/MAS/48-850/IF21/P/DIM 10/1	Only with specific dimmers
545178	15.5T8/MAS/48-830/IF23/P/DIM 25/1	Only with specific dimmers
533372	15.5T8/MAS/48-835/IF24/P/DIM 25/1	Only with specific dimmers
545194	15.5T8/MAS/48-840/IF25/P/DIM 25/1	Only with specific dimmers
545200	15.5T8/MAS/48-850/IF25/P/DIM 25/1	Only with specific dimmers
565580	8.9T8/MAS/48-830/IF15/P/DIM 10/1	Only with specific dimmers
565598	8.9T8/MAS/48-835/IF15/P/DIM 10/1	Only with specific dimmers
565606	8.9T8/MAS/48-840/IF16/P/DIM 10/1	Only with specific dimmers
565614	8.9T8/MAS/48-850/IF16/P/DIM 10/1	Only with specific dimmers
533018	30T8/COR/96-835/IF39/G/FA8 10/1	No
533026	30T8/COR/96-840/IF42/G/FA8 10/1	No
533034	30T8/COR/96-850/IF42/G/FA8 10/1	No
535450	8.5T8/COR/24-830/MF11/G 10/1	No
535468	8.5T8/COR/24-835/MF11/G 10/1	No
535476	8.5T8/COR/24-840/MF11/G 10/1	No
535484	8.5T8/COR/24-850/MF11/G 10/1	No
535492	11.5T8/COR/36-830/MF13/G 10/1	No
535500	11.5T8/COR/36-835/MF13/G 10/1	No
535518	11.5T8/COR/36-840/MF14/G 10/1	No

Order Code	Full Product Name	Dimmable
535526	11.5T8/COR/36-850/MF14/G 10/1	No
535534	15.5T8-6U/COR/24-830/MF20/G 10/1	No
535542	15.5T8-6U/COR/24-835/MF20/G 10/1	No
535559	15.5T8-6U/COR/24-840/MF21/G 10/1	No
535567	15.5T8-6U/COR/24-850/MF21/G 10/1	No
542084	16T8/LED/48-840/IF18/G 25/1	No
542092	16T8/LED/48-850/IF18/G 25/1	No
539858	8.5T8/MAS/36-830/IF13/P/DIM 10/1	Only with specific dimmers
539874	8.5T8/MAS/36-840/IF14/P/DIM 10/1	Only with specific dimmers
539882	8.5T8/MAS/36-850/IF14/P/DIM 10/1	Only with specific dimmers
539866	8.5T8/MAS/36-835/IF13/P/DIM 10/1	Only with specific dimmers
541813	7T8/MAS/24-830/IF10/P/DIM 10/1	Only with specific dimmers
541821	7T8/MAS/24-835/IF10/P/DIM 10/1	Only with specific dimmers
541839	7T8/MAS/24-840/IF11/P/DIM 10/1	Only with specific dimmers
541847	7T8/MAS/24-850/IF11/P/DIM 10/1	Only with specific dimmers
541854	13T8-6U/MAS/24-830/IF20/P/DIM 10/1	Yes
541862	13T8-6U/MAS/24-835/IF20/P/DIM 10/1	Yes
541870	13T8-6U/MAS/24-840/IF21/P/DIM 10/1	Yes
541888	13T8-6U/MAS/24-850/IF21/P/DIM 10/1	Yes
600189	12.5T8/COR/48-840/FF18/G/DIM 25/1	Only with specific dimmers
600197	12.5T8/COR/48-850/FF18/G/DIM 25/1	Only with specific dimmers
560193	12.5T8/COR/48-835/FF17/G/DIM 25/1	Only with specific dimmers
575522	14.5T8/MAS/48-835/MF20/P 10/1	Limited
579441	10.5T8/MAS/48-835/MF15/P/DIM 25/1	Only with specific dimmers
579458	10.5T8/MAS/48-840/MF16/P/DIM 25/1	Only with specific dimmers
579466	10.5T8/MAS/48-850/MF16/P/DIM 25/1	Only with specific dimmers
579474	14.5T8/MAS/48-830/MF20/P/DIM 25/1	Only with specific dimmers
579482	14.5T8/MAS/48-835/MF20/P/DIM 25/1	Only with specific dimmers
579490	14.5T8/MAS/48-840/MF21/P/DIM 25/1	Only with specific dimmers
579508	14.5T8/MAS/48-850/MF21/P/DIM 25/1	Only with specific dimmers
579516	16.5T8/MAS/48-835/MF24/P/DIM 25/1	Only with specific dimmers
579524	16.5T8/MAS/48-840/MF25/P/DIM 25/1	Only with specific dimmers

Order Code	Full Product Name	Dimmable
579532	16.5T8/MAS/48-850/MF25/P/DIM 25/1	Only with specific dimmers
563452	9.9T8/COR/48-835/MF15/G 10/1	Limited
563460	9.9T8/COR/48-840/MF16/G 10/1	Limited
563478	9.9T8/COR/48-850/MF16/G 10/1	Limited
563486	12T8/COR/48-830/MF17/G 10/1	Limited
563494	12T8/COR/48-835/MF17/G 10/1	Limited
563502	12T8/COR/48-840/MF18/G 10/1	Limited
563510	12T8/COR/48-850/MF18/G 10/1	Limited
563528	14.5T8/COR/48-830/MF20/G 10/1	Limited
563536	14.5T8/COR/48-835/MF20/G 10/1	Limited
563544	14.5T8/COR/48-840/MF21/G 10/1	Limited
563551	14.5T8/COR/48-850/MF21/G 10/1	Limited
579318	9.9T8/COR/48-835/MF15/G/DIM 25/1	Only with specific dimmers
579326	9.9T8/COR/48-840/MF16/G/DIM 25/1	Only with specific dimmers
579334	9.9T8/COR/48-850/MF16/G/DIM 25/1	Only with specific dimmers
579342	12T8/COR/48-830/MF17/G/DIM 25/1	Only with specific dimmers
579359	12T8/COR/48-835/MF17/G/DIM 25/1	Only with specific dimmers
579383	12T8/COR/48-840/MF18/G/DIM 25/1	Only with specific dimmers

Order Code	Full Product Name	Dimmable
579391	12T8/COR/48-850/MF18/G/DIM 25/1	Only with specific dimmers
575134	42T8HO/COR/96-840/MF54/G/FA8 10/1	Limited
575142	42T8HO/COR/96-850/MF54/G/FA8 10/1	Limited
575720	33T8/COR/96-840/MF44/G/FA8 10/1	Limited
575738	33T8/COR/96-850/MF44/G/FA8 10/1	Limited
575746	42T8HO/COR/96-840/MF54/G/R17d 10/1	Limited
575753	42T8HO/COR/96-850/MF54/G/R17d 10/1	Limited
577767	14.5T8/CNG/48-835/MF17/G 25/1	Limited
577775	14.5T8/CNG/48-840/MF18/G 25/1	Limited
577783	14.5T8/CNG/48-850/MF18/G 25/1	Limited
577791	14.5T8/CNG/48-865/MF18/G 25/1	Limited
579045	16.5T8/CNG/48-835/MF20/G 25/1	Limited
579052	16.5T8/CNG/48-840/MF21/G 25/1	Limited
579060	16.5T8/CNG/48-850/MF21/G 25/1	Limited
579284	15T8/COR/48-835/MF20/G/120-347V 25/1	Limited
579292	15T8/COR/48-840/MF21/G/120-347V 25/1	Limited
579300	15T8/COR/48-850/MF21/G/120-347V 25/1	Limited
579672	14.5T8/COR/48-5CCT/MF18/G/DIM 25/1	Only with specific dimmers

Operating and electrical

Order Code	Full Product Name	Input Frequency	Voltage (Nom)	Wattage Equivalent	Power (Nom)	Starting Time (Nom)
469247	35T8/96-3500 IF FA8 10/1	50000-64000 Hz	280-410 V	96 W	35 W	-
469254	35T8/96-4000 IF FA8 10/1	50000-64000 Hz	280-410 V	96 W	35 W	-
470096	14T8/COR/48-830/IF20/G/DIM 10/1	25000-105000 Hz	120-277, 347 V	32 W	14 W	0.5 s
470104	14T8/COR/48-835/IF20/G/DIM 10/1	25000-105000 Hz	120-277, 347 V	32 W	14 W	0.5 s
470112	14T8/COR/48-840/IF21/G/DIM 10/1	25000-105000 Hz	120-277, 347 V	32 W	14 W	0.5 s
470120	14T8/COR/48-850/IF21/G/DIM 10/1	25000-105000 Hz	120-277, 347 V	32 W	14 W	0.5 s
553230	10T8/COR/48-840/IF16/G/DIM 10/1	25000-105000 Hz	120-277, 347 V	32-30-28-25 W	10 W	0.5 s
553248	10T8/COR/48-850/IF16/G/DIM 10/1	25000-105000 Hz	120-277, 347 V	32-30-28-25 W	10 W	0.5 s
553214	10T8/COR/48-830/IF15/G/DIM 10/1	25000-105000 Hz	120-277, 347 V	32-30-28-25 W	10 W	0.5 s
553222	10T8/COR/48-835/IF15/G/DIM 10/1	25000-105000 Hz	120-277, 347 V	32-30-28-25 W	10 W	0.5 s
473926	13T8/MAS/48-830/IF20/P/DIM 10/1	20K to 120K Hz	120-277,347 V	32-30-28-25 W	13 W	0.5 s
473934	13T8/MAS/48-835/IF20/P/DIM 10/1	20K to 120K Hz	120-277,347 V	32-30-28-25 W	13 W	0.5 s
473942	13T8/MAS/48-840/IF21/P/DIM 10/1	20K to 120K Hz	120-277,347 V	32-30-28-25 W	13 W	0.5 s
473958	13T8/MAS/48-850/IF21/P/DIM 10/1	20K to 120K Hz	120-277,347 V	32-30-28-25 W	13 W	0.5 s
545178	15.5T8/MAS/48-830/IF23/P/DIM 25/1	20K to 120K Hz	120-277,347 V	32 W	15.5 W	0.5 s
533372	15.5T8/MAS/48-835/IF24/P/DIM 25/1	20K to 120K Hz	120-277,347 V	32 W	15.5 W	0.5 s
545194	15.5T8/MAS/48-840/IF25/P/DIM 25/1	20K to 120K Hz	120-277,347 V	32 W	15.5 W	0.5 s
545200	15.5T8/MAS/48-850/IF25/P/DIM 25/1	20K to 120K Hz	120-277,347 V	32 W	15.5 W	0.5 s
565580	8.9T8/MAS/48-830/IF15/P/DIM 10/1	20K to 120K Hz	120-277,347 V	32 W	8.9 W	0.5 s
565598	8.9T8/MAS/48-835/IF15/P/DIM 10/1	20K to 120K Hz	120-277,347 V	32 W	8.9 W	0.5 s
565606	8.9T8/MAS/48-840/IF16/P/DIM 10/1	20K to 120K Hz	120-277,347 V	32 W	8.9 W	0.5 s
565614	8.9T8/MAS/48-850/IF16/P/DIM 10/1	20K to 120K Hz	120-277,347 V	32 W	8.9 W	0.5 s
533018	30T8/COR/96-835/IF39/G/FA8 10/1	35000-150000 Hz	200-500 V	60 W	30 W	0.5 s
533026	30T8/COR/96-840/IF42/G/FA8 10/1	35000-150000 Hz	200-500 V	60 W	30 W	0.5 s
533034	30T8/COR/96-850/IF42/G/FA8 10/1	35000-150000 Hz	200-500 V	60 W	30 W	0.5 s
535450	8.5T8/COR/24-830/MF11/G 10/1	50 to 60 Hz	120-277 V	17 W	8.5 W	0.9 s
535468	8.5T8/COR/24-835/MF11/G 10/1	50 to 60 Hz	120-277 V	17 W	8.5 W	0.9 s
535476	8.5T8/COR/24-840/MF11/G 10/1	50 to 60 Hz	120-277 V	17 W	8.5 W	0.9 s
535484	8.5T8/COR/24-850/MF11/G 10/1	50 to 60 Hz	120-277 V	17 W	8.5 W	0.9 s
535492	11.5T8/COR/36-830/MF13/G 10/1	50 to 60 Hz	120-277 V	25 W	11.5 W	0.9 s

Order Code	Full Product Name	Input Frequency	Voltage (Nom)	Wattage Equivalent	Power (Nom)	Starting Time (Nom)
535500	11.5T8/COR/36-835/MF13/G 10/1	50 to 60 Hz	120-277 V	25 W	11.5 W	0.9 s
535518	11.5T8/COR/36-840/MF14/G 10/1	50 to 60 Hz	120-277 V	25 W	11.5 W	0.9 s
535526	11.5T8/COR/36-850/MF14/G 10/1	50 to 60 Hz	120-277 V	25 W	11.5 W	0.9 s
535534	15.5T8-6U/COR/24-830/MF20/G 10/1	50 to 60 Hz	120-277 V	32 W	15.5 W	0.9 s
535542	15.5T8-6U/COR/24-835/MF20/G 10/1	50 to 60 Hz	120-277 V	32 W	15.5 W	0.9 s
535559	15.5T8-6U/COR/24-840/MF21/G 10/1	50 to 60 Hz	120-277 V	32 W	15.5 W	0.9 s
535567	15.5T8-6U/COR/24-850/MF21/G 10/1	50 to 60 Hz	120-277 V	32 W	15.5 W	0.9 s
542084	16T8/LED/48-840/IF18/G 25/1	20K to 120K Hz	120-277, 347 V	32 W	16 W	0.5 s
542092	16T8/LED/48-850/IF18/G 25/1	20K to 120K Hz	120-277, 347 V	32 W	16 W	0.5 s
539858	8.5T8/MAS/36-830/IF13/P/DIM 10/1	20K to 120K Hz	120-277,347 V	25 W	8.5 W	0.5 s
539874	8.5T8/MAS/36-840/IF14/P/DIM 10/1	20K to 120K Hz	120-277,347 V	25 W	8.5 W	0.5 s
539882	8.5T8/MAS/36-850/IF14/P/DIM 10/1	20K to 120K Hz	120-277,347 V	25 W	8.5 W	0.5 s
539866	8.5T8/MAS/36-835/IF13/P/DIM 10/1	20K to 120K Hz	120-277,347 V	25 W	8.5 W	0.5 s
541813	7T8/MAS/24-830/IF10/P/DIM 10/1	20K to 120K Hz	120-277,347 V	17 W	7 W	0.5 s
541821	7T8/MAS/24-835/IF10/P/DIM 10/1	20K to 120K Hz	120-277,347 V	17 W	7 W	0.5 s
541839	7T8/MAS/24-840/IF11/P/DIM 10/1	20K to 120K Hz	120-277,347 V	17 W	7 W	0.5 s
541847	7T8/MAS/24-850/IF11/P/DIM 10/1	20K to 120K Hz	120-277,347 V	17 W	7 W	0.5 s
541854	13T8-6U/MAS/24-830/IF20/P/DIM 10/1	20K to 120K Hz	120-277, 347 V	32 W	13 W	0.5 s
541862	13T8-6U/MAS/24-835/IF20/P/DIM 10/1	20K to 120K Hz	120-277, 347 V	32 W	13 W	0.5 s
541870	13T8-6U/MAS/24-840/IF21/P/DIM 10/1	20K to 120K Hz	120-277, 347 V	32 W	13 W	0.5 s
541888	13T8-6U/MAS/24-850/IF21/P/DIM 10/1	20K to 120K Hz	120-277, 347 V	32 W	13 W	0.5 s
600189	12.5T8/COR/48-840/FF18/G/DIM 25/1	50 to 60 Hz	120-277 V	32 W	12.5, 13 W	0.5 s
600197	12.5T8/COR/48-850/FF18/G/DIM 25/1	50 to 60 Hz	120-277 V	32 W	12.5, 13 W	0.5 s
560193	12.5T8/COR/48-835/FF17/G/DIM 25/1	50 to 60 Hz	120-277 V	32 W	12.5, 13 W	0.5 s
575522	14.5T8/MAS/48-835/MF20/P 10/1	50 to 60 Hz	120-277 V	32 W	14.5 W	0.5 s
579441	10.5T8/MAS/48-835/MF15/P/DIM 25/1	50 to 60 Hz	120-277 V	-	10.5 W	0.5 s
579458	10.5T8/MAS/48-840/MF16/P/DIM 25/1	50 to 60 Hz	120-277 V	-	10.5 W	0.5 s
579466	10.5T8/MAS/48-850/MF16/P/DIM 25/1	50 to 60 Hz	120-277 V	-	10.5 W	0.5 s
579474	14.5T8/MAS/48-830/MF20/P/DIM 25/1	50 to 60 Hz	120-277 V	-	14.5 W	0.5 s
579482	14.5T8/MAS/48-835/MF20/P/DIM 25/1	50 to 60 Hz	120-277 V	-	14.5 W	0.5 s
579490	14.5T8/MAS/48-840/MF21/P/DIM 25/1	50 to 60 Hz	120-277 V	-	14.5 W	0.5 s
579508	14.5T8/MAS/48-850/MF21/P/DIM 25/1	50 to 60 Hz	120-277 V	-	14.5 W	0.5 s
579516	16.5T8/MAS/48-835/MF24/P/DIM 25/1	50 to 60 Hz	120-277 V	-	16.5 W	0.5 s
579524	16.5T8/MAS/48-840/MF25/P/DIM 25/1	50 to 60 Hz	120-277 V	-	16.5 W	0.5 s
579532	16.5T8/MAS/48-850/MF25/P/DIM 25/1	50 to 60 Hz	120-277 V	-	16.5 W	0.5 s
563452	9.9T8/COR/48-835/MF15/G 10/1	50 to 60 Hz	120-277 V	32 W	9.9 W	0.5 s
563460	9.9T8/COR/48-840/MF16/G 10/1	50 to 60 Hz	120-277 V	32 W	9.9 W	0.5 s
563478	9.9T8/COR/48-850/MF16/G 10/1	50 to 60 Hz	120-277 V	32 W	9.9 W	0.5 s
563486	12T8/COR/48-830/MF17/G 10/1	50 to 60 Hz	120-277 V	32 W	12 W	0.5 s
563494	12T8/COR/48-835/MF17/G 10/1	50 to 60 Hz	120-277 V	32 W	12 W	0.5 s
563502	12T8/COR/48-840/MF18/G 10/1	50 to 60 Hz	120-277 V	32 W	12 W	0.5 s
563510	12T8/COR/48-850/MF18/G 10/1	50 to 60 Hz	120-277 V	32 W	12 W	0.5 s
563528	14.5T8/COR/48-830/MF20/G 10/1	50 to 60 Hz	120-277 V	32 W	14.5 W	0.5 s
563536	14.5T8/COR/48-835/MF20/G 10/1	50 to 60 Hz	120-277 V	32 W	14.5 W	0.5 s
563544	14.5T8/COR/48-840/MF21/G 10/1	50 to 60 Hz	120-277 V	32 W	14.5 W	0.5 s
563551	14.5T8/COR/48-850/MF21/G 10/1	50 to 60 Hz	120-277 V	32 W	14.5 W	0.5 s
579318	9.9T8/COR/48-835/MF15/G/DIM 25/1	50 to 60 Hz	120-277 V	-	9.9 W	0.5 s
579326	9.9T8/COR/48-840/MF16/G/DIM 25/1	50 to 60 Hz	120-277 V	-	9.9 W	0.5 s
579334	9.9T8/COR/48-850/MF16/G/DIM 25/1	50 to 60 Hz	120-277 V	-	9.9 W	0.5 s
579342	12T8/COR/48-830/MF17/G/DIM 25/1	50 to 60 Hz	120-277 V	-	12 W	0.5 s
579359	12T8/COR/48-835/MF17/G/DIM 25/1	50 to 60 Hz	120-277 V	-	12 W	0.5 s
579383	12T8/COR/48-840/MF18/G/DIM 25/1	50 to 60 Hz	120-277 V	-	12 W	0.5 s

Order Code	Full Product Name	Input Frequency	Voltage (Nom)	Wattage Equivalent	Power (Nom)	Starting Time (Nom)
579391	12T8/COR/48-850/MF18/G/DIM 25/1	50 to 60 Hz	120-277 V	-	12 W	0.5 s
575134	42T8HO/COR/96-840/MF54/G/FA8 10/1	50 to 60 Hz	120-277 V	96 W	42 W	0.5 s
575142	42T8HO/COR/96-850/MF54/G/FA8 10/1	50 to 60 Hz	120-277 V	96 W	42 W	0.5 s
575720	33T8/COR/96-840/MF44/G/FA8 10/1	50 to 60 Hz	120-277 V	96 W	33 W	0.5 s
575738	33T8/COR/96-850/MF44/G/FA8 10/1	50 to 60 Hz	120-277 V	96 W	33 W	0.5 s
575746	42T8HO/COR/96-840/MF54/G/R17d 10/1	50 to 60 Hz	120-277 V	96 W	42 W	0.5 s
575753	42T8HO/COR/96-850/MF54/G/R17d 10/1	50 to 60 Hz	120-277 V	96 W	42 W	0.5 s
577767	14.5T8/CNG/48-835/MF17/G 25/1	50 to 60 Hz	120-277 V	32-30-28-25 W	14.5 W	0.5 s
577775	14.5T8/CNG/48-840/MF18/G 25/1	50 to 60 Hz	120-277 V	32-30-28-25 W	14.5 W	0.5 s
577783	14.5T8/CNG/48-850/MF18/G 25/1	50 to 60 Hz	120-277 V	32 W	14.5 W	0.5 s
577791	14.5T8/CNG/48-865/MF18/G 25/1	50 to 60 Hz	120-277 V	-	14.5 W	0.5 s
579045	16.5T8/CNG/48-835/MF20/G 25/1	50 to 60 Hz	120-277 V	-	16.5 W	0.5 s
579052	16.5T8/CNG/48-840/MF21/G 25/1	50 to 60 Hz	120-277 V	-	16.5 W	0.5 s
579060	16.5T8/CNG/48-850/MF21/G 25/1	50 to 60 Hz	120-277 V	-	16.5 W	0.5 s
579284	15T8/COR/48-835/MF20/G/120-347V 25/1	50 to 60 Hz	120-347 V	-	15 W	0.5 s
579292	15T8/COR/48-840/MF21/G/120-347V 25/1	50 to 60 Hz	120-347 V	-	15 W	0.5 s
579300	15T8/COR/48-850/MF21/G/120-347V 25/1	50 to 60 Hz	120-347 V	-	15 W	0.5 s
579672	14.5T8/COR/48-5CCT/MF18/G/DIM 25/1	50 to 60 Hz	120-277 V	-	14.5 W	0.5 s

General information

Order Code	Full Product Name	Cap-Base	Nominal Lifetime (Nom)	Switching Cycle
469247	35T8/96-3500 IF FA8 10/1	FA8	50000 h	50000
469254	35T8/96-4000 IF FA8 10/1	FA8	50000 h	50000
470096	14T8/COR/48-830/IF20/G/DIM 10/1	G13	70000 h	50000
470104	14T8/COR/48-835/IF20/G/DIM 10/1	G13	70000 h	50000
470112	14T8/COR/48-840/IF21/G/DIM 10/1	G13	70000 h	50000
470120	14T8/COR/48-850/IF21/G/DIM 10/1	G13	70000 h	50000
553230	10T8/COR/48-840/IF16/G/DIM 10/1	G13	70000 h	50000
553248	10T8/COR/48-850/IF16/G/DIM 10/1	G13	70000 h	50000
553214	10T8/COR/48-830/IF15/G/DIM 10/1	G13	70000 h	50000
553222	10T8/COR/48-835/IF15/G/DIM 10/1	G13	70000 h	50000
473926	13T8/MAS/48-830/IF20/P/DIM 10/1	G13	70000 h	50000
473934	13T8/MAS/48-835/IF20/P/DIM 10/1	G13	70000 h	50000
473942	13T8/MAS/48-840/IF21/P/DIM 10/1	G13	70000 h	50000
473958	13T8/MAS/48-850/IF21/P/DIM 10/1	G13	70000 h	50000
545178	15.5T8/MAS/48-830/IF23/P/DIM 25/1	G13	70000 h	50000

Order Code	Full Product Name	Cap-Base	Nominal Lifetime (Nom)	Switching Cycle
533372	15.5T8/MAS/48-835/IF24/P/DIM 25/1	G13	70000 h	50000
545194	15.5T8/MAS/48-840/IF25/P/DIM 25/1	G13	70000 h	50000
545200	15.5T8/MAS/48-850/IF25/P/DIM 25/1	G13	70000 h	50000
565580	8.9T8/MAS/48-830/IF15/P/DIM 10/1	G13	70000 h	50000
565598	8.9T8/MAS/48-835/IF15/P/DIM 10/1	G13	70000 h	50000
565606	8.9T8/MAS/48-840/IF16/P/DIM 10/1	G13	70000 h	50000
565614	8.9T8/MAS/48-850/IF16/P/DIM 10/1	G13	70000 h	50000
533018	30T8/COR/96-835/IF39/G/FA8 10/1	FA8	50000 h	50000
533026	30T8/COR/96-840/IF42/G/FA8 10/1	FA8	50000 h	50000
533034	30T8/COR/96-850/IF42/G/FA8 10/1	FA8	50000 h	50000
535450	8.5T8/COR/24-830/MF11/G 10/1	G13	50000 h	50000
535468	8.5T8/COR/24-835/MF11/G 10/1	G13	50000 h	50000
535476	8.5T8/COR/24-840/MF11/G 10/1	G13	50000 h	50000
535484	8.5T8/COR/24-850/MF11/G 10/1	G13	50000 h	50000
535492	11.5T8/COR/36-830/MF13/G 10/1	G13	50000 h	50000
535500	11.5T8/COR/36-835/MF13/G 10/1	G13	50000 h	50000
535518	11.5T8/COR/36-840/MF14/G 10/1	G13	50000 h	50000
535526	11.5T8/COR/36-850/MF14/G 10/1	G13	50000 h	50000

Order Code	Full Product Name	Cap-Base	Nominal Lifetime (Nom)	Switching Cycle
535534	15.5T8-6U/COR/24-830/MF20/G 10/1	2G13	50000 h	50000
535542	15.5T8-6U/COR/24-835/MF20/G 10/1	2G13	50000 h	50000
535559	15.5T8-6U/COR/24-840/MF21/G 10/1	2G13	50000 h	50000
535567	15.5T8-6U/COR/24-850/MF21/G 10/1	2G13	50000 h	50000
542084	16T8/LED/48-840/IF18/G 25/1	G13	36000 h	50000
542092	16T8/LED/48-850/IF18/G 25/1	G13	36000 h	50000
539858	8.5T8/MAS/36-830/IF13/P/DIM 10/1	G13	70000 h	50000
539874	8.5T8/MAS/36-840/IF14/P/DIM 10/1	G13	70000 h	50000
539882	8.5T8/MAS/36-850/IF14/P/DIM 10/1	G13	70000 h	50000
539866	8.5T8/MAS/36-835/IF13/P/DIM 10/1	G13	70000 h	50000
541813	7T8/MAS/24-830/IF10/P/DIM 10/1	G13	70000 h	50000
541821	7T8/MAS/24-835/IF10/P/DIM 10/1	G13	70000 h	50000
541839	7T8/MAS/24-840/IF11/P/DIM 10/1	G13	70000 h	50000
541847	7T8/MAS/24-850/IF11/P/DIM 10/1	G13	70000 h	50000
541854	13T8-6U/MAS/24-830/IF20/P/DIM 10/1	G13	70000 h	50000
541862	13T8-6U/MAS/24-835/IF20/P/DIM 10/1	G13	70000 h	50000
541870	13T8-6U/MAS/24-840/IF21/P/DIM 10/1	G13	70000 h	50000
541888	13T8-6U/MAS/24-850/IF21/P/DIM 10/1	G13	70000 h	50000
600189	12.5T8/COR/48-840/FF18/G/DIM 25/1	G13	50000 h	50000
600197	12.5T8/COR/48-850/FF18/G/DIM 25/1	G13	50000 h	50000
560193	12.5T8/COR/48-835/FF17/G/DIM 25/1	G13	50000 h	50000
575522	14.5T8/MAS/48-835/MF20/P 10/1	G13	70000 h	50000
579441	10.5T8/MAS/48-835/MF15/P/DIM 25/1	G13	70000 h	50000X
579458	10.5T8/MAS/48-840/MF16/P/DIM 25/1	G13	70000 h	50000X
579466	10.5T8/MAS/48-850/MF16/P/DIM 25/1	G13	70000 h	50000X
579474	14.5T8/MAS/48-830/MF20/P/DIM 25/1	G13	70000 h	50000X
579482	14.5T8/MAS/48-835/MF20/P/DIM 25/1	G13	70000 h	50000X
579490	14.5T8/MAS/48-840/MF21/P/DIM 25/1	G13	70000 h	50000X

Order Code	Full Product Name	Cap-Base	Nominal Lifetime (Nom)	Switching Cycle
579508	14.5T8/MAS/48-850/MF21/P/DIM 25/1	G13	70000 h	50000X
579516	16.5T8/MAS/48-835/MF24/P/DIM 25/1	G13	70000 h	50000X
579524	16.5T8/MAS/48-840/MF25/P/DIM 25/1	G13	70000 h	50000X
579532	16.5T8/MAS/48-850/MF25/P/DIM 25/1	G13	70000 h	50000X
563452	9.9T8/COR/48-835/MF15/G 10/1	G13	50000 h	50000
563460	9.9T8/COR/48-840/MF16/G 10/1	G13	50000 h	50000
563478	9.9T8/COR/48-850/MF16/G 10/1	G13	50000 h	50000
563486	12T8/COR/48-830/MF17/G 10/1	G13	50000 h	50000
563494	12T8/COR/48-835/MF17/G 10/1	G13	50000 h	50000
563502	12T8/COR/48-840/MF18/G 10/1	G13	50000 h	50000
563510	12T8/COR/48-850/MF18/G 10/1	G13	50000 h	50000
563528	14.5T8/COR/48-830/MF20/G 10/1	G13	50000 h	50000
563536	14.5T8/COR/48-835/MF20/G 10/1	G13	50000 h	50000
563544	14.5T8/COR/48-840/MF21/G 10/1	G13	50000 h	50000
563551	14.5T8/COR/48-850/MF21/G 10/1	G13	50000 h	50000
579318	9.9T8/COR/48-835/MF15/G/DIM 25/1	G13	50000 h	50000X
579326	9.9T8/COR/48-840/MF16/G/DIM 25/1	G13	50000 h	50000X
579334	9.9T8/COR/48-850/MF16/G/DIM 25/1	G13	50000 h	50000X
579342	12T8/COR/48-830/MF17/G/DIM 25/1	G13	50000 h	50000X
579359	12T8/COR/48-835/MF17/G/DIM 25/1	G13	50000 h	50000X
579383	12T8/COR/48-840/MF18/G/DIM 25/1	G13	50000 h	50000X
579391	12T8/COR/48-850/MF18/G/DIM 25/1	G13	50000 h	50000X
575134	42T8HO/COR/96-840/MF54/G/FA8 10/1	FA8	50000 h	50000
575142	42T8HO/COR/96-850/MF54/G/FA8 10/1	FA8	50000 h	50000
575720	33T8/COR/96-840/MF44/G/FA8 10/1	FA8	50000 h	50000
575738	33T8/COR/96-850/MF44/G/FA8 10/1	FA8	50000 h	50000
575746	42T8HO/COR/96-840/MF54/G/R17d 10/1	R17D	50000 h	50000
575753	42T8HO/COR/96-850/MF54/G/R17d 10/1	R17D	50000 h	50000
577767	14.5T8/CNG/48-835/MF17/G 25/1	G13	50000 h	50000
577775	14.5T8/CNG/48-840/MF18/G 25/1	G13	50000 h	50000
577783	14.5T8/CNG/48-850/MF18/G 25/1	G13	50000 h	50000
577791	14.5T8/CNG/48-865/MF18/G 25/1	G13	50000 h	50000
579045	16.5T8/CNG/48-835/MF20/G 25/1	G13	50000 h	50000

Order Code	Full Product Name	Cap-Base	Nominal Lifetime (Nom)	Switching Cycle
579052	16.5T8/CNG/48-840/MF21/G 25/1	G13	50000 h	50000
579060	16.5T8/CNG/48-850/MF21/G 25/1	G13	50000 h	50000
579284	15T8/COR/48-835/MF20/G/ 120-347V 25/1	G13	50000 h	50000
579292	15T8/COR/48-840/MF21/G/ 120-347V 25/1	G13	50000 h	50000

Order Code	Full Product Name	Cap-Base	Nominal Lifetime (Nom)	Switching Cycle
579300	15T8/COR/48-850/MF21/G/ 120-347V 25/1	G13	50000 h	50000
579672	14.5T8/COR/48-5CCT/ MF18/G/DIM 25/1	G13	50000 h	50000X

Light technical

Order Code	Full Product Name	Beam Angle (Nom)	Color Code	Correlated Color Temperature (Nom)	Color Rendering Index (Nom)	Luminous Flux (Nom)
469247	35T8/96-3500 IF FA8 10/1	180 °	835	3500 K	82	4000 lm
469254	35T8/96-4000 IF FA8 10/1	180 °	841	4000 K	82	4200 lm
470096	14T8/COR/48-830/IF20/G/DIM 10/1	240 °	830	3000 K	82	2000 lm
470104	14T8/COR/48-835/IF20/G/DIM 10/1	240 °	835	3500 K	82	2000 lm
470112	14T8/COR/48-840/IF21/G/DIM 10/1	240 °	841	4000 K	82	2100 lm
470120	14T8/COR/48-850/IF21/G/DIM 10/1	240 °	850	5000 K	82	2100 lm
553230	10T8/COR/48-840/IF16/G/DIM 10/1	240 °	841	4000 K	82	1600 lm
553248	10T8/COR/48-850/IF16/G/DIM 10/1	240 °	850	5000 K	82	1600 lm
553214	10T8/COR/48-830/IF15/G/DIM 10/1	240 °	830	3000 K	82	1500 lm
553222	10T8/COR/48-835/IF15/G/DIM 10/1	240 °	835	3500 K	82	1500 lm
473926	13T8/MAS/48-830/IF20/P/DIM 10/1	180 °	830	3000 K	80	2000 lm
473934	13T8/MAS/48-835/IF20/P/DIM 10/1	180 °	835	3500 K	80	2000 lm
473942	13T8/MAS/48-840/IF21/P/DIM 10/1	180 °	841	4000 K	80	2100 lm
473958	13T8/MAS/48-850/IF21/P/DIM 10/1	180 °	850	5000 K	80	2100 lm
545178	15.5T8/MAS/48-830/IF23/P/DIM 25/1	180 °	830	3000 K	80	2350 lm
533372	15.5T8/MAS/48-835/IF24/P/DIM 25/1	180 °	835	3500 K	80	2400 lm
545194	15.5T8/MAS/48-840/IF25/P/DIM 25/1	180 °	841	4000 K	80	2500 lm
545200	15.5T8/MAS/48-850/IF25/P/DIM 25/1	180 °	850	5000 K	80	2500 lm
565580	8.9T8/MAS/48-830/IF15/P/DIM 10/1	180 °	830	3000 K	80	1500 lm
565598	8.9T8/MAS/48-835/IF15/P/DIM 10/1	180 °	835	3500 K	80	1500 lm
565606	8.9T8/MAS/48-840/IF16/P/DIM 10/1	180 °	841	4000 K	80	1600 lm
565614	8.9T8/MAS/48-850/IF16/P/DIM 10/1	180 °	850	5000 K	80	1600 lm
533018	30T8/COR/96-835/IF39/G/FA8 10/1	240 °	835	3500 K	80	3950 lm
533026	30T8/COR/96-840/IF42/G/FA8 10/1	240 °	841	4000 K	80	4200 lm
533034	30T8/COR/96-850/IF42/G/FA8 10/1	240 °	850	5000 K	80	4200 lm
535450	8.5T8/COR/24-830/MF11/G 10/1	180 °	830	3000 K	82	1100 lm
535468	8.5T8/COR/24-835/MF11/G 10/1	180 °	835	3500 K	82	1100 lm
535476	8.5T8/COR/24-840/MF11/G 10/1	180 °	841	4000 K	82	1150 lm
535484	8.5T8/COR/24-850/MF11/G 10/1	180 °	850	5000 K	82	1150 lm
535492	11.5T8/COR/36-830/MF13/G 10/1	180 °	830	3000 K	82	1300 lm
535500	11.5T8/COR/36-835/MF13/G 10/1	180 °	835	3500 K	82	1300 lm
535518	11.5T8/COR/36-840/MF14/G 10/1	180 °	841	4000 K	82	1400 lm
535526	11.5T8/COR/36-850/MF14/G 10/1	180 °	850	5000 K	82	1400 lm
535534	15.5T8-6U/COR/24-830/MF20/G 10/1	180 °	830	3000 K	82	2000 lm
535542	15.5T8-6U/COR/24-835/MF20/G 10/1	180 °	835	3500 K	82	2000 lm
535559	15.5T8-6U/COR/24-840/MF21/G 10/1	180 °	841	4000 K	82	2100 lm
535567	15.5T8-6U/COR/24-850/MF21/G 10/1	180 °	850	5000 K	82	2100 lm
542084	16T8/LED/48-840/IF18/G 25/1	240 °	841	4000 K	80	1800 lm
542092	16T8/LED/48-850/IF18/G 25/1	240 °	850	5000 K	80	1800 lm
539858	8.5T8/MAS/36-830/IF13/P/DIM 10/1	180 °	830	3000 K	80	1350 lm

Order Code	Full Product Name	Beam Angle (Nom)	Color Code	Correlated Color Temperature (Nom)	Color Rendering Index (Nom)	Luminous Flux (Nom)
539874	8.5T8/MAS/36-840/IF14/P/DIM 10/1	180 °	841	4000 K	80	1400 lm
539882	8.5T8/MAS/36-850/IF14/P/DIM 10/1	180 °	850	5000 K	80	1400 lm
539866	8.5T8/MAS/36-835/IF13/P/DIM 10/1	180 °	835	3500 K	80	1350 lm
541813	7T8/MAS/24-830/IF10/P/DIM 10/1	180 °	830	3000 K	80	1150 lm
541821	7T8/MAS/24-835/IF10/P/DIM 10/1	180 °	835	3500 K	80	1150 lm
541839	7T8/MAS/24-840/IF11/P/DIM 10/1	180 °	841	4000 K	80	1200 lm
541847	7T8/MAS/24-850/IF11/P/DIM 10/1	180 °	850	5000 K	80	1200 lm
541854	13T8-6U/MAS/24-830/IF20/P/DIM 10/1	180 °	830	3000 K	80	2000 lm
541862	13T8-6U/MAS/24-835/IF20/P/DIM 10/1	180 °	835	3500 K	80	2000 lm
541870	13T8-6U/MAS/24-840/IF21/P/DIM 10/1	180 °	841	4000 K	80	2100 lm
541888	13T8-6U/MAS/24-850/IF21/P/DIM 10/1	180 °	850	5000 K	80	2100 lm
600189	12.5T8/COR/48-840/FF18/G/DIM 25/1	220 °	841	4000 K	82	1800 lm
600197	12.5T8/COR/48-850/FF18/G/DIM 25/1	220 °	850	5000 K	82	1800 lm
560193	12.5T8/COR/48-835/FF17/G/DIM 25/1	220 °	835	3500 K	82	1700 lm
575522	14.5T8/MAS/48-835/MF20/P 10/1	180 °	835	3500 K	80	2000 lm
579441	10.5T8/MAS/48-835/MF15/P/DIM 25/1	180 °	835	3500 K	80	1550 lm
579458	10.5T8/MAS/48-840/MF16/P/DIM 25/1	180 °	841	4000 K	80	1600 lm
579466	10.5T8/MAS/48-850/MF16/P/DIM 25/1	180 °	850	5000 K	80	1600 lm
579474	14.5T8/MAS/48-830/MF20/P/DIM 25/1	180 °	830	3000 K	80	2000 lm
579482	14.5T8/MAS/48-835/MF20/P/DIM 25/1	180 °	835	3500 K	80	2000 lm
579490	14.5T8/MAS/48-840/MF21/P/DIM 25/1	180 °	841	4000 K	80	2100 lm
579508	14.5T8/MAS/48-850/MF21/P/DIM 25/1	180 °	850	5000 K	80	2100 lm
579516	16.5T8/MAS/48-835/MF24/P/DIM 25/1	180 °	835	3500 K	80	2450 lm
579524	16.5T8/MAS/48-840/MF25/P/DIM 25/1	180 °	841	4000 K	80	2500 lm
579532	16.5T8/MAS/48-850/MF25/P/DIM 25/1	180 °	850	5000 K	80	2500 lm
563452	9.9T8/COR/48-835/MF15/G 10/1	240 °	835	3500 K	80	1550 lm
563460	9.9T8/COR/48-840/MF16/G 10/1	240 °	841	4000 K	80	1600 lm
563478	9.9T8/COR/48-850/MF16/G 10/1	240 °	850	5000 K	80	1600 lm
563486	12T8/COR/48-830/MF17/G 10/1	240 °	830	3000 K	80	1700 lm
563494	12T8/COR/48-835/MF17/G 10/1	240 °	835	3500 K	80	1700 lm
563502	12T8/COR/48-840/MF18/G 10/1	240 °	841	4000 K	80	1800 lm
563510	12T8/COR/48-850/MF18/G 10/1	240 °	850	5000 K	80	1800 lm
563528	14.5T8/COR/48-830/MF20/G 10/1	240 °	830	3000 K	80	2000 lm
563536	14.5T8/COR/48-835/MF20/G 10/1	240 °	835	3500 K	80	2000 lm
563544	14.5T8/COR/48-840/MF21/G 10/1	240 °	841	4000 K	80	2100 lm
563551	14.5T8/COR/48-850/MF21/G 10/1	240 °	850	5000 K	80	2100 lm
579318	9.9T8/COR/48-835/MF15/G/DIM 25/1	240 °	835	3500 K	80	1550 lm
579326	9.9T8/COR/48-840/MF16/G/DIM 25/1	240 °	841	4000 K	80	1600 lm
579334	9.9T8/COR/48-850/MF16/G/DIM 25/1	240 °	850	5000 K	80	1600 lm
579342	12T8/COR/48-830/MF17/G/DIM 25/1	240 °	830	3000 K	80	1700 lm
579359	12T8/COR/48-835/MF17/G/DIM 25/1	240 °	835	3500 K	80	1700 lm
579383	12T8/COR/48-840/MF18/G/DIM 25/1	240 °	841	4000 K	80	1800 lm
579391	12T8/COR/48-850/MF18/G/DIM 25/1	240 °	850	5000 K	80	1800 lm
575134	42T8HO/COR/96-840/MF54/G/FA8 10/1	240 °	841	4000 K	80	5400 lm
575142	42T8HO/COR/96-850/MF54/G/FA8 10/1	240 °	850	5000 K	80	5400 lm
575720	33T8/COR/96-840/MF44/G/FA8 10/1	240 °	841	4000 K	80	4400 lm
575738	33T8/COR/96-850/MF44/G/FA8 10/1	240 °	850	5000 K	80	4400 lm
575746	42T8HO/COR/96-840/MF54/G/R17d 10/1	240 °	841	4000 K	80	5400 lm
575753	42T8HO/COR/96-850/MF54/G/R17d 10/1	240 °	850	5000 K	80	5400 lm
577767	14.5T8/CNG/48-835/MF17/G 25/1	240 °	835	3500 K	80	1750 lm
577775	14.5T8/CNG/48-840/MF18/G 25/1	240 °	841	4000 K	80	1800 lm
577783	14.5T8/CNG/48-850/MF18/G 25/1	240 °	850	5000 K	80	1800 lm

Order Code	Full Product Name	Beam Angle (Nom)	Color Code	Correlated Color Temperature (Nom)	Color Rendering Index (Nom)	Luminous Flux (Nom)
577791	14.5T8/CNG/48-865/MF18/G 25/1	240 °	865	6500 K	80	1800 lm
579045	16.5T8/CNG/48-835/MF20/G 25/1	240 °	835	3500 K	80	2000 lm
579052	16.5T8/CNG/48-840/MF21/G 25/1	240 °	841	4000 K	80	2100 lm
579060	16.5T8/CNG/48-850/MF21/G 25/1	240 °	850	5000 K	80	2100 lm
579284	15T8/COR/48-835/MF20/G/120-347V 25/1	240 °	835	3500 K	80	2000 lm
579292	15T8/COR/48-840/MF21/G/120-347V 25/1	240 °	841	4000 K	80	2100 lm
579300	15T8/COR/48-850/MF21/G/120-347V 25/1	240 °	850	5000 K	80	2100 lm
579672	14.5T8/COR/48-5CCT/MF18/G/DIM 25/1	240 °	3000K/ 3500K/ 4000K/ 5000K/ 6500K	3000, 3500, 4000, 5000, 6500 K	80	1800 lm

Temperature

Order Code	Full Product Name	T-Ambient (Max)	T-Case Maximum (Nom)
469247	35T8/96-3500 IF FA8 10/1	45 °C	45 °C
469254	35T8/96-4000 IF FA8 10/1	45 °C	45 °C
470096	14T8/COR/48-830/IF20/G/DIM 10/1	45 °C	50 °C
470104	14T8/COR/48-835/IF20/G/DIM 10/1	45 °C	50 °C
470112	14T8/COR/48-840/IF21/G/DIM 10/1	45 °C	50 °C
470120	14T8/COR/48-850/IF21/G/DIM 10/1	45 °C	50 °C
553230	10T8/COR/48-840/IF16/G/DIM 10/1	45 °C	50 °C
553248	10T8/COR/48-850/IF16/G/DIM 10/1	45 °C	50 °C
553214	10T8/COR/48-830/IF15/G/DIM 10/1	45 °C	50 °C
553222	10T8/COR/48-835/IF15/G/DIM 10/1	45 °C	50 °C
473926	13T8/MAS/48-830/IF20/P/DIM 10/1	45 °C	40 °C
473934	13T8/MAS/48-835/IF20/P/DIM 10/1	45 °C	40 °C
473942	13T8/MAS/48-840/IF21/P/DIM 10/1	45 °C	40 °C
473958	13T8/MAS/48-850/IF21/P/DIM 10/1	45 °C	40 °C
545178	15.5T8/MAS/48-830/IF23/P/DIM 25/1	55 °C	40 °C
533372	15.5T8/MAS/48-835/IF24/P/DIM 25/1	55 °C	40 °C
545194	15.5T8/MAS/48-840/IF25/P/DIM 25/1	55 °C	40 °C
545200	15.5T8/MAS/48-850/IF25/P/DIM 25/1	55 °C	40 °C
565580	8.9T8/MAS/48-830/IF15/P/DIM 10/1	45 °C	40 °C
565598	8.9T8/MAS/48-835/IF15/P/DIM 10/1	45 °C	40 °C
565606	8.9T8/MAS/48-840/IF16/P/DIM 10/1	45 °C	40 °C
565614	8.9T8/MAS/48-850/IF16/P/DIM 10/1	45 °C	40 °C
533018	30T8/COR/96-835/IF39/G/FA8 10/1	45 °C	45 °C
533026	30T8/COR/96-840/IF42/G/FA8 10/1	45 °C	45 °C
533034	30T8/COR/96-850/IF42/G/FA8 10/1	45 °C	45 °C
535450	8.5T8/COR/24-830/MF11/G 10/1	45 °C	50 °C
535468	8.5T8/COR/24-835/MF11/G 10/1	45 °C	50 °C
535476	8.5T8/COR/24-840/MF11/G 10/1	45 °C	50 °C
535484	8.5T8/COR/24-850/MF11/G 10/1	45 °C	50 °C
535492	11.5T8/COR/36-830/MF13/G 10/1	45 °C	50 °C
535500	11.5T8/COR/36-835/MF13/G 10/1	45 °C	50 °C
535518	11.5T8/COR/36-840/MF14/G 10/1	45 °C	50 °C
535526	11.5T8/COR/36-850/MF14/G 10/1	45 °C	50 °C
535534	15.5T8-6U/COR/24-830/MF20/G 10/1	45 °C	51 °C
535542	15.5T8-6U/COR/24-835/MF20/G 10/1	45 °C	51 °C

Order Code	Full Product Name	T-Ambient (Max)	T-Case Maximum (Nom)
535559	15.5T8-6U/COR/24-840/MF21/G 10/1	45 °C	51 °C
535567	15.5T8-6U/COR/24-850/MF21/G 10/1	45 °C	51 °C
542084	16T8/LED/48-840/IF18/G 25/1	45 °C	35 °C
542092	16T8/LED/48-850/IF18/G 25/1	45 °C	35 °C
539858	8.5T8/MAS/36-830/IF13/P/DIM 10/1	45 °C	40 °C
539874	8.5T8/MAS/36-840/IF14/P/DIM 10/1	45 °C	40 °C
539882	8.5T8/MAS/36-850/IF14/P/DIM 10/1	45 °C	40 °C
539866	8.5T8/MAS/36-835/IF13/P/DIM 10/1	45 °C	40 °C
541813	7T8/MAS/24-830/IF10/P/DIM 10/1	45 °C	40 °C
541821	7T8/MAS/24-835/IF10/P/DIM 10/1	45 °C	40 °C
541839	7T8/MAS/24-840/IF11/P/DIM 10/1	45 °C	40 °C
541847	7T8/MAS/24-850/IF11/P/DIM 10/1	45 °C	40 °C
541854	13T8-6U/MAS/24-830/IF20/P/DIM 10/1	45 °C	50 °C
541862	13T8-6U/MAS/24-835/IF20/P/DIM 10/1	45 °C	50 °C
541870	13T8-6U/MAS/24-840/IF21/P/DIM 10/1	45 °C	50 °C
541888	13T8-6U/MAS/24-850/IF21/P/DIM 10/1	45 °C	50 °C
600189	12.5T8/COR/48-840/FF18/G/DIM 25/1	45 °C	60 °C
600197	12.5T8/COR/48-850/FF18/G/DIM 25/1	45 °C	60 °C
560193	12.5T8/COR/48-835/FF17/G/DIM 25/1	45 °C	60 °C
575522	14.5T8/MAS/48-835/MF20/P 10/1	45 °C	70 °C
579441	10.5T8/MAS/48-835/MF15/P/DIM 25/1	45 °C	70 °C
579458	10.5T8/MAS/48-840/MF16/P/DIM 25/1	45 °C	70 °C
579466	10.5T8/MAS/48-850/MF16/P/DIM 25/1	45 °C	70 °C
579474	14.5T8/MAS/48-830/MF20/P/DIM 25/1	45 °C	70 °C
579482	14.5T8/MAS/48-835/MF20/P/DIM 25/1	45 °C	70 °C
579490	14.5T8/MAS/48-840/MF21/P/DIM 25/1	45 °C	70 °C
579508	14.5T8/MAS/48-850/MF21/P/DIM 25/1	45 °C	70 °C

Order Code	Full Product Name	T-Ambient (Max)	T-Case Maximum (Nom)
579516	16.5T8/MAS/48-835/MF24/P/DIM 25/1	45 °C	70 °C
579524	16.5T8/MAS/48-840/MF25/P/DIM 25/1	45 °C	70 °C
579532	16.5T8/MAS/48-850/MF25/P/DIM 25/1	45 °C	70 °C
563452	9.9T8/COR/48-835/MF15/G 10/1	45 °C	70 °C
563460	9.9T8/COR/48-840/MF16/G 10/1	45 °C	70 °C
563478	9.9T8/COR/48-850/MF16/G 10/1	45 °C	70 °C
563486	12T8/COR/48-830/MF17/G 10/1	45 °C	70 °C
563494	12T8/COR/48-835/MF17/G 10/1	45 °C	70 °C
563502	12T8/COR/48-840/MF18/G 10/1	45 °C	70 °C
563510	12T8/COR/48-850/MF18/G 10/1	45 °C	70 °C
563528	14.5T8/COR/48-830/MF20/G 10/1	45 °C	70 °C
563536	14.5T8/COR/48-835/MF20/G 10/1	45 °C	70 °C
563544	14.5T8/COR/48-840/MF21/G 10/1	45 °C	70 °C
563551	14.5T8/COR/48-850/MF21/G 10/1	45 °C	70 °C
579318	9.9T8/COR/48-835/MF15/G/DIM 25/1	45 °C	70 °C
579326	9.9T8/COR/48-840/MF16/G/DIM 25/1	45 °C	70 °C
579334	9.9T8/COR/48-850/MF16/G/DIM 25/1	45 °C	70 °C
579342	12T8/COR/48-830/MF17/G/DIM 25/1	45 °C	70 °C
579359	12T8/COR/48-835/MF17/G/DIM 25/1	45 °C	70 °C
579383	12T8/COR/48-840/MF18/G/DIM 25/1	45 °C	70 °C
579391	12T8/COR/48-850/MF18/G/DIM 25/1	45 °C	70 °C
575134	42T8HO/COR/96-840/MF54/G/FA8 10/1	45 °C	55 °C
575142	42T8HO/COR/96-850/MF54/G/FA8 10/1	45 °C	55 °C
575720	33T8/COR/96-840/MF44/G/FA8 10/1	45 °C	50 °C
575738	33T8/COR/96-850/MF44/G/FA8 10/1	45 °C	50 °C
575746	42T8HO/COR/96-840/MF54/G/R17d 10/1	45 °C	55 °C
575753	42T8HO/COR/96-850/MF54/G/R17d 10/1	45 °C	55 °C
577767	14.5T8/CNG/48-835/MF17/G 25/1	45 °C	70 °C
577775	14.5T8/CNG/48-840/MF18/G 25/1	45 °C	70 °C
577783	14.5T8/CNG/48-850/MF18/G 25/1	45 °C	70 °C
577791	14.5T8/CNG/48-865/MF18/G 25/1	45 °C	70 °C
579045	16.5T8/CNG/48-835/MF20/G 25/1	45 °C	70 °C
579052	16.5T8/CNG/48-840/MF21/G 25/1	45 °C	70 °C
579060	16.5T8/CNG/48-850/MF21/G 25/1	45 °C	70 °C
579284	15T8/COR/48-835/MF20/G/120-347V 25/1	45 °C	70 °C
579292	15T8/COR/48-840/MF21/G/120-347V 25/1	45 °C	70 °C
579300	15T8/COR/48-850/MF21/G/120-347V 25/1	45 °C	70 °C
579672	14.5T8/COR/48-5CCT/MF18/G/DIM 25/1	45 °C	70 °C

