



Create a vintage or modern look while saving money with LED technology

LED Designer Deco

Philips LED Designer Deco lamps allow you to maintain a warm, classic light or a modern, chic effect while providing longer life and energy savings

Benefits

- Light distribution and color which replicates the effect of standard, vintage-style incandescent lamps, or a modern sophisticated tint
- Long life -- lowers maintenance costs by reducing re-lamp frequency
- Excellent color consistency with high color rendering (CRI)

Features

- Integrated compact driver design to achieve a decorative look and feel
- Smooth Dimming
- Instant on
- 15,000 hours rated average life
- Wet location

Application

- Restaurants/Bars
- Lobbies/Reception areas

LED Designer Deco

Versions




LEDbulb CLAF NAM T10 E26
Amber



LEDbulb UFO Others E27 FR



LEDbulb NAM S14 E26 CL




LEDbulb 5,5ST19 VIN 930 E26 CL
G SP D 1PF T20



LEDbulb E26 A50 40W




LEDbulb LATAM6 Tshape E27 FR



LEDbulb E26 G63 40W




LEDbulb E26 T20 40W






LEDbulb ST19 E26 CL

Versions



LEDbulb 6,5ST19 VIN 820 E26
Amber G SP D 1PFT20

Dimensional drawing







Product	D	C
7.5A50/VIN/820/CL/G/E26/amber/SP/DIM 1CT	160 mm	292 mm

Product	D	C
5.5ST19/VIN/950/E26/CL/G/SP D 4/1PF T20	64 mm	137 mm
6.5ST19/VIN/820/E26/Amber/G/SP/D 1PFT20	64 mm	137 mm
8.8ST19/PER/950/CL/G/E26/DIM 1PF T20	64 mm	143 mm

Product	D	C
7.5G63/VIN/820/CL/G/E26/amber/SP/DIM 1CT	200 mm	285 mm

Dimensional drawing





Product	D	C
TBulb LEDBulb 10W E27 6500K W 1CT/6 LAT	200 mm	105 mm

Product	D	C
7.5T20/VIN/820/CL/G/E26/amber/SP/DIM 1CT	65 mm	272 mm

Product	D	C
16UFO/LED/865/FR/P/ND 6/1FB	150 mm	77 mm
16UFO/PER/830/FR/P/E26/ND 4/1PF	150 mm	77 mm
16UFO/PER/850/FR/P/E26/ND 4/1PF	150 mm	77 mm
16UFO/PER/865/FR/P/E26/ND 4/1PF	150 mm	77 mm
26UFO/LED/865/FR/P/ND 6/1FB	200 mm	77 mm
26UFO/PER/830/FR/P/E26/ND 4/1PF	200 mm	77 mm
26UFO/PER/830/FR/P/E26/ND 4/1PF	200 mm	77 mm
26UFO/PER/850/FR/P/E26/ND 4/1PF	200 mm	77 mm
26UFO/PER/865/FR/P/E26/ND 4/1PF	200 mm	77 mm
UFO LEDBulb 15W E27 3000K 230V 1CT/6	150 mm	82 mm
UFO LEDBulb 15W E27 6500K 230V 1CT/6	150 mm	82 mm
UFO LEDBulb 24W E27 3000K 230V 1CT/6	200 mm	82 mm
UFO LEDBulb 24W E27 6500K 230V 1CT/6	200 mm	82 mm

Product	D	C
3.5T10/VIN/820/E26/Amber/G/SP D 4/1PFT20	32 mm	103 mm

Dimensional drawing



Product	D	C
1S14/VIN/827/CL/G/E26/ND 1CT	45 mm	86 mm

Product	D	C
4.5T10/VIN/820/E26/CL/GL/DIM 4/1BC T20	29 mm	190 mm
4.5T10/VIN/820/E26/CL/GL/DIM 4/FBH T20	29 mm	190 mm

Product details



LEDbulb 7,5 820



LEDbulb 7,5 840

General Information	
Nominal lifetime	15,000 hour(s)
Light Technical	
LLMF At End Of Nominal Lifetime (Nom)	70 %

General Information

Order Code	Full Product Name	Cap-Base	Rated	Switching Cycle
			Lifetime (Hours)	
929002987403	3.5T10/VIN/820/E26/ Amber/G/SP D 4/1PFT20	E26	-	20,000
929001971471	UFO LEDBulb 15W E27 3000K 230V 1CT/6	E27	-	50,000
929001971571	UFO LEDBulb 15W E27 6500K 230V 1CT/6	E27	-	50,000
929003082704	1S14/VIN/827/CL/G/E26/ND 1CT	E26	-	20,000
929002988803	5.5ST19/VIN/950/E26/CL/G/SP D 4/1PF T20	E26	-	20,000
929001951533	4.5T10/VIN/820/E26/CL/GL/DI M 4/FBH T20	E26	15,000 hour(s)	20,000
929001951553	4.5T10/VIN/820/E26/CL/GL/DI M 4/1BC T20	E26	-	20,000
929001936413	7.5A50/VIN/820/CL/G/E26/ amber/SP/DIM 1CT	E26	15,000 hour(s)	20,000
929001978811	TBulb LEDBulb 10W E27 6500K W 1CT/6 LAT	E27	-	50,000
929001936313	7.5G63/VIN/820/CL/G/E26/ amber/SP/DIM 1CT	E26	15,000 hour(s)	20,000
929001936513	7.5T20/VIN/820/CL/G/E26/ amber/SP/DIM 1CT	E26	15,000 hour(s)	20,000
929002010553	16UFO/PER/830/FR/P/E26/ND 4/1PF	E26	15,000 hour(s)	50,000
929002010605	16UFO/LED/865/FR/P/ND 6/1FB	E26	15,000 hour(s)	50,000

Order Code	Full Product Name	Cap-Base	Rated	Switching Cycle
			Lifetime (Hours)	
929002010625	16UFO/PER/865/FR/P/E26/ND 4/1PF	E26	15,000 hour(s)	50,000
929002441103	16UFO/PER/850/FR/P/E26/ND 4/1PF	E26	-	50,000
929001971871	UFO LEDBulb 24W E27 3000K 230V 1CT/6	E27	-	50,000
929001971971	UFO LEDBulb 24W E27 6500K 230V 1CT/6	E27	-	50,000
929002296103	8.8ST19/PER/950/CL/G/E26/DI M 1PF T20	E26	-	20,000
929002986903	6.5ST19/VIN/820/E26/ Amber/G/SP/D 1PFT20	E26	-	20,000
929002010703	26UFO/PER/830/FR/P/E26/ND 4/1PF	E26	-	50,000
929002010753	26UFO/PER/830/FR/P/E26/ND 4/1PF	E26	15,000 hour(s)	50,000
929002010805	26UFO/LED/865/FR/P/ND 6/1FB	E26	15,000 hour(s)	50,000
929002010825	26UFO/PER/865/FR/P/E26/ND 4/1PF	E26	15,000 hour(s)	50,000
929002441203	26UFO/PER/850/FR/P/E26/ND 4/1PF	E26	-	50,000

Light Technical

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color Temperature (Nom)	Color rendering index		Color Code	Luminous Flux
				(CRI)			
929002987403	3.5T10/VIN/820/E26/Amber/G/SP D 4/1PFT20	330 degree(s)	2000 K	80		820	225 lm
929001971471	UFO LEDBulb 15W E27 3000K 230V 1CT/6	120 degree(s)	3000 K	80		830	1,250 lm
929001971571	UFO LEDBulb 15W E27 6500K 230V 1CT/6	120 degree(s)	6500 K	80		865	1,700 lm
929003082704	1S14/VIN/827/CL/G/E26/ND 1CT	-	2700 K	80		827	60 lm
929002988803	5.5ST19/VIN/950/E26/CL/G/SP D 4/1PF T20	330 degree(s)	5000 K	90		950	500 lm
929001951533	4.5T10/VIN/820/E26/CL/GL/DIM 4/FBH T20	-	2000 K	80		820	300 lm
929001951553	4.5T10/VIN/820/E26/CL/GL/DIM 4/1BC T20	-	2000 K	80		820	300 lm
929001936413	7.5A50/VIN/820/CL/G/E26/amber/SP/DIM 1CT	330 degree(s)	2000 K	80		820	400 lm
929001978811	TBulb LEDBulb 10W E27 6500K W 1CT/6 LAT	120 degree(s)	6500 K	80		865	1,000 lm
929001936313	7.5G63/VIN/820/CL/G/E26/amber/SP/DIM 1CT	330 degree(s)	2000 K	80		820	400 lm
929001936513	7.5T20/VIN/820/CL/G/E26/amber/SP/DIM 1CT	330 degree(s)	2000 K	80		820	400 lm
929002010553	16UFO/PER/830/FR/P/E26/ND 4/1PF	120 degree(s)	3000 K	80		830	1,150 lm
929002010605	16UFO/LED/865/FR/P/ND 6/1FB	120 degree(s)	6500 K	80		865	1,200 lm
929002010625	16UFO/PER/865/FR/P/E26/ND 4/1PF	120 degree(s)	6500 K	80		865	1,200 lm
929002441103	16UFO/PER/850/FR/P/E26/ND 4/1PF	120 degree(s)	5000 K	80		850	1,200 lm
929001971871	UFO LEDBulb 24W E27 3000K 230V 1CT/6	120 degree(s)	3000 K	80		830	2,715 lm
929001971971	UFO LEDBulb 24W E27 6500K 230V 1CT/6	120 degree(s)	6500 K	80		865	2,715 lm
929002296103	8.8ST19/PER/950/CL/G/E26/DIM 1PF T20	280 degree(s)	5000 K	90		950	800 lm
929002986903	6.5ST19/VIN/820/E26/Amber/G/SP/D 1PFT20	330 degree(s)	2000 K	80		820	400 lm
929002010703	26UFO/PER/830/FR/P/E26/ND 4/1PF	120 degree(s)	3000 K	80		830	1,950 lm

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color Temperature (Nom)	Color rendering index		
				(CRI)	Color Code	Luminous Flux
929002010753	26UFO/PER/830/FR/P/E26/ND 4/1PF	120 degree(s)	3000 K	80	830	1,950 lm
929002010805	26UFO/LED/865/FR/P/ND 6/1FB	120 degree(s)	6500 K	80	865	2,050 lm
929002010825	26UFO/PER/865/FR/P/E26/ND 4/1PF	120 degree(s)	6500 K	80	865	2,050 lm
929002441203	26UFO/PER/850/FR/P/E26/ND 4/1PF	120 degree(s)	5000 K	80	850	2,050 lm

Operating and Electrical

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Starting Time (Nom)	Wattage Equivalent
929002987403	3.5T10/VIN/820/E26/Amber/G/SP D 4/1PFT20	60 Hz	60 Hz	3.5 W	0.5 s	25 W
929001971471	UFO LEDBulb 15W E27 3000K 230V 1CT/6	50 to 60 Hz	50 to 60 Hz	15 W	0.45 s	85 W
929001971571	UFO LEDBulb 15W E27 6500K 230V 1CT/6	50 to 60 Hz	50 to 60 Hz	15 W	0.5 s	100 W
929003082704	1S14/VIN/827/CL/G/E26/ND 1CT	50 to 60 Hz	50 to 60 Hz	1 W	0.5 s	10 W
929002988803	5.5ST19/VIN/950/E26/CL/G/SP D 4/1PF T20	60 Hz	60 Hz	5.5 W	0.5 s	60 W
929001951533	4.5T10/VIN/820/E26/CL/GL/DIM 4/FBH T20	60 Hz	60 Hz	4.5 W	0.5 s	40 W
929001951553	4.5T10/VIN/820/E26/CL/GL/DIM 4/1BC T20	60 Hz	60 Hz	4.5 W	0.5 s	40 W
929001936413	7.5A50/VIN/820/CL/G/E26/amber/SP/DIM 1CT	50 to 60 Hz	50 to 60 Hz	7.5 W	0.5 s	40 W
929001978811	TBulb LEDBulb 10W E27 6500K W 1CT/6 LAT	50 to 60 Hz	50 to 60 Hz	10 W	0.5 s	75 W
929001936313	7.5G63/VIN/820/CL/G/E26/amber/SP/DIM 1CT	50 to 60 Hz	50 to 60 Hz	7.5 W	0.5 s	40 W
929001936513	7.5T20/VIN/820/CL/G/E26/amber/SP/DIM 1CT	50 to 60 Hz	50 to 60 Hz	7.5 W	0.5 s	40 W
929002010553	16UFO/PER/830/FR/P/E26/ND 4/1PF	50 to 60 Hz	50 to 60 Hz	16 W	0.5 s	75 W
929002010605	16UFO/LED/865/FR/P/ND 6/1FB	50 to 60 Hz	50 to 60 Hz	16 W	0.5 s	75 W
929002010625	16UFO/PER/865/FR/P/E26/ND 4/1PF	50 to 60 Hz	50 to 60 Hz	16 W	0.5 s	75 W
929002441103	16UFO/PER/850/FR/P/E26/ND 4/1PF	50 to 60 Hz	50 to 60 Hz	16 W	0.5 s	75 W
929001971871	UFO LEDBulb 24W E27 3000K 230V 1CT/6	50 to 60 Hz	50 to 60 Hz	24 W	0.5 s	150 W
929001971971	UFO LEDBulb 24W E27 6500K 230V 1CT/6	50 to 60 Hz	50 to 60 Hz	24 W	0.5 s	150 W
929002296103	8.8ST19/PER/950/CL/G/E26/DIM 1PF T20	60 Hz	60 Hz	8.8 W	0.5 s	40 W
929002986903	6.5ST19/VIN/820/E26/Amber/G/SP/D 1PFT20	60 Hz	60 Hz	6.5 W	0.5 s	60 W
929002010703	26UFO/PER/830/FR/P/E26/ND 4/1PF	50 to 60 Hz	50 to 60 Hz	26 W	0.5 s	125 W
929002010753	26UFO/PER/830/FR/P/E26/ND 4/1PF	50 to 60 Hz	50 to 60 Hz	26 W	0.5 s	125 W
929002010805	26UFO/LED/865/FR/P/ND 6/1FB	50 to 60 Hz	50 to 60 Hz	26 W	0.5 s	125 W
929002010825	26UFO/PER/865/FR/P/E26/ND 4/1PF	50 to 60 Hz	50 to 60 Hz	26 W	0.5 s	125 W
929002441203	26UFO/PER/850/FR/P/E26/ND 4/1PF	50 to 60 Hz	50 to 60 Hz	26 W	0.5 s	125 W

Temperature

Order Code	Full Product Name	Ambient temperature range	T-Case Maximum (Nom)
929002987403	3.5T10/VIN/820/E26/Amber/G/SP D 4/1PFT20	-20 °C to 45 °C	-
929001971471	UFO LEDBulb 15W E27 3000K 230V 1CT/6	-	72 °C
929001971571	UFO LEDBulb 15W E27 6500K 230V 1CT/6	-	72 °C
929003082704	1S14/VIN/827/CL/G/E26/ND 1CT	-	26 °C
929002988803	5.5ST19/VIN/950/E26/CL/G/SP D 4/1PF T20	-20 °C to 45 °C	-
929001951533	4.5T10/VIN/820/E26/CL/GL/DI M 4/FBH T20	-	55 °C

Order Code	Full Product Name	Ambient temperature range	T-Case Maximum (Nom)
929001951553	4.5T10/VIN/820/E26/CL/GL/DI M 4/1BC T20	-	55 °C
929001936413	7.5A50/VIN/820/CL/G/E26/amber/SP/DIM 1CT	-20 °C to 40 °C	45 °C
929001978811	TBulb LEDBulb 10W E27 6500K W 1CT/6 LAT	-	-
929001936313	7.5G63/VIN/820/CL/G/E26/amber/SP/DIM 1CT	-20 °C to 40 °C	45 °C
929001936513	7.5T20/VIN/820/CL/G/E26/amber/SP/DIM 1CT	-20 °C to 40 °C	45 °C
929002010553	16UFO/PER/830/FR/P/E26/ND 4/1PF	-20 °C to 45 °C	75 °C

Order Code	Full Product Name	Ambient temperature range	T-Case Maximum (Nom)
929002010605	16UFO/LED/865/FR/P/ND 6/1FB	-	75 °C
929002010625	16UFO/PER/865/FR/P/E26/ND 4/1PF	-20 °C to 45 °C	75 °C
929002441103	16UFO/PER/850/FR/P/E26/ND 4/1PF	-	75 °C
929001971871	UFO LEDBulb 24W E27 3000K 230V 1CT/6	-	68 °C
929001971971	UFO LEDBulb 24W E27 6500K 230V 1CT/6	-	68 °C
929002296103	8.8ST19/PER/950/CL/G/E26/DI M 1PF T20	-	60 °C

Controls and Dimming

Order Code	Full Product Name	Dimmable
929002987403	3.5T10/VIN/820/E26/Amber/G/SP D 4/1PFT20	Only with specific dimmers
929001971471	UFO LEDBulb 15W E27 3000K 230V 1CT/6	No
929001971571	UFO LEDBulb 15W E27 6500K 230V 1CT/6	No
929003082704	1S14/VIN/827/CL/G/E26/ND 1CT	No
929002988803	5.5ST19/VIN/950/E26/CL/G/SP D 4/1PF T20	Only with specific dimmers
929001951533	4.5T10/VIN/820/E26/CL/GL/DIM 4/FBH T20	Yes
929001951553	4.5T10/VIN/820/E26/CL/GL/DIM 4/IBC T20	Yes
929001936413	7.5A50/VIN/820/CL/G/E26/amber/SP/DIM 1CT	Only with specific dimmers
929001978811	TBulb LEDBulb 10W E27 6500K W 1CT/6 LAT	No
929001936313	7.5G63/VIN/820/CL/G/E26/amber/SP/DIM 1CT	Only with specific dimmers
929001936513	7.5T20/VIN/820/CL/G/E26/amber/SP/DIM 1CT	Only with specific dimmers

Mechanical and Housing

Order Code	Full Product Name	Bulb Finish	Bulb Shape
929002987403	3.5T10/VIN/820/E26/Amber/G/SP D 4/1PFT20	Amber	T-10
929001971471	UFO LEDBulb 15W E27 3000K 230V 1CT/6	Frosted	Others
929001971571	UFO LEDBulb 15W E27 6500K 230V 1CT/6	Frosted	Others
929003082704	1S14/VIN/827/CL/G/E26/ND 1CT	Clear	S-14
929002988803	5.5ST19/VIN/950/E26/CL/G/SP D 4/1PF T20	Clear	ST19
929001951533	4.5T10/VIN/820/E26/CL/GL/DIM 4/FBH T20	Amber	T-10
929001951553	4.5T10/VIN/820/E26/CL/GL/DIM 4/IBC T20	Amber	T-10
929001936413	7.5A50/VIN/820/CL/G/E26/amber/SP/DIM 1CT	Amber	A50
929001978811	TBulb LEDBulb 10W E27 6500K W 1CT/6 LAT	Frosted	T-shape

Order Code	Full Product Name	Ambient temperature range	T-Case Maximum (Nom)
929002986903	6.5ST19/VIN/820/E26/ Amber/G/SP/D 1PFT20	-20 °C to 45 °C	-
929002010703	26UFO/PER/830/FR/P/E26/ND 4/1PF	-	72 °C
929002010753	26UFO/PER/830/FR/P/E26/ND 4/1PF	-20 °C to 45 °C	72 °C
929002010805	26UFO/LED/865/FR/P/ND 6/1FB	-	72 °C
929002010825	26UFO/PER/865/FR/P/E26/ND 4/1PF	-20 °C to 45 °C	72 °C
929002441203	26UFO/PER/850/FR/P/E26/ND 4/1PF	-	72 °C

Order Code	Full Product Name	Dimmable
929002010553	16UFO/PER/830/FR/P/E26/ND 4/1PF	No
929002010605	16UFO/LED/865/FR/P/ND 6/1FB	No
929002010625	16UFO/PER/865/FR/P/E26/ND 4/1PF	No
929002441103	16UFO/PER/850/FR/P/E26/ND 4/1PF	No
929001971871	UFO LEDBulb 24W E27 3000K 230V 1CT/6	No
929001971971	UFO LEDBulb 24W E27 6500K 230V 1CT/6	No
929002296103	8.8ST19/PER/950/CL/G/E26/DIM 1PF T20	Yes
929002986903	6.5ST19/VIN/820/E26/Amber/G/SP/D 1PFT20	Only with specific dimmers
929002010703	26UFO/PER/830/FR/P/E26/ND 4/1PF	No
929002010753	26UFO/PER/830/FR/P/E26/ND 4/1PF	No
929002010805	26UFO/LED/865/FR/P/ND 6/1FB	No
929002010825	26UFO/PER/865/FR/P/E26/ND 4/1PF	No
929002441203	26UFO/PER/850/FR/P/E26/ND 4/1PF	No






Order Code	Full Product Name	Bulb Finish	Bulb Shape
929001936313	7.5G63/VIN/820/CL/G/E26/amber/SP/DIM 1CT	Amber	G63
929001936513	7.5T20/VIN/820/CL/G/E26/amber/SP/DIM 1CT	Amber	T20
929002010553	16UFO/PER/830/FR/P/E26/ND 4/1PF	Frosted	Others
929002010605	16UFO/LED/865/FR/P/ND 6/1FB	Frosted	Others
929002010625	16UFO/PER/865/FR/P/E26/ND 4/1PF	Frosted	Others
929002441103	16UFO/PER/850/FR/P/E26/ND 4/1PF	Frosted	Others
929001971871	UFO LEDBulb 24W E27 3000K 230V 1CT/6	Frosted	Others
929001971971	UFO LEDBulb 24W E27 6500K 230V 1CT/6	Frosted	Others
929002296103	8.8ST19/PER/950/CL/G/E26/DIM 1PF T20	Clear	ST19











Order Code	Full Product Name	Bulb	
		Bulb Finish	Shape
929002986903	6.5T19/VIN/820/E26/Amber/G/SP/D 1PFT20	Amber	ST19
929002010703	26UFO/PER/830/FR/P/E26/ND 4/1PF	Frosted	Others
929002010753	26UFO/PER/830/FR/P/E26/ND 4/1PF	Frosted	Others

Order Code	Full Product Name	Bulb	
		Bulb Finish	Shape
929002010805	26UFO/LED/865/FR/P/ND 6/1FB	Frosted	Others
929002010825	26UFO/PER/865/FR/P/E26/ND 4/1PF	Frosted	Others
929002441203	26UFO/PER/850/FR/P/E26/ND 4/1PF	Frosted	Others

Approval and Application

Order Code	Full Product Name	Energy Consumption
		kWh/1000 h
929002987403	3.5T10/VIN/820/E26/Amber/G/SP D 4/1PFT20	-
929001971471	UFO LEDBulb 15W E27 3000K 230V 1CT/6	15 kWh
929001971571	UFO LEDBulb 15W E27 6500K 230V 1CT/6	15 kWh
929003082704	1S14/VIN/827/CL/G/E26/ND 1CT	-
929002988803	5.5T19/VIN/950/E26/CL/G/SP D 4/1PF T20	-
929001951533	4.5T10/VIN/820/E26/CL/GL/DIM 4/FBH T20	- kWh
929001951553	4.5T10/VIN/820/E26/CL/GL/DIM 4/1BC T20	- kWh
929001936413	7.5A50/VIN/820/CL/G/E26/amber/SP/DIM 1CT	-
929001978811	TBulb LEDBulb 10W E27 6500K W 1CT/6 LAT	-
929001936313	7.5G63/VIN/820/CL/G/E26/amber/SP/DIM 1CT	-
929001936513	7.5T20/VIN/820/CL/G/E26/amber/SP/DIM 1CT	-
929002010553	16UFO/PER/830/FR/P/E26/ND 4/1PF	-
929002010605	16UFO/LED/865/FR/P/ND 6/1FB	- kWh
929002010625	16UFO/PER/865/FR/P/E26/ND 4/1PF	-
929002441103	16UFO/PER/850/FR/P/E26/ND 4/1PF	- kWh
929001971871	UFO LEDBulb 24W E27 3000K 230V 1CT/6	24 kWh
929001971971	UFO LEDBulb 24W E27 6500K 230V 1CT/6	24 kWh
929002296103	8.8ST19/PER/950/CL/G/E26/DIM 1PF T20	- kWh
929002986903	6.5ST19/VIN/820/E26/Amber/G/SP/D 1PFT20	-
929002010703	26UFO/PER/830/FR/P/E26/ND 4/1PF	- kWh
929002010753	26UFO/PER/830/FR/P/E26/ND 4/1PF	-
929002010805	26UFO/LED/865/FR/P/ND 6/1FB	- kWh
929002010825	26UFO/PER/865/FR/P/E26/ND 4/1PF	-
929002441203	26UFO/PER/850/FR/P/E26/ND 4/1PF	- kWh





LED Designer Deco

