



Competitive industry solution with well accepted look & feel

GreenPerform Highbay G4

Following the success of GreenPerform Highbay families, GreenPerform Highbay G4 is continuously exploring a better price & performance balance. The product family offers wide product ranges, competitive enough SPEC with long term quality & reliability, covering most of the potential industrial applications.

Benefits

- Strong energy saving story
- Better & easier on site calibration
- Robust & Reliable with a long service lifetime
- Various application requirements satisfied with complete product family

Features

- System efficacy 135lm/W $\pm 10\%$
- Round light exit window for better & easier on site calibration
- Long service lifetime 50Khrs L70B50 @Ta 35°C
- Complete lumen package offering
- Multiple optics available: WB & NB
- Suitable for hook, pipe, bracket mounting

Application

- General manufacturing
- Warehouses and logistical centers
- Exhibition halls and high ceiling lounges