



# Full Range Recessed Up-light to Make Your Space Distinctive

## UNIn-ground

UNIn-ground family provide a completed range of up-lights in terms of wattage, beam angle, color temperature, etc. It is to make your space distinctive with more safety and convenience as well. Compact and robust design with aluminum housing, waterproof connectors are all for ensuring long-lasting operation without your more caring after installation. Waterproof connector is to give more ease to installation and save your installation cost. Apart from high-quality white light, RGB (and mono RGB) are available with DMX512 decoder built-in side.

### Benefits

- Easy to opt
- Quick installation
- Long lifespan
- Robust design for severe conditions

### Features

- wide range of wattage from 1W to 36W
- more options on light beam angle
- warm white is standard and neutral white, RGB and mono RGB is customized
- compact design and lower height of fittings
- IK67, IP67 rated, pass 20KN static load and 500hrs salty spray test passed
- working temperature -40°C to +50°C

### Application

- Public spaces
- Vertical architectural surfaces
- Plaza ground