



Simple, easy, convenient

FCX LED High Bay

LED Value high bay luminaires make it so easy for you to bring your commercial or industrial space into the future. With its low profile and durable design, you might overlook the efficiency and great price, but take a second look. The Value high bay really has it all. Ideal for your mid- to high ceiling applications, this sturdy luminaire comes in two sizes, with lumen outputs up to 22,000 and standard 0-10V dimming. Take the easy route to your next lighting upgrade, with the Value high bay.

Benefits

- Simple form
- Convenient specification
- Ease of installation
- Ease of maintenance

Features

- Multiple lumen options
- Standard 0-10V dimming
- Simple mounting method

Application

- Manufacturing
- Warehouses

FCX LED High Bay

Versions

