



The new Philips tri-colour batten offers exceptional value. It is perfect for your everyday lighting installations.

Available in two standard sizes, it has options of 3 colour temperatures and 2 wattages to provide flexibility to the customer.

Smartbright CCT/Wattage Tunable Waterproof batten

Smartbright CCT/Wattage Tunable Waterproof batten

The new SmartBright Tri Colour Waterproof Batten provides flexibility the customer to choose from 3 colour temperatures and 2 wattages before installation, to suit specific needs.

Benefits

- Tri-colour, dual wattage selectable
- 50,000 hours life
- Multi-purpose weatherproof design with IP65/IK08 rating
- 5 year warranty

Features

- Three colour temperatures and dual-power settings – One device for many applications
- IP65/IK08 – Water and dustproof. For all outdoor applications
- Reliable with a long service life of 50,000 hours L70
- 5-year warranty

Application

- Parking Garages
- Factories
- Correctional facilities
- Underpasses
- Airports

Versions



Smartbright CCT/Wattage Tunable Waterproof batten

-	
Driver failure rate at 5,000 hours	0.003 %
Application Conditions	
Ambient temperature range	-20 to +40 °C
Maximum dimming level	Not applicable
Approval and Application	
Mech. impact protection code	IK08
Ingress protection code	IP65
Controls and Dimming	
Dimmable	No
Operating and Electrical	
Input Voltage	220 to 240 V
General Information	
Beam angle of light source	120 °
CE mark	-
Protection class IEC	Safety class I (I)
Optical cover/lens type	PC
Driver included	Yes
ENEC mark	-
Flammability mark	NO
Glow-wire test	650/30
Light source replaceable	No
Number of gear units	1 unit
Optic type	120
Initial Performance (IEC Compliant)	
Initial chromaticity	0.38;0.38
Init. Corr. Colour Temperature	- K
Init. Colour rendering index	>80
Initial LED luminaire efficacy	100 lm/W
Luminous flux tolerance	+/-10%
Mechanical and Housing	
Colour	Grey
Over Time Performance (IEC Compliant)	
Median useful life L80B50	44000 h
Median useful life L90B50	21000 h

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial luminous flux	Initial input power
911401821680	WT067C SWT SCCT LED L600 PSU AU	2000 lm	20 W
911401821780	WT067C SWT SCCT LED L1200 PSU AU	4000 lm	40 W

Smartbright CCT/Wattage Tunable Waterproof batten

