



**The new Smartbright slim panel offers customer excellent solution for their lighting needs. It is durable, energy efficient and comes with 3 years warranty.**

### **SmartBright Slim panel KR**

The new Philips Smartbright slim panel offers exceptional value. It is Perfect for your everyday ceiling lighting installations. It is available in 3 standard sizes and 2 different CCT options to suit your need.

#### **Benefits**

- 25K hour life, 3 Years warranty
- Energy efficiency: 90 Lm/Watt
- 3 sizes and 2 CCT option

# SmartBright Slim panel KR

## Features

- 25000 hr life, 3 Years warranty
- $Pst < 1.0$  ,  $SVM < 1.6$  CRI 80
- Class I, IP20/IK02
- Surge protection: 1KV/2KV
- CRI 80

## Application

- Offices
- Hospitality
- Retail

## Versions








1X4 Standard



1x4 standard

## Dimensional drawing



SmartBright Slim panel KR

General Information	
Driver included	Yes
Light Technical	
Optical cover/lens type	Polystyrene bowl/ cover prismatic
Color rendering index (CRI)	>80
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Temperature	
Ambient temperature range	-10 to +40 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Housing Color	White
Approval and Application	
CE mark	-
Protection class IEC	Safety class I
Mech. impact protection code	IK02
Ingress protection code	IP20
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Over Time Performance (IEC Compliant)	
Driver failure rate at 5000 h	0.01 %

Light Technical

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	
		Temperature (Nom)	(rated) (Nom)	Luminous Flux
911401746902	RC091V LED45S/857 PSU W32L128 KR	5700 K	90 lm/W	4,500 lumen
911401746882	RC091V LED45S/840 PSU W32L128 KR	4000 K	90 lm/W	4,500 lumen
911401746872	RC091V LED45S/840 PSU W64L64 KR	4000 K	90 lm/W	4,500 lumen
911401746892	RC091V LED45S/857 PSU W64L64 KR	5700 K	90 lm/W	4,500 lumen
911401746912	RC091V LED20S/840 PSU W32L64 KR	4000 K	80 lm/W	2,000 lumen
911401746922	RC091V LED20S/857 PSU W32L64 KR	5700 K	80 lm/W	2,000 lumen

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401746902	RC091V LED45S/857 PSU W32L128 KR	50 W
911401746882	RC091V LED45S/840 PSU W32L128 KR	50 W
911401746872	RC091V LED45S/840 PSU W64L64 KR	50 W

Order Code	Full Product Name	Power Consumption
911401746892	RC091V LED45S/857 PSU W64L64 KR	50 W
911401746912	RC091V LED20S/840 PSU W32L64 KR	25 W
911401746922	RC091V LED20S/857 PSU W32L64 KR	25 W

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
911401746902	RC091V LED45S/857 PSU W32L128 KR	857 daylight
911401746882	RC091V LED45S/840 PSU W32L128 KR	840 neutral white
911401746872	RC091V LED45S/840 PSU W64L64 KR	840 neutral white

Order Code	Full Product Name	Initial chromaticity
911401746892	RC091V LED45S/857 PSU W64L64 KR	857 daylight
911401746912	RC091V LED20S/840 PSU W32L64 KR	840 neutral white
911401746922	RC091V LED20S/857 PSU W32L64 KR	857 daylight

## SmartBright Slim panel KR

