



# A reliable solution for tunnel and underpass

## TunnelView LED Medium (TULM)

Lumec TunnelView tunnel/underpass luminaires provide seamless replacement of existing HID luminaires. This fixture is available in three sizes, offers multiple lumen packages, and a complete array of optical distributions, making it an outstanding solution for all types of tunnel and underpass applications. Includes Service Tag, Signify's innovative way to provide assistance throughout the life of the product.

### Benefits

- Rugged design optimized to withstand harsh environments
- Sleek profile preserves headroom in Tunnels
- Light weight and installer friendly

### Features

- Three sizes for application flexibility
- Nine optical distributions for maximum versatility
- 2700K, 3000K, or 4000K Color temperatures
- Extensive mounting options from fixed or adjustable to swivel
- Controls options: DALI, Sensor Ready, Dimming

### Application

- Tunnel
- Road and Street
- Underpass

## TunnelView LED Medium (TULM)

### Versions

