



TubeLine LED - Optimized comfort in a linear form

TubeLine LED (TBL)

Fluorescent linear lighting has traditionally been the preferred choice for customers demanding a high level of visual comfort. With excellent lighting uniformity on the road and walls, perfect visual guidance and high color recognition, linear lighting offers the driver superior lighting quality and safety. With TubeLine, the same lighting quality can be achieved but with the advantages of LED technology. TubeLine is a state-of-the-art LED tunnel luminaire which offers all the benefits of linear lighting. With the latest LED technology, linear lighting has never been more achievable within the constraints of limited budgets.

Benefits

- Optimal traffic flow due to increased visual comfort and safety compared to point-source lighting
- Quick return on investment
- Flexible, easy-to-install solution

Features

- Robust, corrosion-resistant extruded aluminum design
- Standard length 2 meter
- Smooth design, easy to clean
- Remote driver designed to prevent lane closures
- Lumen packages up to 18,000 lm
- Flexible mounting and connectivity
- Compatible with most Tunnel Lighting controls

Application

- Tunnel
- Underpass

TubeLine LED (TBL)

Versions

