



Compact Design..... Sleek yet Powerful

GreenPerform Sleek

Green Perform Sleek luminaire is designed for low dept false ceiling. Slim design with non-integral driver enables installation into low height false ceilings of different thickness and materials. Narrow rim semi-deep recessed design gives high quality lighting for designer ceilings. Highly efficient Electronic driver with high performance LED's ensures the longer life & high performance in this product category. Wide range of CCT's & Lumen packs suitable for various application.

Benefits

- Low Height: Suitable for all types of low height designer false ceiling
- Non-Integral Driver: Ensures long luminaire life & easy installation / serviceability
- Efficacy: Best in class system level efficacy of > 110 lm/W
- Continuous Usage: PDC housing ensures long LED life under continuous usage
- Greater energy savings help end users to reduce ROI

Features

- Low Height Recess Mounted Downlighter Range in Circular form-factor
- Available in multiple Lumen Packs: 600/800/1000/1200 and 1500 Lumen
- High efficacy of > 110 lm/w - Best in class in its category
- Available in three Color Temperature – 3000K, 4000K & 6500K
- Robust Design with Pressure Diecast aluminum Housing, ensuring long life
- 2.5 KV Surge Protection

Application

- Modern Workspaces
- Institutions
- Small format Retail outlets
- Hospital
- High end Villa's

GreenPerform Sleek

Versions



DN295B

Product details

DN295B



DN295B

