



The decorative, easy to install LED replacement batten

The FastSet LED decorative batten is the perfect 1:1 replacement for conventional battens. With a wide profile and easy installation it easily fits into all different indoor applications. FastSet can be installed as a standalone luminaire or in a line configuration.

Features & benefits

- One luminaire which is suitable for standalone or line configuration
- Good light quality and comfort thanks to its wide distribution
- With three push-in terminal blocks to choose from and two different mounting methods it's a breeze to install
- IP44 rating makes the FastSet resilient against moisture and dust
- Three year warranty


Product data

Model	FastSet Surface Mount (SM150)	
Type	LED48	LED60
Equivalent of	2x36W Fluorescent	2x58W Fluorescent
Power	45W	55W
System Lumen	4800lm	6000lm
Power factor	>0.9	
Type	Fixed output (PSU)	
Diffuser	Ribbed Opal Diffuser	
Electrical Class	Class I	
Input Voltage	220V-240V, 50/60Hz	
CCT	3000K (WW) and 4000K (NW)	
CRI	>80	
Beam Angle	116°	
Operating Temperature	0°C – 35°C	
Lifetime (L70)*	50,000 hours	
IP/ IK Rating	IP44/IK03	
Mounting Type	Direct to Ceiling or via Mounting clips, suitable also for Wall Mount	
Electrical Connection	End and rear access point, through-wiring, 3 x Push in terminal blocks	
Housing Colour	RAL 9003	
Material	Diffuser: PC	
	Housing: Metal housing	
Application	Office, Education, Carparks, Laboratory, Kitchens and Stairwells	


*When a new fitting reaches 70% of full potential

Dimensions

FastSet Surface Mounted SM150C L1160



FastSet Surface Mounted SM150C L1440



Order placement information

12NC	Descriptions	Specification
912401483057	SM150C LED48S/840 PSU TW3 PI5 L1160	45W, 4800lm, 4000K, fixed output, 4ft
912401483058	SM150C LED48S/830 PSU TW3 PI5 L1160	45W, 4800lm, 3000K, fixed output, 4ft
912401483059	SM150C LED60S/840 PSU TW3 PI5 L1440	55W, 6000lm, 4000K, fixed output, 5ft
912401483060	SM150C LED60S/830 PSU TW3 PI5 L1440	55W, 6000lm, 3000K, fixed output, 5ft

© 2017 Koninklijke Philips N.V.
All rights reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner.
The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent or other industrial or intellectual property rights.

Version: July 2018



Philips Lighting New Zealand
Level 3, 123 Carlton Gore Road
Newmarket, Auckland 1023
New Zealand
Ph: 0800 454 448 / 0800 4 LIGHT
connected.nz@philips.com
www.philips.co.nz/lighting