




Ordering Information

Catalog No.	Finish	Mounting	Lamps
22MW4WH 22MW4BK 22MW4AL	Matte White Matte Black Metallic Aluminum	All Lytespan Track Systems. Does not mount on ProSpec Track.	12V 50W Max. T4 2-pin GY6.35 base lamp. (Clear Only) Use Philips or Sylvania lamps only, must be 1 3/4" MOL. Transverse or C-6 filament recommended.

Features

- Transformer:** Class two electronic transformer for 12v halogen lamps
- Track Attachment Fitting:** Molded polycarbonate; rotates into track
- Brass Contact:** Extends for connection to second circuit
(Advent Lytespan track only)
- Horizontal Pivot:** Wireless stem profile with infinite horizontal rotation
- Vertical Pivot:** 0-90° vertical adjustment
- Socket:** Bi-pin multipoint contact low voltage halogen socket
- Housing:** Die cast aluminum
- Smoothing Lens:** Meets UL standards for use with unshielded lamps

Finish

All Painted finishes are baked enamel.

Dimming

Use only dimmers specifically designed for use with electronic transformers.
Low voltage fixtures may produce audible sound when dimmed.

Accessories

- Accessory Holder:** None
Accessories: None
Lens: None
Louver: None
Snoot Accessory: None


Labels

UL, cUL

Job Information	Type:
Job Name:	
Cat. No.:	
Lamp(s):	
Notes:	

Lighting Data

Footcandles on wall:



Lamp Information:

50W 12V T4

Lumens: 950

Rated Avg. life: 2,000 hrs.

EXAMPLE: With track located 2' from wall and multiple units spaced 3' on center and aimed 50° from horizontal, the illumination on wall 3' from ceiling will be 25 f.c. beneath units and 24 f.c. between units.

Footcandles on Wall

Track 2 Feet From Wall

Single Unit

		0'	1'	2'	3'	4'
	Beam Center					
1'		51	36	7	1	1
2'		45	30	12	2	1
3'		19	15	9	3	1
4'		8	7	5	3	1
5'		4	4	3	2	1
6'		2	2	2	2	1
7'		1	1	1	1	1
8'		1	1	1	1	1

Multiple Units

	2'	3'	4'
1'	71 78 70	58 45 58	56 15 56
2'	72 67 71	52 44 52	49 24 49
3'	38 35 37	25 24 25	20 18 20
4'	20 18 19	13 13 13	10 10 10
5'	12 11 11	8 8 8	6 6 6
6'	8 8 7	6 5 6	4 4 4
7'	5 5 5	4 4 4	3 3 3
8'	4 4 3	3 3 3	2 2 2

Track 3 Feet From Wall

Single Unit

		0'	1'	2'	3'	4'
	Beam Center					
1'		23	21	11	3	1
2'		23	17	11	4	1
3'		20	16	11	5	2
4'		12	10	8	5	2
5'		6	5	4	3	2
6'		3	3	3	2	2
7'		2	2	2	2	1
8'		1	1	1	1	1

Multiple Units

	3'	4'	5'
1'	28 33 28	24 23 24	23 14 23
2'	31 31 31	25 22 25	23 16 23
3'	32 30 32	24 23 24	22 17 22
4'	22 21 23	17 16 17	14 13 14
5'	13 13 14	10 10 10	8 8 8
6'	9 8 9	7 6 7	5 5 5
7'	6 6 6	5 5 5	4 4 4
8'	4 5 4	4 4 4	3 3 3

Job Information

Type: