

PHILIPS

Day-Brite

CFI

Recessed

EvoGrid LED

Dimmer compatibility list

©2015 Koninklijke Philips N.V. All rights reserved.
Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.

Philips Lighting North America Corporation
200 Franklin Square Drive, Somerset, NJ 08873
Tel. 855-486-2216

Imported by: Philips Lighting
A division of Philips Electronics Ltd.
281 Hillmount Road, Markham, ON, Canada L6C 2S3
Tel. 800-668-9008

EvoGrid_Dimmer_Comp_List 08/15
www.philips.com/luminaires

Brand	Model	Dimmer type	Neutral wire	Wattage /VA	Input voltage	Min. power (W)
Philips Mark 10 dimmer						
Occuswitch Wireless	LRC1730/00	Mark 10 wireless dimmer	Neutral	800W/1600W	120/277V	80W for 277V
Sunrise	SR600MK10120	Mark 10	Neutral	600VA	120V	
Sunrise	SR600MK10277	Mark 10	Neutral	600VA	277V	
Sunrise	SR1000MK10120	Mark 10	Neutral	1000VA	120V	
Sunrise	SR1200MK10277	Mark 10	Neutral	1200VA	277V	
Multiset Pro	MSP600EB	Mark 10	Neutral	600VA	120V	
Multiset Pro	MHP1000EB	Mark 10	Neutral	1000W	120V	
Multiset Pro	MHP1500EB	Mark 10	Neutral	1500W	120V	
Philips Phase cut dimming amplifier						
Occuswitch Classic	LCU2425/00	Mark 10 power extender	Neutral	1920W	120V	
Occuswitch Classic	LCU2430/00	Mark 10 power extender	Neutral	3000W	277V	
Leviton phase cut dimmer						
Renoir II	AWSMT-XAW	Mark 10	Neutral	600/1150/1385W	120/230/277 V	80W/120W
Renoir II	AWSMT-XBW	Mark 10	Neutral	1000/1917/2308W	120/230/277 V	80W/120W
Renoir II	AWSMT-XCW	Mark 10	Neutral	1500/2875/3463W	120/230/277 V	80W/120W
Renoir II	AWSMT-XDW	Mark 10	Neutral	1920/3680/4432W	120/230/277 V	80W/120W
Vizia+	VPX10-1LZ	Mark 10	Neutral	1000VA	120V	80W@120V
Vizia+	VPX12-7LZ	Mark 10	Neutral	1200VA	277V	80W@277V
Illumatech	IPX06-10Z	Mark 10	No	600VA	120V	
Illumatech	IPX06-70Z	Mark 10	No	600VA	277V	80W@277V
Illumatech	IPX10-10Z	Mark 10	No	1000VA	120V	
Illumatech	IPX12-70Z	Mark 10	No	1200VA	277V	80W@277V
Sureslide	6674	LED/CFL/Incandescent	No	150/150/600W	120V	
Renoir	2666-31	Mark 10	No	900W/1200VA	120V	80W@120V
Renoir	2666-37	Mark 10	No	900W/1200VA	277V	80W@277V
D4200	D4206	station, 6dimmers, Mark 10, Incandescent	Neutral	6x1000W	120V	
Wattstopper mark 10 dimmer						
	WD170	Mark 10, Occupancy sensing	No	500W	120V	
	WD180	Mark 10, Occupancy sensing	No	500W	277V	
	ADFM-8A	Mark 10	No		120V	
	ADFM277-10A	Mark 10	No		277V	80W@277V
Miro	DCD267	Universal Mark 10 incandescent	Neutral	500W	120V	
Miro wireless	DRD4	universal Mark 10 incandescent	Neutral	500W	120V	
DLM	LMRC-222	Universal Mark 10 incandescent	Neutral	2x1920W/ 4432W	120/277V	80W/80W
Lutron mark 10 dimmer						
Nova	NFTU-5A	Mark 10 (Tu-wire)	No		120V	
Spacer System	SPSFTU-5A	Mark 10 (Tu-wire)	Neutral		120V	
Diva	DVFTU-5A3P	Mark 10 (Tu-wire)	No		120V	
Grafik Eye QS	QSGRJ-X++P++	Mark 10 (Tu-wire)	Neutral	800W/1200W	120V	
Dimming Amplifier	HP-2	Mark 10	Neutral		120V/277V	
Nova T	NTFTU-5A-277	Mark 10 (Tu-wire)	Neutral		277V	