


With its slim, uncluttered design, Sync is the epitome of compact style. Sync offers true direct/indirect lighting distribution and luminous aesthetics with exceptional glare control.

Ordering guide



Mounting Hardware Mount Type Suspension Length Consult separate mounting spec sheet for mount type options Distance from ceiling to top of luminaire in inches **Endcaps** Integrated Controls Please indicate with check mark. Response Daylight Single Zone (DS)







^{*} Nominal values within a range. Down kits reduce output & efficacy. Consult photometry data for color temp, lumens & distribution of chosen configuration.

[†] Not all wiring types are available with all configurations. Consult Philips Ledalite for a complete list of available options.

3400 lm/4ft w/ 100% Down Kit* 3000/3500/4000K

Optical System

The optical system contains arrays of LEDs edge-lighting a low profile light-guide panel, using total internal reflection to homogenize the sources. The microstructured surface of the panel optimizes light extraction to create an efficacious direct/indirect distribution. Light is purified and controlled by MesoOptics film as it passes through a non-glare acrylic lens. Standard distribution is 75% up / 25% down for suspended and 65% up / 35% down for wall mount version.

Endcaps

Diecast aluminum endcaps, available in flat (standard) or sculpted (optional).

Finish

Standard finish is a textured matte powder coat in white, black or titanium silver.

Housing

Precision formed 18 gauge cold-rolled steel.

Weight

Maximum: Suspended 3.75lb/ft & Wall 3.0lb/ft.

Electrical

Factory pre-wired to section ends with quick-wire connectors.

Standard Driver

Philips Advance Xitanium 0-10V, 1-100%. Class 2 rated output. Consult Philips Ledalite for other available drivers.

Standard Battery Pack

Philips Bodine, 90 min, 10W, Class 2 rated output, Emergency lumen output = 10W x luminaire efficacy x 1.1. Typical output: 1100lm.

Lumen Maintenance

LEDs have been tested by the manufacturer in accordance with IESNA LM-80-08. At an ambient temperature of 25°C, the LED lumen maintenance expectation according to IES TM-21-11 is: L₈₀ (12k) >72,000 hrs (Reported methodology).

Source Color

LEDs rated for color rendering CRI >80 and fixture to fixture color accuracy within 2 SDCM.

Controls

Suspended version available with the following integrated controls:
Response daylight sensor (for single zone).

Mounting

Suspended: Tamper-resistant aircraft cable gripper provides unlimited vertical adjustment. Aircraft cable, crimp and cable gripper are independently tested to meet stringent safety requirements.

Wall: Fixture is mounted flush to wall using hidden wall brackets which attach to existing structure, variable within 2"-5" of end or joint.

Joints

Self-aligning joining system with hands-free pre-joining wire access

Approvals

Certified to UL, CSA and IES standards.
Certain suspended versions without down kits are
DesignLights Consortium® qualified. Please see the DLC
QPL list for exact catalog numbers
(www.designlights.org/QPL).

Warranty


Philips indoor professional luminaires 5 year LED warranty: www.philips.com/warranties.

Environment

Rated for dry or damp locations in operating ambient temperatures 0–40°C (32–104°F). Certain luminaire components may be adversely affected by contaminants. Damage caused by sulfur, chlorine, petroleum based solutions or other contaminants are not covered under warranty. Not suitable for natatorium environments.

Due to continuing product improvements, Philips Ledalite reserves the right to change the specifications without notice.

Dimensions - Cross Section



3400 lm/4ft w/ 100% Down Kit* 3000/3500/4000K

Dimensions - Modules

Modules

Module length excludes end caps. Nominal mounting spacing for individually mounted modules.


J 100% Down Kit

	4 (1219.2mm) — — — — — — — — — — — — — — — — — —	
4 ft.		
4 IL.		
	├ 8' (2438.8	mm)
	0 (2450.0	····y
Ω ft		

Note: Refer to installation instructions for exact mount.


Optics and Styles

G 80% Down Kit




3400 lm/4ft w/ 100% Down Kit* 3000/3500/4000K

Photometry - 3500K



0% Up / 100% Down



Candela Distribution

Vertical			rizontal			Zona
Angle	0	22.5	45	67.5	90	Lumer
0	877	877	877	877		0
5	880	880	884	888	889	85
15	896	903	940	974	983	267
25	900	917	989	1049	1071	453
35	830	840	886	918	922	544
45	627	619	611	600	594	473
55	408	400	388	385	385	354
65	242	239	240	243	248	239
75	100	101	102	104	105	112
85	19	20	22	22	22	26
90	0	0	0	0	0	0
95	1	1	1	1	0	1
105	1	2	2	3	1	2
115	2	2	3	2	2	2
125	2	3	2	2	2	2 2
135	2 2	2	2	3	3	2
145	2	2	2	3	3	2
155	2	2	2	2	3	1
165	2	2	2	1	2	1
175	1	1	1	1	1	0
180	1	1	1	1	1	0

Values per 4ft unit

Fixture photometry has been conducted in accordance with IESNA LM-79-08

IES files for this and other photometric options can be downloaded online at www.lightingproducts.philips.com

Coefficients of Utilization (%)

DCD	Ceiling:		8	0			70			50		0
RCR	Wall:	70	50	30	10	70	50	30	50	30	10	0
0		119	119	119	119	116	116	116	111	111	111	100
1		110	106	102	98	107	103	100	99	96	93	86
2		101	93	87	82	98	91	86	88	83	79	73
3		92	83	75	69	90	81	74	78	72	67	63
4		85	74	66	59	83	72	65	70	63	58	54
5		78	66	58	51	76	65	57	63	56	51	47
6		73	60	51	45	71	59	51	57	50	45	42
7		67	54	46	40	66	54	46	52	45	40	37
8		63	50	42	36	61	49	41	48	41	36	33
9		59	46	38	32	57	45	38	44	37	32	30
10		55	42	35	29	54	42	34	41	34	29	27

Avg. Luminance (cd/m2)

Vertical	Horizontal Angle					
Angle	0	45	90			
55	6905	6570	6517			
65	5561	5513	5705			
75	3757	3836	3953			
85	2092	2441	2441			

Distribution

Hemisphere	0% Up / 100% Down		
Glare Control	Meets RP-1-12 recommendations for VDT-Normal spaces		
Spacing Along (0°)	1.44		
Spacing Across (90°)	1.5		

3400 lm/4ft w/ 100% Down Kit* 3000/3500/4000K

Optical Performance

Nominal CCT:	3000K	3500K	4000K
Flux (lm)	2457	2565	2639
Efficacy (lm/W)	86.2	90.3	93.3
Power (W)	28.5	28.4	28.3
CCT (K)	3045	3312	3931
CRI	84	82	83
R9	10	-1	5
x	0.4338	0.4167	0.3849
у	0.4031	0.3968	0.3837
Duv	0.0000	0.0000	0.0020

Electrical Performance - 3500K

Input Voltage	120V	277V	347V
Input Power	28.4W	28.4W	28.5W
Input Current	0.24A	0.11A	0.09A
Power Factor	0.994	0.962	0.953
Total Harm. Distortion	8.0%	11.6%	11.0%

Tested values . contact technical support for rated values. Off-state power zero unless certain controls are specified.

