




Project:	
Spec Type:	
Catalog No:	2308LxGQ
Qty	
Line Notes:	

TruGroove recessed micro delivers the perfect combination of slender aesthetic and lighting control, creating luminous environments with exceptional uniformity and wide row spacing from a 1.75" aperture continuous line-of light. An extended family and refined design are perfect for lighting any professional space.

Ordering guide



- * Nominal values within a range. Consult photometry data for CRI, color temp, lumens & distribution of chosen configuration.
- † Not all wiring types are available with all configurations. Consult Philips Ledalite for a complete list of available options.
- ≈ Available in continuous run lengths from 6ft in steps as small as 1/8in for 1000lm/4ft, 1500lm/4ft & 2200lm/4ft symmetric (performance) configurations.
- ≈ All 3100lm/4ft and asymmetric configurations can be specified in 1ft steps. 2ft standalone modules are not available in asymmetric.

Ceiling Trims







Drywall Trimless



Drywall Trim







performance asymmetric 2200 lm/4ft, 3000/3500/4000K

Optical System

White light emitted from the LED sources is redirected by a precisely formed reflector and exits through the optical lens assembly. This assembly contains an acrylic extrusion profile retaining a layer of MesoOptic film, creating both an uninterrupted continuum of light and an optical batwing or asymmetric distribution from a 1.75" flush aperture.

Finish

Extruded aluminum trim and die-cast endplates coated with electrostatically applied and thermally cured polyester. Powder coat paint finish. White sensors only.

Housing

Die-formed 20 gauge cold-rolled steel. Multiple upper wire entrances available for continuous row mounting of fixtures.

Weight

Maximum 2.8lb/ft.

Electrical

Factory pre-wired to section ends with quick-wire connectors.

QuickShip

Upon request, TruGroove recessed micro can be madeto-order and shipped in 10-working days from receipt of order

Some configurations excluded. Limit of 500' linear feet per order.

QuickShip details are available in the links below:

QuickShip ColorCoded Guide

QuickShip Order Guide

Standard Drivers

Philips Advance Xitanium 0-10V, 1-100%. Philips Advance Xitanium SR, 5-100% (SpaceWise DT). Class 2 rated output. Consult Philips Ledalite for other available drivers.

Standard Battery Pack

Philips Bodine, 90 min, 10W, Class 2 rated output, Emergency lumen output = 10W x luminaire efficacy x 1.1. Typical output: 1100lm.

Lumen Maintenance

LEDs have been tested by the manufacturer in accordance with IESNA LM-80-08. At an ambient temperature of 25°C in non-insulation contact applications the LED lumen maintenance expectation according to IES TM-21-11-A is:

RI>80

L₉₀ (10k) >60,000 hrs (**Reported** methodology) L₈₀ (10k) 128,000 hrs (**Calculated** methodology). C**R**|>90:

L₉₀ (10k) 59,000 hrs (**Reported** methodology) L₈₀ (10k) 118,000 hrs (**Calculated** methodology).

Source Color

LEDs rated for color rendering CRI >80, R9 >0 and fixture to fixture color accuracy within 2 SDCM. Available 90 CRI option is rated for CRI >90, and R9 >60.

Controls

Certain configurations available with: Response Daylight Sensors SpaceWise DT Occupancy & Daylight Sensors w/ advanced grouping & Dwell Time.

*SpaceWise DT commissioning is via a compatible Android phone and Philips Field App. Compatible wireless dimming wall switches are available for dimming. For more information, please refer to www.philips.com/spacewise

Mounting

Mounting brackets on housing sides support T-Grid installation. 1/16" diameter aircraft cable with self-locking, tamper-resistant, miniature cable gripper provides vertical adjustment for drywall. Aircraft cable, crimp and gripper independently tested to meet stringent safety requirements.

Joints

Self-aligning joining system with hands-free pre-joining wire access.

Approvals

Certified to UL, CSA and IES standards. Insulation Contact (IC) rated.

Consult factory for DLC eligible configurations

Warranty

Five-year luminaire limited warranty including LED boards and driver.

USA: Warranty Support

Canada: Warranty Support

Environment


Rated for operation in dry and damp locations in ambient temperatures of 25°C. Many luminaire components, such as reflectors, refractors, lenses, and LEDs are made from materials which can be adversely affected by airborne contaminants. If sulfur based chemicals, petroleum based products, cleaning solutions, or other contaminants are expected in the intended area of use, consult factory for compatibility. Damage caused by sulfur, chlorine, petroleum based solution or other contaminants are not covered under warranty

 $\label{eq:decomposition} Due to continuing product improvements, Phillips Ledalite reserves the right to change the specifications without notice.$


Corner details and dimensions

Flat 90° Lit Corner Units (Side Views)

T-Grid



Drywall




Nominal Length	Housing	Lens	Mounting Points	Trim - T-Grid	Trim - Drywall Trimless	Trim - Drywall Trim
2x2ft Flat	25.1"/637mm	N/A	23.6"/600mm	25.3"/642mm	26.5"/673mm	25.6"/651mm


performance asymmetric 2200 lm/4ft, 3000/3500/4000K

Ceiling Types Drywall T-Grid* 3.62" (92mm) 3.75" (95mm) 3.57" (91mm) 3.26" (83mm) -2.74" (70mm) -2.74" (70mm) 2.74" (70mm) 5" (127mm Standard 9/16" Trimless Trim Tegular 9/16" Tegular 15/16" Standard 15/16"

Module Details & Dimensions


Standalone






Standalone							
Nominal	Housing	Lens	Mounting Points	Trim -T-Grid	Trim - Drywall Trimless	Trim - Drywall Trim	
2ft	23.9"/607mm	23.0"/584mm	23.4"/594mm	23.8"/605mm	26.4"/670mm	24.5"/622mm	
3ft	35.9"/912mm	35.0″/889mm	35.4"/899mm	35.8"/909mm	38.4"/975mm	36.5"/927mm	
4ft	47.9"/1217mm	47.0″/1194mm	47.4"/1204mm	47.8"/1214mm	50.4"/1280mm	48.5"/1232mm	
5ft	59.9″/1521mm	59.0″/1499mm	59.4″/1509mm	59.8"/1519mm	62.4"/1585mm	60.5″/1537mm	
6ft	71.9″/1826mm	71.0"/1803mm	71.4″/1814mm	71.8"/1824mm	74.4"/1889mm	72.5"/1841mm	
8ft	95.9″/2436mm	95.0"/2413mm	95.4″/2423mm	95.8"/2433mm	98.4"/2499mm	96.5"/2451mm	


Mid-Run



Mid-Run					
Nominal	Housing & Lens	Mounting Points			
2ft	24.0"/610mm	23.2"/589mm			
3ft	36.0"/914mm	35.2"/894mm			
4ft	48.0"/1219mm	47.2"/1199mm			
5ft	60.0″/1524mm	59.2″/1504mm			
6ft	72.0"/1829mm	71.2″/1809mm			
8ft	96.0"/2438mm	95.2″/2418mm			
Incremental	L	L-0.8"/20mm			

End-Run







End-Run								
Nominal	Housing	Lens	Mounting Points	Trim -T-Grid	Trim - Drywell Trimless	Trim - Drywa ll Trim		
2ft	24.0"/610mm	23.5"/597mm	23.2"/589mm	23.9"/606mm	25.7"/653mm	24.8"/629mm		
3ft	36.0"/914mm	35.5"/901mm	35.2"/894mm	35.9″/910mm	37.7″/957mm	36.7"/933mm		
4ft	48.0"/1219mm	47.5"/1206mm	47.2″/1199mm	47.9"/1215mm	49.7″/1262mm	48.7"/1238mm		
5ft	60.0"/1524mm	59.5″/1511mm	59.2"/1504mm	59.9"/1520mm	61.7"/1567mm	60.7″/1543mm		
6ft	72.0"/1829mm	71.5″/1816mm	71.2"/1809mm	71.9"/1825mm	73.7"/1872mm	72.8"/1848mm		
8ft	96.0"/2438mm	95.5"/2425mm	95.2"/2418mm	95.8″/2434mm	97.7"/2481mm	96.7"/2457mm		
Incremental	L	L=0.5"/13mm	L-0.8"/20mm	L-0.1"/3mm	L+1.7"/43mm	L+0.75"/19mm		

performance asymmetric 2200 lm/4ft, 3000/3500/4000K

Photometry @ CRI>80, 3500K



0% Up / 100% Down



Candela Distribution

Vertical			Zonal			
Angle	0	45	90	135	180	Lumen
0	931	931	931	931	931	0
5	1185	1113	885	785	732	91
15	1697	1478	874	563	482	284
25	1714	1574	834	394	330	436
35	1180	1206	713	301	263	456
45	678	722	504	242	218	369
55	370	399	301	191	173	262
65	209	211	182	133	119	171
75	89	88	85	68	59	84
85	17	16	18	18	16	21
90	0	0	0	0	0	0
95	0	0	0	0	0	0
105	0	0	0	0	0	0
115	0	0	0	0	0	0
125	0	0	0	0	0	0
135	0	0	0	0	0	0
145	0	0	0	0	0	0
155	0	0	0	0	0	0
165	0	0	0	0	0	0
175	0	0	0	0	0	0
180	0	0	0	0	0	0

Values per 4ft unit

Fixture photometry has been conducted in accordance with IESNA LM-79-08

IES files for this and other photometric options can be downloaded online at www.lightingproducts.philips.com

Coefficients of Utilization (%)

D.CD	Ceiling:		8	0			70			50		0
RCR	Wall:	70	50	30	10	70	50	30	50	30	10	0
0		119	119	119	119	116	116	116	111	111	111	100
1		110	106	103	99	108	104	101	100	97	95	87
2		102	95	89	84	99	93	87	89	85	81	75
3		94	85	77	72	92	83	76	80	74	70	65
4		87	76	68	62	85	75	67	72	66	61	57
5		80	69	61	55	78	68	60	66	59	54	51
6		75	63	54	49	73	62	54	60	53	48	45
7		70	57	49	44	68	56	49	55	48	43	41
8		65	53	45	39	64	52	44	51	44	39	37
9		61	49	41	36	60	48	41	47	40	35	33
10		57	45	38	33	56	45	37	44	37	32	31

Avg. Luminance (cd/m2)

Vertical	Horizontal Angle					
Angle	0	90	180			
55	11556	9398	5415			
65	8852	7703	5036			
75	6145	5877	4088			
85	3552	3674	3230			

Distribution

Hemisphere	0% Up / 100% Down			
Glare Control	Meets RP-1-12 recommendations for VDT-Normal spaces			
Spacing Along (0°)	1.6			
Spacing Across (90°)	1.25			
Spacing at 180°	0.49			

performance asymmetric 2200 lm/4ft, 3000/3500/4000K

Optical Performance @ 120V

Nominal Spec:	830	835	840	935
Flux (lm)	2096	2175	2189	2128
Efficacy (lm/W)	94.8	98.9	100.0	83.5
Power (W)	22.1	22.0	21.9	25.5
CCT (K)	3071	3490	4027	3523
CRI	84	82	84	94
R9	16	11	16	71
x	0.4308	0.4061	0.3798	0.4035
у	0.3998	0.3917	0.3782	0.3887
Duv	0.0009	0.0002	0.0009	0.0005

Electrical Performance @ CRI>80, 3500K

Input Voltage	120V	277V	347V
Input Power	22.0W	22.3W	22.1W
Input Current	0.19A	0.09A	0.07A
Power Factor	0.989	0.932	0.933
Total Harm. Distortion	12.1%	17.0%	12.8%

Tested values – contact technical support for rated values. Off-state power zero unless certain controls are specified.

