



Project:	
Location:	
Cat.No:	
Туре:	
Lamps:	Qty:
Notes:	

The Day-Brite / CFI Designer clean room troffer is a recessed luminaire tested to federal standard 209E and desiged for use with 1-1/2" face width inverted "T" bar ceilings.

Ordering guide

Example: 1DCLG232-FA21-UNV-1/2-EBLHE-LPT835HL

Width F	Family	Ceiling Type*	No. of Lamps (not includ- ed)	Lamp Type	Door Frame	Lens	Voltage	Options
1	DCL	G		_	FA	_	_	
1 1' D	OCL Designer clean room	G Grid *Flange configuration can be manufactured but will not be Clean Room rated due to openings in housing to access swing- arm jack screws. The use of FMA "F" mounting kits (sealed to the luminaire and ceiling is recommended for NEMA "F" applications.	1 2 3 (except 54HO)	28 28WT5 (46") 32 32WT8 (48") 54HO 54WT5HO (46")	FA Flat Aluminum	12 K-12, 125" nominal 19 K-19, 156" nominal 21 Pattern 12, .125" nominal	120 277 347 UNV Universal Voltage 120-277V	1/1 One 1-lamp ballast 1/2 One 2-lamp ballast 1/3 One 3-lamp ballast 1/3 One 3-lamp ballast 1/21 2-lamp & 1-lamp ballast EB Electronic ballast, 10% THD, std. ballast factor EB10R T8 electronic ballast, program rapid start, -10% THE EBHE T8 electronic ballast, high efficiency, std. ballast fa EBHHE T8 electronic ballast, high efficiency, low ballast fa EBHHE T8 electronic ballast, high efficiency, low ballast fa EBHHE T8 electronic ballast, high efficiency, low ballast fa EBDD Advance Mark 7 dimming ballast, 0-10V (low voltage) control EBDX Advance Mark 10 dimming ballast, phase control EBD Electronic dimming ballast, ustomer specified E1 B100 emerg, ballast, T8, 350-450 lumens, 120/277V E1CAN B100-CAN emerg ballast, Canada market, T8, 350-450 lumens, 120/347V E7 B60 emerg, ballast, T8, 600-700 lumens, 120/277V E5 B50 emerg, ballast, T8, 600-700 lumens, 120/277V E1 B50 emerg, ballast, T8, 600-700 lumens, 120/277V E1 B50 emerg, ballast, US, or Canada market, T8, 1100-1400 lumens, UNV
	•	r separately)		Seal to luminaire an	d ceiling)			E5-CAN



2-way gasketing, 1W + gasketing between door frame & housing

2W

Designer clean room troffer 1x4 1DCL

T8, T5, or T5HO

Application

- · Premium quality recessed static troffer for use in:
- Grid inverted T (NEMA "G") ceilings.

Construction/Finish

- · Meets federal standard No. 209E for class 100,000, 10,000 and 1,000.
- · Gasketed housing limits the passage of particle matter through the luminaire.
- · Designer Clean Room is NOT designed for rigorous pharmaceutical grade clean room applications
- Housing is gasketed to form a barrier between plenum and inside of luminaire. Door frame and lens are not sealed.
- · Floating door (with black reveal) standard.
- · Hinge and latch extruded aluminum door allows relamping and servicing from below the ceiling.
- · Standard lens is DB-21, 1/8" nominal thickness prismatic acrylic.
- Designed for use with 1-1/2" max. face width inverted T-Bars, 1-1/2" max. height. Also suitable for use with standard (1" wide)


T-bars. Not suitable for use with 2" wide T-bars.

- · Installing contractor is responsible for sealing luminaire to "T" Bar with clear silicone sealant.
- · Housing is painted after fabrication with white polyester powder finish.

Electrical

· cULus listed for wet location for covered ceiling use only.

Dimensions



Photometry

Efficiency - 66.8% 1' x 2' 2 Lamp **LER - 60 TER - 55**

Catalog No.	1DCLG232-FA21-1/2-EB
Test No.	15551
S/MH	1.1
Lamp Type	F32T8
Lumens/Lamp	2900
Ballast Factor	0.92
Input Watts	59

Comparative yearly lighting energy cost per 1000 lumens - \$4.00 based on 3000 hrs. and \$.08 pwr KWH.

The photometric results were obtained in the Day-Brite laboratory which is NVLAP accredited by the National Institute of Standards and Technology

Candlepower							
Angle	End	45	Cross				
0	1909	1909	1909				
5	1904	1896	1895				
10	1876	1866	1857				
15	1830	1810	1785				
20	1762	1715	1676				
25	1669	1600	1550				
30	1540	1467	1441				
35	1379	1332	1303				
40	1175	1134	1133				
45	969	911	883				
50	752	692	663				
55	569	478	513				
60	422	308	394				
65	306	200	293				
70	219	149	215				
75	154	113	156				
80	97	74	98				
85	43	41	45				

Light Distribution					Average Luminance				
Degrees 0-30	Lumens 1428	% Lamp 24.6	% Luminaire 36.8	Angle 45	End 5477	45° 5149	Cros : 4991		
0-40	2258	38.9	58.3	55	3965	3331	3574		
0-60 0-90	3434 3875	59.2 66.8	88.6 100.0	65 75	2894 2378	1891 1745	2771 2409		
- "				85	1972	1880	2063		

Coefficients of Utilization

EFFECTIVE FLOOR CAVITY REFLECTANCE 20 PER (pfc=0.20							
pcc		80			70		
pw	70	50	30	70	50	30	
	70		30	70	, ,	3	

pcc		80			70		5	U
pw	70	50	30	70	50	30	50	30
RCR								
0	80	80	80	78	78	78	73	73
1	73	70	68	71	69	67	67	65
2	68	63	58	66	61	58	59	56
3	63	56	52	60	56	51	54	50
4	57	51	46	56	50	45	48	44
5	54	46	40	53	46	40	44	40
6	50	41	36	48	40	35	40	35
7	46	39	33	46	38	33	36	32
8	44	34	29	42	34	29	34	29
9	40	33	28	40	32	27	32	27
10	39	29	25	38	29	25	28	25



Some luminaires use fluorescent or high intensity discharge (HID) lamps that contain small amounts of mercury. Such lamps are labeled, "Contain Mercury" and/or the symbol "HG". Lamps that contain mercury must be disposed of in accordance with local requirements. Information regarding lamp recycling and disposal can be found at www.lamprecycle.org

