






Project:		
Spec Type:		
Catalog No:	7705LxEAD	
Qty		
Line Notes:		

Incredible efficacy & boundless lighting choices mean the re-engineered Sona suspended LED is destined to become a future classic. Flexible up/down distributions and tailored LED optics mean you always have the right light for every task.

Ordering guide



^{*} Nominal values within a range. Down kits reduce output & efficacy. Consult photometry data for CRI, color temp, lumens & distribution of chosen configuration.

Mount Type Consult separate mounting spec sheet for mount type options: Ledalite Suspended Mounting Options Endcaps Integrated Controls Please indicate with check mark. Response Daylight Single Zone (DS) SpaceWise DT Occupancy & Daylight Sensor (SZ)







[†] Not all wiring types are available with all configurations. Consult Philips Ledalite for a complete list of available options.

3100 lm/4ft w/ 50% Down Kit 3000/3500/4000K

Optical System

 $\label{light Chamber Upper: Lateral-facing LED arrays deliver light into both the upper and lower hemispheres, giving a highly efficient, native 70% up / 30% down distribution with a wide, homogeneous upper batwing distribution. A fully indirect version with a solid lower housing can be specified, as well as a 50% down-light kit option.$

1 Light Chamber Lower: A downward-facing LED array aims light into the lower hemisphere, for a highly efficient, fully direct distribution or optional 80% down version.

2 Light Chambers: Both lateral-facing and downward-facing LED arrays are combined in separate upper and lower chambers for the ultimate in up/down distribution control

Lenses: On the upper surface an engineered diffuser smooths the light distribution on the ceiling and acts as a dust cover. On the lower surface, two 4" wide optics are available: either a curved, engineered acrylic diffuse lens flush to the housing; or a white louver with regressed diffuser for improved high angle cut-off and visual comfort.

Endcaps

Diecast aluminum endcaps, either Sculpted (curved) or Flat

Finish

High quality powder coated, available in matte white, black or titanium silver. Other custom colors, including pacific aqua, are available on request. White sensors only.

Housing

Precision formed 18 gauge cold-rolled steel. Cross section size (approx.): $2.6\,^{\rm h}$ x $9\,^{\rm w}$ (suspended) or $7.4\,^{\rm w}$ (wall mount).

Weight

Maximum: Suspended 4.9lb/ft, Wall 3.4lb/ft

Electrical

Factory pre-wired to section ends with quick-wire connectors.

Standard Drivers

Philips Advance Xitanium 0-10V, 1-100%. Philips Advance Xitanium Sensor Ready, 5-100%. Class 2 rated output. Consult Philips Ledalite for other available drivers.

Standard Battery Pack

Philips Bodine, 90 min, 10W, Class 2 rated output, Emergency lumen output = 10W x luminaire efficacy x 1.1. Typical output: suspended 1400lm, wall 1200lm.

Lumen Maintenance

www.philips.com/spacewise

LEDs have been tested by the manufacturer in accordance with IESNA LM-80-08. At an ambient temperature of 25°C, the LED lumen maintenance expectation according to IES TM-21-11 is: L80 (12k) >72,000 hrs (Reported methodology) L80 (12k) 110,000 hrs (Projected methodology).

Source Color

LEDs rated for color rendering CRI >80, R9 >0 and fixture to fixture color accuracy within 3 SDCM.

Controls

Suspended version (1 light chamber only) available with the following integrated controls: Response Daylight Sensors SpaceWise DT Occupancy & Daylight Sensors w/ advanced grouping & Dwell Time.

*SpaceWise DT commissioning is via a compatible Android phone and Philips Field App. Compatible wireless dimming wall switches are available for dimming. 347V is not available as a standard option. For more information, please refer to

Mounting Suspended: F

Suspended: Rapid installation sling mount at joints and ends. High strength aircraft cable and stainless steel gripper provide unlimited vertical adjustment and are independently tested to stringent safety standards. Variable mounting along the length of the housing is available for certain configurations upon request. Wall: A hidden steel rail and bracket system attaches to the existing structure and supports housings close to the wall. Mount positioning is fully variable along the modules to accommodate site conditions, spaced up to $4\frac{1}{2}$ on center and within 6" of an end or joint.

Joints

Self-aligning, gasketed joining system with hands-free wiring feature.

Approvals

Certified to UL, CSA and IES standards. Most suspended versions (except 1 light chamber down with louver) are DesignLights Consortium® qualified. Please see the DLC QPL list for exact catalog numbers (www.designlights.org/QPL).

Warranty


Philips indoor professional luminaires 5 year LED warranty: www.philips.com/warranties

Environment

Rated for dry or damp locations in operating ambient temperatures 0–40°C (32–104°F). Certain luminaire components may be adversely affected by contaminants. Damage caused by sulfur, chlorine, petroleum based solutions or other contaminants in the area of operation are not covered under warranty. Not suitable for natatorium environments.

Due to continuing product improvements, Philips Ledalite reserves the right to change the specifications without notice.


Dimensions - Cross Section




3100 lm/4ft w/ 50% Down Kit 3000/3500/4000K

Dimensions - Modules

Suspended - Side view, no end caps




Optics and Styles




3100 lm/4ft w/ 50% Down Kit 3000/3500/4000K

Photometry @ CRI>80, 3500K



50% Up / 50% Down



Candela Distribution

Vertical		Zonal				
Angle	0	22.5	45	67.5	90	Lumens
0	486	486	486	486	486	0
5	480	484	484	485	486	46
15	464	468	468	470	471	132
25	431	435	436	439	440	201
35	383	387	390	392	393	243
45	322	326	331	332	333	254
55	251	256	259	260	262	230
65	172	176	180	182	184	177
75	90	94	101	107	110	107
85	21	29	40	49	52	44
90	1	11	24	34	39	0
95	21	30	44	57	65	53
105	70	98	152	195	210	157
115	119	179	306	406	434	286
125	163	226	379	516	557	325
135	192	229	311	400	435	244
145	211	230	269	303	318	169
155	223	233	251	269	274	116
165	230	235	241	248	251	69
175	233	236	236	237	238	23
180	236	236	236	236	236	0

Values per 4ft unit

Fixture photometry has been conducted in accordance with IESNA LM-79-08

IES files for this and other photometric options can be downloaded online at www.lightingproducts.philips.com

Coefficients of Utilization (%)

DCD	Ceiling:		8	0			70			50		0
RCR	Wall:	70	50	30	10	70	50	30	50	30	10	0
0		107	107	107	107	99	99	99	83	83	83	50
1		97	93	89	85	90	86	82	72	70	68	41
2		88	81	74	69	81	75	69	63	59	55	34
3		81	71	63	57	74	65	59	55	50	46	29
4		74	62	54	48	67	58	51	49	44	39	24
5		67	56	47	41	62	52	44	44	38	34	21
6		62	50	42	36	57	46	39	39	34	29	18
7		57	45	37	31	53	42	34	36	30	26	16
8		53	41	33	27	49	38	31	32	27	23	14
9		49	37	29	24	46	35	28	30	24	20	13
10		46	34	27	22	43	32	25	27	22	18	12

Avg. Luminance (cd/m2)

Vertical	Horizontal Angle					
Angle	0	45	90			
55	3930	3832	3809			
65	3644	3504	3499			
75	3087	3021	3131			
85	2085	2742	3164			

Distribution

Hemisphere	50% Up / 50% Down		
Glare Control	Meets RP-1-12 recommendations for VDT-Normal spaces		
Spacing Along (0°)	1.25		
Spacing Across (90°)	1.28		

3100 lm/4ft w/ 50% Down Kit 3000/3500/4000K

Optical Performance @ 120V

Nominal Spec:	3000K	3500K	4000K
Flux (lm)	2763	2876	2937
Efficacy (lm/W)	120.7	125.6	127.1
Power (W)	22.9	22.9	23.1
CCT (K)	3020	3378	3958
CRI	84	83	84
R9	11	9	11
x	0.4361	0.4138	0.3835
у	0.4048	0.3976	0.3820
Duv	0.0003	0.0012	0.0016

Electrical Performance @ CRI>80, 3500K

Input Voltage	120V	277V	347V
Input Power	22.9W	23.0W	23.4W
Input Current	0.19A	0.09A	0.07A
Power Factor	0.992	0.938	0.936
Total Harm. Distortion	9.4%	12.7%	13.0%

Tested values - contact technical support for rated values. Off-state power zero unless certain controls are specified.

With SpaceWise DT, standby power <0.5W (120V) or <0.8W (277V).



Tel. 800-668-9008