

# Stonco

by @signify

Special Purpose

RoughLyte LED

VCXL/VWXL



## Small but mighty

End your search for durable lighting that will really last, choose the Stonco RoughLyte LED.

The Stonco RoughLyte LED is available in 14 watts, providing up to 1390 lumens. Applications include wall and ceiling mounted exterior surfaces. Roughlyte LED fixtures guard against moisture and debris (for globe down mounting only).

**The mighty little light with long lasting shine.**




# VCXL/VWXL RoughLyte LED




- Wall or ceiling mounting available.
- Provides 83% energy savings over 100W Incandescent.\*
- Heat and shock resistant glass globe with cast aluminum guard.
- Long life reduces maintenance.
- Provides up to 1,390 lumens.
- 5 year limited warranty.

\*Based on comparison between 100W INC @1710 lumens and VCXL14-NW-G1 @ 1390 lumens

## Ceiling Mount (VCXL)



## Wall Mount (VWXL)



## Ordering guide

Example: VCXL-14-NW-G1-8

Luminaire	Wattage	Generation	Voltage
	<b>14</b>	<b>NW-G1</b>	<b>8</b>
<b>VCXL</b> Ceiling 4" box mounted	<b>14</b> 14W	<b>NW-G1</b> Neutral White, 4000K, 70CRI, Generation 1	<b>8</b> 120-277VAC
<b>VWXL</b> Wall 4" box mounted			

## LED Wattage and Lumen Values

Ordering Codes	Total LEDs	Drive Current (mA)	Color Temp.(K)	Average System Wattage <sup>1</sup>	Type VS		
					Lumen Output <sup>1,2</sup>	Bug Rating	Efficacy (LPW)
<b>VC/VWXL14-NW-G1</b>	1	350	4000	14	1390	B1-U3-G1	102

1. Wattage and lumen output may vary by due to LED manufacturer forward volt specification and ambient temperature.

Wattage shown is average for 120V through 277V input. Measured wattage may vary due to variation in input voltage.

2. Lumen values based on photometric tests performed in compliance with IESNA LM-79.

The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract.

