

Ø12.00 BOLT CIRCLE

STREET SIDE

HOUSE SIDE

TOP SECTIONED VIEW

0.75 ANCHOR RODS, 4 PLACES


VERIFY BOLD LINE IS 12" LONG

ACCESS DOOR

NOTES:

1. SUGGESTED BOLT CIRCLE: 12" DIAMETER
 MAXIMUM BOLT CIRCLE: 12" DIAMETER
 MINIMUM BOLT CIRCLE: 8" DIAMETER
2. HADCO STRONGLY RECOMMENDS USING LEVELING NUTS TO MOUNT THE POST BASE. IF FOUNDATION IS NOT LEVEL, INCREASE "X" DIMENSION ACCORDINGLY WHEN USING LEVELING NUTS WITH WASHERS.

 X = 3" WITH LEVELING NUTS
 X = 2" WITHOUT LEVELING NUTS
3. IF USING GROUTING TO CONCEAL GAP BETWEEN BASE AND FOUNDATION, ALLOW FOR WATER DRAINAGE.



	<small>CONFIDENTIAL: This drawing is confidential and proprietary to Signify Holdings and may not be reproduced in whole or in part without the express written consent of Signify Holdings. © 2018 Signify Holdings. All rights reserved.</small>		TITLE: TEMP,AR 4000
	DRAWN BY: HDS CHECKED BY: B. DORON APPR BY: E. HADDAD	DATE: 1/3/97 DATE: 8/4/09 DATE: 1/7/97	DRW SIZE: C MATERIAL: 17 X 22 WHITE BOND PAPER,
<small>UNLESS OTHERWISE SPECIFIED: *ALL DIMENSIONS ARE IN INCHES. *ALL THREADS ARE UNC-2B OR UNF-2B AFTER COATING. *ALL THREADS ARE TO BE VERIFIED WITH A THREAD GAGE.</small>	EF-04-01-11 Rev.09	SCALE 1:1	SHEET 1 OF 1
* DO NOT SCALE THIS DRAWING *	PART NO: T01700913		