



# Arioso Recessed Air

## 2x2, 2 Lamp F17T8, Air Handling w/Perforated Metal Shield & White Overlay

2x2, 2 Lamp F17T8, Air Handling w/Perforated Metal Shield & White Overlay

The Philips Day-Brite / Philips CFI Arioso Recessed Air offers air handling capabilities along with all the benefits of the standard Arioso. Through integrated side slots, this luminaire incorporates the air handling feature without disturbing the simple clean lines and so

### Product data

General Information	
Lamp Source Code	FLU
Lamp Watts	17
Lamp Envelope Code	T-8
Number of Lamps	2
Photometric Distribution Type	Direct
Mounting	Recessed franse vertaling
Operating and Electrical	
Voltages	120/277/347/UNIV V
Mechanical and Housing	
Fixture Size	2 ft x 2 ft

Shape	Square
Product Data	
Order product name	2x2, 2 Lamp F17T8, Air Handling w/Perforated Metal Shield & White Overlay
Commercial Code	2AVGA217-PMW
Order code	2AVGA217-PMW
Catalog Number Description	2x2, 2 Lamp F17T8, Air Handling w/Perforated Metal Shield & White Overlay
Service / Spec Smart	-
Material Nr. (12NC)	DAY00000307