



Arioso Recessed LED

2x4, 7400 Nominal Delivered Lumens, 4000K, Frosted Acrylic Lens

2x4, 7400 Nominal Delivered Lumens, 4000K, Frosted Acrylic Lens

The Philips Day-Brite / Philips CFI Arioso Recessed LED offers standard-setting efficiency without aesthetic compromise. These LED luminaires combine state-of-the-art, flexible and globally- recognized LED lighting platforms with proven Arioso optical combinations.

Product data

General Information		Initial Performance (IEC Compliant)	
Lamp Source Code	LED	Luminaire Lumens	7400
Colour Temperature	4000K		
CRI	80		
Photometric Distribution Type	Direct		
Mounting	Recessed franse vertaling		
Operating and Electrical		Product Data	
Luminaire Input Watts	75	Order product name	2x4, 7400 Nominal Delivered Lumens, 4000K, Frosted Acrylic Lens
		Commercial Code	2AVEG74L840-4-ACR
		Order code	2AVEG74L840-4-ACR
		Catalog Number Description	2x4, 7400 Nominal Delivered Lumens, 4000K, Frosted Acrylic Lens
		Service / Spec Smart	-
		Material Nr. (12NC)	DAY00000454
Mechanical and Housing			
Fixture Size	2 ft x 4 ft		
Shape	Rectangular		