



# DPWL Designer Wet Location

## 2x4, 3 Lamp F32T8, Wet Location, Prismatic Acrylic Lens

### 2x4, 3 Lamp F32T8, Wet Location, Prismatic Acrylic Lens

Designer Wet Location is a recessed luminaire UL Listed for damp and wet locations (for covered ceiling use only).

#### Product data

General Information	
Lamp Source Code	FLU
Lamp Watts	32
Lamp Envelope Code	T-8
Number of Lamps	3
Photometric Distribution Type	Direct
Mounting	Recessed
Operating and Electrical	
Voltages	120/277/347 V
Mechanical and Housing	
Fixture Size	2 ft x 4 ft

Product Data	
Order product name	2x4, 3 Lamp F32T8, Wet Location, Prismatic Acrylic Lens
Commercial Code	2DPWLG332-FS01-1/21-EB
Order code	2DPWLG332-FS01-1/21-EB
Catalog Number Description	2x4, 3 Lamp F32T8, Wet Location, Prismatic Acrylic Lens
Service / Spec Smart	-
Material Nr. (12NC)	DAY00000879