



# HBA Low Bay

## 22" Open Pearlescent Blue Acrylic Reflector, 1 Lamp 400wPSMH (Coated)

22" Open Pearlescent Blue Acrylic Reflector, 1 Lamp 400wPSMH (Coated)

The HBA is a high efficiency luminaire for general;purpose and retail lighting. This luminaire is ideal for;retail stores, warehouse aisles, and industrial;applications where uplight is required.

### Product data

General Information	
Lamp Source Code	PS
Lamp Watts	400
Lamp Envelope Code	BT/ED/E-37
Number of Lamps	1
Photometric Distribution Type	Semi Direct
Mounting	Suspended
Operating and Electrical	
Voltages	120/208/240/277/347/480 V
Mechanical and Housing	
Shape	Round

Product Data	
Order product name	22" Open Pearlescent Blue Acrylic Reflector, 1 Lamp 400wPSMH (Coated)
Commercial Code	HBA400P-AR22-PB (C)
Order code	HBA400P-AR22-PB (C)
Catalog Number Description	22" Open Pearlescent Blue Acrylic Reflector, 1 Lamp 400wPSMH (Coated)
Service / Spec Smart	-
Material Nr. (12NC)	DAY00001577