



LBN Low Bay

1 Lamp 400wMH, Acrylic Lens

1 Lamp 400wMH, Acrylic Lens

The LBN Low Bay Luminaire offers the high;efficiency general purpose industrial lighting for;mounting height requirements of 30' and below.

Product data

General Information	
Lamp Source Code	MH
Lamp Watts	400
Lamp Envelope Code	BT/ED/E-37
Number of Lamps	1
Photometric Distribution Type	Direct
Mounting	Suspended
Operating and Electrical	
Luminaire Input Watts	458
Voltages	120/208/240/277/347/480 V
Mechanical and Housing	
Fixture Size	28 in

Shape	Round
Product Data	
Order product name	1 Lamp 400wMH, Acrylic Lens
Commercial Code	LBN400M-CRA
Order code	LBN400M-CRA
Catalog Number Description	1 Lamp 400wMH, Acrylic Lens
Service / Spec Smart	-
Material Nr. (12NC)	DAY00003468