



# LBN Low Bay

## 1 Lamp 400wHPS, Acrylic Lens

1 Lamp 400wHPS, Acrylic Lens

The LBN Low Bay Luminaire offers the high;efficiency general purpose industrial lighting for;mounting height requirements of 30' and below.

### Product data

| General Information           |                           |
|-------------------------------|---------------------------|
| Lamp Source Code              | HPS                       |
| Lamp Watts                    | 400                       |
| Lamp Envelope Code            | BT/ED/E-18                |
| Number of Lamps               | 1                         |
| Photometric Distribution Type | Direct                    |
| Mounting                      | Suspended                 |
| Operating and Electrical      |                           |
| Luminaire Input Watts         | 464                       |
| Voltages                      | 120/208/240/277/347/480 V |
| Mechanical and Housing        |                           |
| Fixture Size                  | 28 in                     |

| Shape                      | Round                        |
|----------------------------|------------------------------|
| Product Data               |                              |
| Order product name         | 1 Lamp 400wHPS, Acrylic Lens |
| Commercial Code            | LBN400S-CRA                  |
| Order code                 | LBN400S-CRA                  |
| Catalog Number Description | 1 Lamp 400wHPS, Acrylic Lens |
| Service / Spec Smart       | -                            |
| Material Nr. (12NC)        | DAY00003470                  |