



# LW Low Profile Vaporlume

## 4', 2 Lamp F32T8, Lineal Ribbed Polycarbonate Lens

### 4', 2 Lamp F32T8, Lineal Ribbed Polycarbonate Lens

The Low Profile Vaporlume is a wet location listed luminaire that incorporates a low profile housing design and high impact lens.

#### Product data

<b>General Information</b>		<b>Shape</b>	
Lamp Source Code	FLU	Linear	
Lamp Watts	32		
Lamp Envelope Code	T-8		
Number of Lamps	2		
Photometric Distribution Type	Semi Direct		
Mounting	Surface Wall		
<b>Operating and Electrical</b>		<b>Product Data</b>	
Luminaire Input Watts	53	Order product name	4', 2 Lamp F32T8, Lineal Ribbed Polycarbonate Lens
Voltages	120/277/347 V	Commercial Code	LWRE232-UNV
<b>Mechanical and Housing</b>		Order code	LWRE232-UNV
Fixture Size	48 in	Catalog Number Description	4', 2 Lamp F32T8, Lineal Ribbed Polycarbonate Lens
		Service / Spec Smart	-
		Material Nr. (12NC)	DAY00004101