



SofTrace Recessed Fluorescent

2x2, 2 Lamp F24T5HO, Diffuse (Smooth) Center Diffuser & Ribbed Side Diffusers

2x2, 2 Lamp F24T5HO, Diffuse (Smooth) Center Diffuser & Ribbed Side Diffusers

SofTrace brings new meaning to the concept of combining style with performance. Equipped with a fresh streamlined design and innovative technology, SofTrace provides a huge step forward for the lighting industry. The sleek profile design belies the true "horsepower under the hood". With efficiency levels exceeding 95% and lumens per Watt as great as 87, an architectural product now delivers leading edge performance for the most environmentally conscious user.

Product data

General Information		Product Data	
Lamp Source Code	FLU	Order product name	2x2, 2 Lamp F24T5HO, Diffuse (Smooth) Center Diffuser & Ribbed Side Diffusers
Lamp Watts	24	Commercial Code	2STG224HO-DS-1/2-EB-RIB
Lamp Envelope Code	T-5	Order code	2STG224HO-DS-1/2-EB-RIB
Number of Lamps	2	Catalog Number Description	2x2, 2 Lamp F24T5HO, Diffuse (Smooth) Center Diffuser & Ribbed Side Diffusers
Photometric Distribution Type	Direct	Service / Spec Smart	-
Mounting	Recessed	Material Nr. (12NC)	DAY00004408
Operating and Electrical			
Luminaire Input Watts	50		
Voltages	120/277/347 V		
Mechanical and Housing			
Fixture Size	2 ft x 2 ft		

SofTrace Recessed Fluorescent

