



# SofTrace Air Fluorescent

## 2x2, 2 Lamp F17T8, Air Handling, Diffuse (Ribbed) Center Diffuser

### 2x2, 2 Lamp F17T8, Air Handling, Diffuse (Ribbed) Center Diffuser

SofTrace Air brings new meaning to the concept of combining style with performance. Equipped with a fresh streamlined design and innovative technology, SofTrace provides a huge step forward for the lighting industry. The sleek profile design belies the true “horsepower under the hood”. With efficiency levels exceeding 95% and lumens per Watt as great as 87, an architectural product now delivers leading edge performance for the most environmentally conscious user.

#### Product data

General Information	
Lamp Source Code	FLU
Lamp Watts	17
Lamp Envelope Code	T-8
Number of Lamps	2
Photometric Distribution Type	Direct
Mounting	Recessed franse vertaling
Operating and Electrical	
Luminaire Input Watts	32
Voltages	120/277/347 V
Mechanical and Housing	
Fixture Size	2 ft x 2 ft

Product Data	
Order product name	2x2, 2 Lamp F17T8, Air Handling, Diffuse (Ribbed) Center Diffuser
Commercial Code	2STGA217-D-1/2-EB
Order code	2STGA217-D-1/2-EB
Catalog Number Description	2x2, 2 Lamp F17T8, Air Handling, Diffuse (Ribbed) Center Diffuser
Service / Spec Smart	-
Material Nr. (12NC)	DAY00004454