



# SofTrace Air Fluorescent

## 2x4, 2 Lamp F32T8, Air Handling, Diffuse (Smooth) Center Diffuser & Ribbed Side Diffusers

2x4, 2 Lamp F32T8, Air Handling, Diffuse (Smooth) Center Diffuser & Ribbed Side Diffusers

SofTrace Air brings new meaning to the concept of combining style with performance. Equipped with a fresh streamlined design and innovative technology, SofTrace provides a huge step forward for the lighting industry. The sleek profile design belies the true “horsepower under the hood”. With efficiency levels exceeding 95% and lumens per Watt as great as 87, an architectural product now delivers leading edge performance for the most environmentally conscious user.

### Product data

General Information	
Lamp Source Code	FLU
Lamp Watts	32
Lamp Envelope Code	T-8
Number of Lamps	2
Photometric Distribution Type	Direct
Mounting	Recessed frange vertaling
Operating and Electrical	
Luminaire Input Watts	59
Voltages	120/277/347 V
Mechanical and Housing	
Fixture Size	2 ft x 4 ft

Product Data	
Order product name	2x4, 2 Lamp F32T8, Air Handling, Diffuse (Smooth) Center Diffuser & Ribbed Side Diffusers
Commercial Code	2STGA232-DS-1/2-EB-RIB
Order code	2STGA232-DS-1/2-EB-RIB
Catalog Number Description	2x4, 2 Lamp F32T8, Air Handling, Diffuse (Smooth) Center Diffuser & Ribbed Side Diffusers
Service / Spec Smart	-
Material Nr. (12NC)	DAY00004484