



HBO Open High Bay Acrylic Reflector

22" Open Acrylic Reflector, 1 Lamp 400wPSMH

22" Open Acrylic Reflector, 1 Lamp 400wPSMH

The HBO Open High Bay Luminaire features an open, acrylic reflector for maximum efficiency in general purpose retail, educational and industrial applications where uplight is required.

Product data

| General Information | |
|---------------------|------------|
| Lamp Source Code | PS |
| Lamp Watts | 400 |
| Lamp Envelope Code | BT/ED/E-37 |
| Number of Lamps | 1 |
| Mounting | Suspended |

| Operating and Electrical | |
|--------------------------|---------------------------|
| Voltages | 120/208/240/277/347/480 V |

| Mechanical and Housing | |
|------------------------|-------|
| Shape | Round |

| Product Data | |
|----------------------------|---|
| Order product name | 22" Open Acrylic Reflector, 1 Lamp 400wPSMH |
| Commercial Code | HBO400PMT-PSC-Q-OR-AR22 |
| Order code | HBO400PMT-PSC-Q-OR-AR22 |
| Catalog Number Description | 22" Open Acrylic Reflector, 1 Lamp 400wPSMH |
| Service / Spec Smart | - |
| Material Nr. (12NC) | DAY00005797 |