



Kleenseal 100 Recessed Cleanroom

2x4, 2 Lamp F32T8, .125" Prismatic Acrylic, Wet Location, Inset Doorframe w/Captive Screws

2x4, 2 Lamp F32T8, .125" Prismatic Acrylic, Wet Location, Inset Doorframe w/Captive Screws

The Kleenseal KTR 100 is a cleanroom luminaire well suited for laboratories, fuel storage areas and dirty areas such as locker rooms. Ideal for Class 100-100,000 cleanrooms.

Product data

General Information	
Lamp Source Code	FLU
Lamp Watts	32
Lamp Envelope Code	T-8
Number of Lamps	2
Photometric Distribution Type	Direct
Mounting	Recessed
Operating and Electrical	
Voltages	120/277/347 V
Mechanical and Housing	
Fixture Size	2 ft x 4 ft

Shape	Rectangular
Product Data	
Order product name	2x4, 2 Lamp F32T8, .125" Prismatic Acrylic, Wet Location, Inset Doorframe w/Captive Screws
Commercial Code	K1242F32-6AP3
Order code	K1242F32-6AP3
Catalog Number Description	2x4, 2 Lamp F32T8, .125" Prismatic Acrylic, Wet Location, Inset Doorframe w/Captive Screws
Service / Spec Smart	-
Material Nr. (12NC)	DAY00007473