



# Kleenseal 100 Recessed Cleanroom

2x4, 6 Lamp F32T8, .125" Prismatic Acrylic, Wet Location, Inset Doorframe w/Captive Screws

2x4, 6 Lamp F32T8, .125" Prismatic Acrylic, Wet Location, Inset Doorframe w/Captive Screws

The Kleenseal KTR 100 is a cleanroom luminaire well suited for laboratories, fuel storage areas and dirty areas such as locker rooms. Ideal for Class 100-100,000 cleanrooms.

## Product data

<b>General Information</b>		<b>Shape</b>	
Lamp Source Code	FLU	Rectangular	
Lamp Watts	32		
Lamp Envelope Code	T-8		
Number of Lamps	6		
Photometric Distribution Type	Direct		
Mounting	Recessed		
<b>Operating and Electrical</b>		<b>Product Data</b>	
Voltages	120/277/347 V	Order product name	2x4, 6 Lamp F32T8, .125" Prismatic Acrylic, Wet Location, Inset Doorframe w/Captive Screws
		Commercial Code	K1246F32-6AP3
		Order code	K1246F32-6AP3
		Catalog Number Description	2x4, 6 Lamp F32T8, .125" Prismatic Acrylic, Wet Location, Inset Doorframe w/Captive Screws
		Service / Spec Smart	-
		Material Nr. (12NC)	DAY00007477
<b>Mechanical and Housing</b>			
Fixture Size	2 ft x 4 ft		