



# T Series T8 Strip

2', 2 Lamp F17T8

2', 2 Lamp F17T8

Heavy duty Standard Cross Section Strip Luminaire offers row, surface or suspension mounting. High reflectance white baked enamel partnered with a variety of reflector options provides outstanding performance.

## Product data

General Information	
Lamp Source Code	FLU
Lamp Watts	17
Lamp Envelope Code	T-8
Number of Lamps	2
Mounting	Surface Suspended Wall
Operating and Electrical	
Voltages	120/277/347 V
Mechanical and Housing	
Fixture Size	24 in

Shape	Linear
Product Data	
Order product name	2', 2 Lamp F17T8
Commercial Code	T217-UNV-1/2-EB
Order code	T217-UNV-1/2-EB
Catalog Number Description	2', 2 Lamp F17T8
Service / Spec Smart	Service Smart (2 Days) USA
Material Nr. (12NC)	DAY00007977