



DayLED Recessed LED

2x2, 3800 Nominal Delievered Lumens, 4000K, Pattern 12 .125" Thick Diffuse Acrylic Lens

2x2, 3800 Nominal Delievered Lumens, 4000K, Pattern 12 .125" Thick Diffuse Acrylic Lens

The Philips Day-Brite DayLED is an LED troffer offering general lighting distribution excellent for ambient illumination. It features a sealed, maintenance free, low profile housing, along with a frameless design that maximizes its luminous aperture and provides a clean, attractive ceiling appearance.

Product data

General Information		Initial Performance (IEC Compliant)	
Lamp Source Code	LED	Luminaire Lumens	3800
Colour Temperature	4000K		
CRI	80		
Photometric Distribution Type	Direct		
Mounting	Recessed franse vertaling		
Operating and Electrical		Product Data	
Luminaire Input Watts	45	Order product name	2x2, 3800 Nominal Delievered Lumens, 4000K, Pattern 12 .125" Thick Diffuse Acrylic Lens
Voltages	120/277/347 V	Commercial Code	2LTG38L840-2-184
		Order code	2LTG38L840-2-184
		Catalog Number Description	2x2, 3800 Nominal Delievered Lumens, 4000K, Pattern 12 .125" Thick Diffuse Acrylic Lens
		Service / Spec Smart	-
		Material Nr. (12NC)	DAY00008294
Mechanical and Housing			
Fixture Size	2 ft x 2 ft		