



DayLED Recessed LED

2x2, 3800 Nominal Delievered Lumens, 4000K, Pattern 12 .125" Thick Acrylic Lens

2x2, 3800 Nominal Delievered Lumens, 4000K, Pattern 12 .125" Thick Acrylic Lens

The Philips Day-Brite DayLED is an LED troffer offering general lighting distribution excellent for ambient illumination. It features a sealed, maintenance free, low profile housing, along with a frameless design that maximizes its luminous aperture and provides a clean, attractive ceiling appearance.

Product data

| General Information | | Initial Performance (IEC Compliant) | |
|-------------------------------|---------------|-------------------------------------|---|
| Lamp Source Code | LED | Luminaire Lumens | 3800 |
| Color Temperature | 4000K | | |
| CRI | 80 | Product Data | |
| Photometric Distribution Type | Direct | Order product name | 2x2, 3800 Nominal Delievered Lumens, 4000K, Pattern 12 .125" Thick Acrylic Lens |
| Mounting | Recessed | Commercial Code | 2LTG38L840-2-21 |
| | | Order code | 2LTG38L840-2-21 |
| Operating and Electrical | | Catalog Number Description | 2x2, 3800 Nominal Delievered Lumens, 4000K, Pattern 12 .125" Thick Acrylic Lens |
| Luminaire Input Watts | 46 | Service / Spec Smart | - |
| Voltages | 120/277/347 V | Material Nr. (12NC) | DAY00008295 |
| Mechanical and Housing | | | |
| Fixture Size | 2 ft x 2 ft | | |