



DayLED Recessed LED

2x4, 7100 Nominal Delivered Lumens, 4000K, Pattern 12 .125" Thick Acrylic Diffuse Lens

2x4, 7100 Nominal Delivered Lumens, 4000K, Pattern 12 .125" Thick Acrylic Diffuse Lens

The Philips Day-Brite DayLED is an LED troffer offering general lighting distribution excellent for ambient illumination. It features a sealed, maintenance free, low profile housing, along with a frameless design that maximizes its luminous aperture and provides a clean, attractive ceiling appearance.

Product data

General Information		Initial Performance (IEC Compliant)	
Lamp Source Code	LED	Luminaire Lumens	7100
Color Temperature	4000K		
CRI	80		
Photometric Distribution Type	Direct		
Mounting	Recessed		
Operating and Electrical		Product Data	
Luminaire Input Watts	78	Order product name	2x4, 7100 Nominal Delivered Lumens, 4000K, Pattern 12 .125" Thick Acrylic Diffuse Lens
Voltages	120/277/347 V	Commercial Code	2LTG71L840-4-184
		Order code	2LTG71L840-4-184
		Catalog Number Description	2x4, 7100 Nominal Delivered Lumens, 4000K, Pattern 12 .125" Thick Acrylic Diffuse Lens
		Service / Spec Smart	-
		Material Nr. (12NC)	DAY00008296
Mechanical and Housing			
Fixture Size	2 ft x 4 ft		