



DayLED Recessed LED

2x4, 5600 Nominal Delivered Lumens, 4000K, Pattern 12 .125" Thick Acrylic Diffuse Lens

2x4, 5600 Nominal Delivered Lumens, 4000K, Pattern 12 .125" Thick Acrylic Diffuse Lens

The Philips Day-Brite DayLED is an LED troffer offering general lighting distribution excellent for ambient illumination. It features a sealed, maintenance free, low profile housing, along with a frameless design that maximizes its luminous aperture and provides a clean, attractive ceiling appearance.

Product data

General Information	
Lamp Source Code	LED
Color Temperature	4000K
CRI	80
Photometric Distribution Type	Direct
Mounting	Recessed
Operating and Electrical	
Luminaire Input Watts	60
Voltages	120/277/347 V
Mechanical and Housing	
Fixture Size	2 ft x 4 ft

Initial Performance (IEC Compliant)	
Luminaire Lumens	5600
Product Data	
Order product name	2x4, 5600 Nominal Delivered Lumens, 4000K, Pattern 12 .125" Thick Acrylic Diffuse Lens
Commercial Code	2LTG56L840-4-184
Order code	2LTG56L840-4-184
Catalog Number Description	2x4, 5600 Nominal Delivered Lumens, 4000K, Pattern 12 .125" Thick Acrylic Diffuse Lens
Service / Spec Smart	-
Material Nr. (12NC)	DAY00008301