



# FluxStream LED Industrial

4' Industrial, 4,000 Nominal Delivered Lumens, 3500K, 80 CRI, UNV, 0-10V Dimming

4' Industrial, 4,000 Nominal Delivered Lumens, 3500K, 80 CRI, UNV, 0-10V Dimming

The FluxStream family of LED linear luminaires deliver high-quality, more uniform light versus fluorescents for a greater range of applications. Choose FluxStream for simple, robust LED light industrial commercial linear lighting solutions that need to perform and endure.

## Product data

General Information		Initial Performance (IEC Compliant)	
Lamp Source Code	LED	Luminaire Lumens	4000
Color Temperature	3500K		
CRI	80		
Mounting	Surface Suspended		
Operating and Electrical		Product Data	
Luminaire Input Watts	31	Order product name	4' Industrial, 4,000 Nominal Delivered Lumens, 3500K, 80 CRI, UNV, 0-10V Dimming
Voltages	120/277 V	Commercial Code	FSI440L835-UNV-DIM
		Order code	FSI440L835-UNV-DIM
		Catalog Number Description	4' Industrial, 4,000 Nominal Delivered Lumens, 3500K, 80 CRI, UNV, 0-10V Dimming
		Service / Spec Smart	-
		Material Nr. (12NC)	DAY00008884
Mechanical and Housing			
Fixture Size	48 in		
Shape	Linear		