



FluxStream LED Industrial

4' Industrial, 4,000 Nominal Delivered Lumens, 4000K, 80 CRI, UNV, 0-10V Dimming

4' Industrial, 4,000 Nominal Delivered Lumens, 4000K, 80 CRI, UNV, 0-10V Dimming

The FluxStream family of LED linear luminaires deliver high-quality, more uniform light versus fluorescents for a greater range of applications. Choose FluxStream for simple, robust LED light industrial commercial linear lighting solutions that need to perform and endure.

Product data

General Information		Initial Performance (IEC Compliant)	
Lamp Source Code	LED	Luminaire Lumens	4000
Colour Temperature	4000K		
CRI	80		
Photometric Distribution Type	General Diffuse		
Mounting	Surface Suspended		
Operating and Electrical		Product Data	
Luminaire Input Watts	31	Order product name	4' Industrial, 4,000 Nominal Delivered Lumens, 4000K, 80 CRI, UNV, 0-10V Dimming
Voltages	120/277 V	Commercial Code	FSI440L840-UNV-DIM
		Order code	FSI440L840-UNV-DIM
		Catalog Number Description	4' Industrial, 4,000 Nominal Delivered Lumens, 4000K, 80 CRI, UNV, 0-10V Dimming
		Service / Spec Smart	Spec Smart (10 Days) USA
		Material Nr. (12NC)	DAY00008885
Mechanical and Housing			
Fixture Size	48 in		
Shape	Linear		