



FluxStream LED Industrial

4' Industrial, 5,500 Nominal Delivered Lumens, 3000K, 80 CRI, UNV, 0-10V Dimming

4' Industrial, 5,500 Nominal Delivered Lumens, 3000K, 80 CRI, UNV, 0-10V Dimming

The FluxStream family of LED linear luminaires deliver high-quality, more uniform light versus fluorescents for a greater range of applications. Choose FluxStream for simple, robust LED light industrial commercial linear lighting solutions that need to perform and endure.

Product data

General Information	
Lamp Source Code	LED
Color Temperature	3000K
CRI	80
Mounting	Surface Suspended

Operating and Electrical	
Luminaire Input Watts	45
Voltages	120/277 V

Mechanical and Housing	
Fixture Size	48 in
Shape	Linear

Initial Performance (IEC Compliant)	
Luminaire Lumens	5500

Product Data	
Order product name	4' Industrial, 5,500 Nominal Delivered Lumens, 3000K, 80 CRI, UNV, 0-10V Dimming
Commercial Code	FSI455L830-UNV-DIM
Order code	FSI455L830-UNV-DIM
Catalog Number Description	4' Industrial, 5,500 Nominal Delivered Lumens, 3000K, 80 CRI, UNV, 0-10V Dimming
Service / Spec Smart	-
Material Nr. (12NC)	DAY00008888