



ClearAppeal Recessed LED

2x2, 3000 Nominal Delivered Lumens, 80 CRI, 3500K, Diffuse (Smooth), Dimming Driver

2x2, 3000 Nominal Delivered Lumens, 80 CRI, 3500K, Diffuse (Smooth), Dimming Driver

Product data

General Information	
Color Temperature	3500K
CRI	80
Mounting	Recessed
Operating and Electrical	
Luminaire Input Watts	32
Voltages	347/UNIV V
Mechanical and Housing	
Fixture Size	2 ft x 2 ft
Shape	Square
Initial Performance (IEC Compliant)	
Luminaire Lumens	3000

Product Data	
Order product name	2x2, 3000 Nominal Delivered Lumens, 80 CRI, 3500K, Diffuse (Smooth), Dimming Driver
Commercial Code	2CAG30L835-2-DS-UNV-DIM
Order code	2CAG30L835-2-DS-UNV-DIM
Catalog Number Description	2x2, 3000 Nominal Delivered Lumens, 80 CRI, 3500K, Diffuse (Smooth), Dimming Driver
Service / Spec Smart	Spec Smart (10 Days) USA
Material Nr. (12NC)	DAY0008627