



# ClearAppeal Recessed LED

2x2, 3400 Nominal Delivered Lumens, 80 CRI, 3500K, Diffuse (Smooth), Dimming Driver

2x2, 3400 Nominal Delivered Lumens, 80 CRI, 3500K, Diffuse (Smooth), Dimming Driver

## Product data

General Information	
Color Temperature	3500K
CRI	80
Mounting	Recessed
Operating and Electrical	
Luminaire Input Watts	37
Voltages	347/UNIV V
Mechanical and Housing	
Fixture Size	2 ft x 2 ft
Shape	Square
Initial Performance (IEC Compliant)	
Luminaire Lumens	3400

Product Data	
Order product name	2x2, 3400 Nominal Delivered Lumens, 80 CRI, 3500K, Diffuse (Smooth), Dimming Driver
Commercial Code	2CAG34L835-2-DS-DIM
Order code	2CAG34L835-2-DS-DIM
Catalog Number Description	2x2, 3400 Nominal Delivered Lumens, 80 CRI, 3500K, Diffuse (Smooth), Dimming Driver
Service / Spec Smart	Service Smart (2 Days) USA
Material Nr. (12NC)	DAY0008633