



ClearAppeal Recessed LED

2x4, 5500 Nominal Delivered Lumens, 80 CRI, 3500K, Diffuse (Smooth), Dimming Driver, Emergency Battery Backup

2x4, 5500 Nominal Delivered Lumens, 80 CRI, 3500K, Diffuse (Smooth), Dimming Driver, Emergency Battery Backup

Product data

| General Information | |
|-------------------------------------|-------------|
| Color Temperature | 3500K |
| CRI | 80 |
| Mounting | Recessed |
| Operating and Electrical | |
| Luminaire Input Watts | 51 |
| Voltages | 347/UNIV V |
| Mechanical and Housing | |
| Fixture Size | 2 ft x 4 ft |
| Shape | Rectangular |
| Initial Performance (IEC Compliant) | |
| Luminaire Lumens | 5500 |

| Product Data | |
|----------------------------|---|
| Order product name | 2x4, 5500 Nominal Delivered Lumens, 80 CRI, 3500K, Diffuse (Smooth), Dimming Driver, Emergency Battery Backup |
| Commercial Code | 2CAG55L835-4-DS-DIM-EMLED |
| Order code | 2CAG55L835-4-DS-DIM-EMLED |
| Catalog Number Description | 2x4, 5500 Nominal Delivered Lumens, 80 CRI, 3500K, Diffuse (Smooth), Dimming Driver, Emergency Battery Backup |
| Service / Spec Smart | Spec Smart (10 Days) USA |
| Material Nr. (12NC) | DAY0008654 |